# **AMDLA4010S MOLDED INDUCTOR**



Request Samples (>)



Check Inventory (>)





#### **FEATURES**

- Shielded construction
- Soft saturation
- Low DCR per cubic mm
- Designed for switching frequencies between 100KHz-3MHz
- Automotive option available upon request





## **ELECTRICAL SPECIFICATIONS @ 25°C**

PART NUMBER*	INDUCTANCE (uH)		IRMS (A)	ISAT (A)	DC RESISTANCE (mΩ)		TYPE	
	(un)				TYP	MAX		
AMDLA4010S-R22MT	0.22	20	11	18	9.8	12	Lead Frame	
AMDLA4010S-R33MT	0.33	20	10	14	11.7	14.5	Lead Frame	
AMDLA4010S-R47MT	0.47	20	8.5	11	15.2	18.5	Lead Frame	
AMDLA4010S-1R0MT	1.0	20	4.2	6.5	35	42	Lead Frame	
AMDLA4010S-2R2MT	2.2	20	2.8	4.5	90	108	Lead Frame	
AMDLA4010S-6R8MT	6.8	20	1.4	2.8	224	268	Lead Frame	
AMDLA4010S-100MT	10	20	1.1	1.7	260	312	Lead Frame	

<sup>\*</sup> Please refer to Part Identification section

#### **Test Conditions**

Inductance: 1 MHz, 1 V, 0 Adc Humidity Range: 65% RH

Temperature Rise Current: Current measured at Δ T of 40°C Saturation Current: Current measured at  $\Delta$  L of 30%

# **GENERAL SPECIFICATIONS**

### **Operating Temperature:**

-55°C to +125°C with (40°C rise) Irms current.

Maximum Part Temperature: +125°C **Components Storage Temperature:** 

-55°C to +125°C

Tape and Reel Packaging Temperature: -20°C to +65°C

MSL: Level 1

#### **MATERIALS**

Metal Alloy Core: Wire: Copper Terminal: Tin Plating Black Ink:

# PART BUILDER





**1. Tolerance:** M = 20%

2. Packaging: B = Bulk

T = Tape and Reel (4,000pcs/reel)

## PRODUCT DIMENSIONS








<sup>\*</sup>Refer to Electrical Specification table



## RECOMMENDED REFLOW PROFILE



ZONE	DESCRIPTION	TEMPERATURE	TIMES
1	Preheat	T <sub>smin</sub> ~ T <sub>smax</sub> 150°C ~ 180°C	60 ~ 120 sec.
2	Reflow	T <sub>∟</sub> 230°C	30 ~ 40 sec.
3	Peak Heat	T <sub>P</sub> 250°C+0/-5°C	10 sec. MAX






## **PACKAGING**


Tape and Reel: 4,000 Units per Carton: 32,000

T&R per Carton: 8


Weight per Carton: 13.2 kg Weight per Unit: 0.34 g

Carton Dimensions: 360 x 360 x 400 mm





TYPE	А	В	С	D
13" x 12 mm	12.4 +2/-0	100.0 ± 0.5	13.0 +0.5/-0.2	330.0



B <sub>o</sub>	A <sub>o</sub>	K <sub>o</sub>	Р	W	F	Т	D
4.85 ± 0	10 4.45 ± 0.10	1.40 ± 0.10	8.00 ± 0.10	12.00 ± 0.30	5.50 ± 0.10	$0.30 \pm 0.05$	1.50

Dimensions: mm

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.

