

Light Meter

✓ **Measures light intensity up to 20,000 Foot-candles or Lux**
With high resolution to 0.01 Fc/Lux

Features:

- Relative mode indicates change in light levels
- Peak mode capture highest reading
- Remote light sensor on 12" (305mm) coiled cable — expandable to 24" (609mm)
- Utilizes precision photo diode and color correction filter
- Cosine and color corrected measurements
- High accuracy of $\pm(5\%$ reading + 0.5%FS)
- MIN/MAX feature stores maximum and minimum readings
- Data Hold freezes reading in the display
- Large LCD display with analog bargraph
- Backlight for readings in low light levels
- Dimensions: 5.9 x 2.95 x 1.57" (150 x 75 x 40mm); Weight: 7oz (200g)
- Complete with 9V battery, light sensor with protective cover, and protective holster



Ideal for measuring parking lot illumination, security lighting, and night ATM areas

**Test Equipment
Depot**
1-800-517-8431

99 Washington Street
Melrose, MA 02176
Phone 781-665-1400
Toll Free 1-800-517-8431

- ▶ Visit us at www.TestEquipmentDepot.com
- ▶ Back to the Extech LT300 Product Info Page