

# Cisco Industrial Ethernet 2000 Series Switches

The Cisco<sup>®</sup> Industrial Ethernet 2000 (IE 2000) Series is a range of compact, industrially ruggedized access switches. IE 2000 series provide customers with ease of use, secure access, and industry leading convergence using Cisco Resilient Ethernet Protocol (REP). Multiple industries such as automotive, oil and gas, mining, transportation, and energy companies are all increasingly requiring IP based networks in their production areas. The newest IE 2000 additions have been designed to support access layer connectivity and to meet the increasing needs for security, voice, and video traffic across industrial networks.

## Product Overview

Cisco IE 2000 Series are designed for low cost, low ports, and small sizes:

- 4, 8, or 16 10/100Base-T Ethernet ports fixed configurations with compact form factor
- 2x Gigabit Combo ports, SFP (100MB and 1G) or RJ45 uplink
- Dual-input DC power supply, alarm relays, DIN rail mount
- Conformal coating available
- Swappable SD flash card (for configuration storage), mini-USB connector, and RS-232 console port
- Industrial environmental compliance and certifications
- Industrial partner applications: EtherNet/IP and PROFINET

## Primary Applications and Features

- **Easy deployment:** Zero-touch discovery using DHCP, express setup, fast bootup time (<60 sec) to help migrating to Ethernet environment without resistance
- **Security:** Dot1x, port security, and DHCP allow dynamic port-base authentication, Secure Shell (SSHv2), SNMPv3 provides encrypted administrator traffic during Telnet and SNMP sessions, TACACS+ and RADIUS authentication facilitate centralized control and restrict unauthorized users
- **Resiliency:** Flex links for fast recovery, Cisco REP protocol for fast convergence
- **Manageability:** Auto SmartPort, Web Device Manager, Telnet, HTTPS access, SNMP, CNA and CiscoWorks LAN Management Solution (LMS)
- **Industrial automation protocols:** Support for Common Industrial Protocol (CIP) and PROFINETv2 that allow integration with existing management platform from Rockwell, Siemens, and other industrial environments

## Switch performance and scalability

- Line rate/Non-blocking ports
- Forwarding rate: 6.5 Mpps with 64 bytes packets
- Egress buffer: 2MB
- Unicast MAC addresses: 8000
- IGMP multicast groups: 255
- Max VLANs: 255
- IPv4 Mac security ACEs: 384 (default TCAM template)

## Switch Configurations

Figure 1 shows switch models, and Table 1 shows Cisco IE 2000 Series Configuration information.

**Figure 1.** Industrial Ethernet 2000 Series



**Table 1.** Cisco IE 2000 Series Configurations

Product Number	Total Ports	RJ45 Ports	Combo Ports	SFP slots	Software	IEEE 1588	Conformal Coating
IE-2000-4TS-L*	6	4		2 FE**	LAN Lite		
IE-2000-4TS-B	6	4		2 FE	LAN Base		
IE-2000-4T-L	6	6			LAN Lite		
IE-2000-4T-B	6	6			LAN Base		
IE-2000-4TS-G-L	6	4		2 GE	LAN Lite		
IE-2000-4TS-G-B	6	4		2 GE	LAN Base		
IE-2000-4T-G-L	6	6 (2 GE)			LAN Lite		
IE-2000-4T-G-B	6	6 (2 GE)			LAN Base		
IE-2000-8TC-L	10	8	2 FE		LAN Lite		
IE-2000-8TC-B	10	8	2 FE		LAN Base		
IE-2000-8TC-G-L	10	8	2 GE		LAN Lite		
IE-2000-8TC-G-B	10	8	2 GE		LAN Base		
IE-2000-8TC-G-E	10	8	2 GE		LAN Base	X	
IE-2000-16TC-L	20	16	2 FE	2 FE	LAN Lite		
IE-2000-16TC-B	20	16	2 FE	2 FE	LAN Base		
IE-2000-16TC-G-L	20	16	2 GE	2 FE	LAN Lite		
IE-2000-16TC-G-E	20	16	2 GE	2 FE	LAN Base	X	
IE-2000-16TC-G-X	20	16	2 GE	2 FE	LAN Base	X	X

Product Number	Description
PWR-IE3000-AC	AC to DC 24V/2.1A DIN Rail power supply, supports 110/220VAC and 88-300VDC
PWR-2955-AC	AC to DC 24V/2.5A DIN Rail power supply
MEM-SD-1GB-RGD	1GB SD Memory card
STK-RACKMNT-2955	19" DIN Rail Mount Kit

\*-L: Field upgradable.

\*\* For the complete list of the supported SFP models, refer to [http://www.cisco.com/en/US/products/hw/modules/ps5455/products\\_device\\_support\\_tables\\_list.html](http://www.cisco.com/en/US/products/hw/modules/ps5455/products_device_support_tables_list.html)

Table 2 lists product specifications.

**Table 2.** Product Specifications

Description	Specification
<b>Hardware</b>	<ul style="list-style-type: none"> <li>• 256MB DRAM with ECC memory</li> <li>• IEEE 1588v2 FPGA</li> <li>• 64MB on-board flash memory</li> <li>• 1GB removable SD flash memory card (optional)</li> <li>• Mini-USB connector</li> </ul>
<b>Alarm</b>	<ul style="list-style-type: none"> <li>• Alarm I/O: two alarm inputs to detect dry contact open or closed, one alarm output relay</li> </ul>
<b>Power Supply</b>	<ul style="list-style-type: none"> <li>• Redundant DC input voltage with operating range: 9.6 to 60 VDC</li> <li>• Maximum DC input current: 1A @48 VDC, 2A @24 VDC</li> </ul>
<b>Power Consumption</b>	<ul style="list-style-type: none"> <li>• 6-port models: 9.5-15W</li> <li>• 10-port models: 12.5-20W</li> <li>• 20-port models: 21-30W</li> </ul>
<b>Connectors and Cabling</b>	<ul style="list-style-type: none"> <li>• 100BASE-FX MMF (2 km), -LX SMF (10 km) -ZX SMF (100 km), -BX10 SMF (10 km) SFP and CWDM SFP-based ports: LC fiber connectors</li> <li>• 10/100/1000BASE-T ports: RJ-45 connectors, 4-pair Category 5 UTP cabling</li> </ul>
<b>Dimensions (H x W x D) Including DIN Rail</b>	<ul style="list-style-type: none"> <li>• IE-2000 6 ports chassis: 5.1 x 2.95 x 4.51 in (12.7 x 7.37 x 11.46 cm)</li> <li>• IE-2000 10 ports short chassis: 5.1 x 3.6 x 4.51 in (12.7 x 8.89 x 11.46 cm)</li> <li>• IE-2000 10 ports long chassis: 5.1 x 3.6 x 5.26 in (12.7 x 8.89 x 13.36 cm)</li> <li>• IE-2000 20 ports chassis: 5.1 x 5.0 x 5.26 in (12.7 x 12.45 x 13.36 cm)</li> </ul>
<b>Weight</b>	<ul style="list-style-type: none"> <li>• IE-2000 6 ports chassis: 2.45 lbs (1.11 kg)</li> <li>• IE-2000 10 ports short chassis: 2.75 lbs (1.25 kg)</li> <li>• IE-2000 10 ports long chassis: 3.45 lbs (1.56 kg)</li> <li>• IE-2000 20 ports chassis: 4.35 lbs (1.97 kg)</li> </ul>

Table 3 lists Cisco IE 2000 software features.

**Table 3.** Cisco IE 2000 Software Features

LAN Lite Feature Set	LAN Base Feature Set
Layer 2 switching features	LAN Lite Feature Set
MAC address notification, Unicast Mac filtering	QoS, DHCP, 802.1x, DAI, port security, IP Source Guard, HTTPPS
SCP, SSH, SNMPv3, TACACS+, RADIUS	VVID, Guest VLAN, MAB
Web Device Manager, SmartPort, Cisco Prime LMS, CNA	EtherChannel, Storm Control
Industrial Manager Protocols: CIP EtherNet/IP, PROFINET v2*	IPv4 Static Routing, IPv6 host capabilities
Multicast: IGMP, IGMP querier	RSPAN
Resilient Ethernet Protocol (REP), Flex Links, STP, RSTP, MST	IEEE 1588v2 PTP

\* Post CCO certification

Table 4 lists compliance specifications.

**Table 4.** Compliance Specifications

Description	Specification
<b>Safety Certifications</b>	<ul style="list-style-type: none"> <li>• UL/CSA 60950-1</li> <li>• EN 60950-1</li> <li>• CB to IEC 60950-1 (with country deviations)</li> <li>• NOM to NOM-019-SCF1 (through partners and distributors)</li> <li>• CE Marking</li> </ul>
<b>Hazard Location</b>	<ul style="list-style-type: none"> <li>• ANSI/ISA 12.12.01 (Class 1, Div 2 A-D)</li> <li>• EN 60079-0, -15 ATEX certification (Class I, Zone 2 A-D)</li> </ul>
<b>EMC Emissions and Immunity Compliance</b>	<ul style="list-style-type: none"> <li>• FCC 47 CFR Part 15 Class A</li> <li>• EN 55022A Class A</li> </ul>

Description	Specification
	<ul style="list-style-type: none"> <li>• VCCI Class A</li> <li>• RoHS compliance</li> <li>• AS/NZS CISPR 22 Class A, AS/NZS CISPR 24</li> <li>• CISPR11 Class A, CISPR22 Class A</li> <li>• ICES 003 Class A</li> <li>• KCC -Korea</li> <li>• CE Marking</li> <li>• C-Tick (Australia)</li> <li>• Russia certification</li> <li>• Brazil certification</li> <li>• IEC/EN61000-4-2 (Electro Static Discharge), 15kV Air/8kV Contact</li> <li>• IEC/EN 61000-4-3 (Radiated Immunity, 10 and 20V/m)</li> <li>• IEC/EN 61000-4-4 (Fast Transients - 4kV power line, 4kV data line)</li> <li>• IEC/EN 61000-4-5 (Surge 2 kV/1 kV)</li> <li>• IEC/EN 61000-4-6 (Conducted Immunity, 10V/emf)</li> <li>• IEC/EN 61000-4-8 (Power Frequency Magnetic Field Immunity)</li> <li>• IEC/EN 61000-4-9 (Pulse Magnetic Field Immunity)</li> <li>• IEC/EN 61000-4-10 (Oscillatory Magnetic Field Immunity)</li> <li>• IEC/EN 61000-4-11 (AC power Voltage Immunity)</li> <li>• IEC/EN 61000-4-29 (Voltage Dips Immunity)</li> <li>• IEC/EN 61000-6-1 (Immunity for Light Industrial Environments)</li> <li>• IEC/EN 61000-6-4 Class A</li> <li>• EN 61326</li> </ul>
<b>Shock and Vibration</b>	<ul style="list-style-type: none"> <li>• IEC 60068-2-27 (Operational Shock: 30G 11ms, half sine)</li> <li>• IEC 60068-2-27 (Non-Operational Shock 55-70G, trapezoidal)</li> <li>• IEC 60068-2-6, IEC 60068-2-64, EN 61373 (Operational Vibration)</li> <li>• IEC 60068-2-6, IEC 60068-2-64, EN 61373 (Non-operational Vibration)</li> </ul>
<b>Industry Standards</b>	<ul style="list-style-type: none"> <li>• UL 508</li> <li>• CSA C22.2 No. 142</li> <li>• EN 61131-2 (Programmable Controllers)</li> <li>• Protective Coating</li> <li>• Substation (IEEE 1613, IEC 61850-3) KEMA post FCS</li> <li>• Lloyd's Register Type Approval - ENV2 or ENV3</li> <li>• British, German Lloyds</li> <li>• Marine (LR, BV, GL, DnV, Rina ABS, KR)</li> <li>• RA 156-165 Mhz 24 dBuV/M - Class A is 50 dBuV/M - Marine Band</li> <li>• Railway EN 50155, EN50121-3-2, EN50121-4 (EMI, EMC, Mechanical)</li> <li>• NEMA TS-2</li> <li>• ABB Industrial IT Certification</li> <li>• IP30</li> <li>• ODVA Industrial EtherNet/IP</li> <li>• PROFINETv2</li> </ul>
<b>Corrosive Testing*</b>	<ul style="list-style-type: none"> <li>• ISO-12944-6</li> <li>• IEC-60068-2-60</li> </ul>
<b>Humidity</b>	<ul style="list-style-type: none"> <li>• IEC 60068-52-2 (Salt Fog Mist, Test Kb) Marine environments</li> <li>• IEC 60068 -2-3</li> <li>• IEC 60068-2-30</li> <li>• Relative Humidity: 5% to 95% Non-condensing</li> </ul>
<b>Operating Temperature</b>	<ul style="list-style-type: none"> <li>• -40C to +70C (Vented Enclosure Operating)</li> <li>• -40C to +60C (Sealed Enclosure Operating)</li> <li>• -34C to +75C (Fan or Blower equipped Enclosure Operating)</li> <li>• Operational Altitude: Up to 15,000 ft</li> </ul>
<b>Storage Temperature</b>	<ul style="list-style-type: none"> <li>• -40C to +85C (Storage Temperature)</li> <li>• IEC 60068-2-14</li> <li>• Storage Altitude: Up to 15,000 ft</li> </ul>
<b>MTBF</b>	<ul style="list-style-type: none"> <li>• Mean time between failure: 374,052 hrs (42.7 yrs)</li> </ul>
<b>Warranty</b>	<ul style="list-style-type: none"> <li>• One year limited warranty</li> </ul>

\* IE-2000-16TC-G-X only.

## Warranty Information

Warranty information is available on <http://www.cisco-servicefinder.com/warrantyfinder.aspx>.

## Service and Support

Cisco is committed to minimizing total cost of ownership (TCO). The company offers a portfolio of technical support services to help make sure that its products operate efficiently, remain highly available, and benefit from the most up-to-date system software. The services and support programs described in Table 5 are available as part of the Cisco Desktop Switching Service and Support solution and are available directly from Cisco and through resellers.

**Table 5.** Cisco Services and Support Programs

Service and Support	Features	Benefits
<b>Advanced Services</b>		
<ul style="list-style-type: none"><li>• Cisco Total Implementation Solutions (TIS), available direct from Cisco</li><li>• Cisco Packaged TIS, available through resellers</li><li>• Cisco SMARTnet® and SMARTnet Onsite support, available direct from Cisco</li><li>• Cisco Packaged SMARTnet support program, available through resellers</li><li>• Cisco SMB Support Assistant</li></ul>	<ul style="list-style-type: none"><li>• Project management</li><li>• Site survey, configuration, and deployment</li><li>• Installation, test, and cutover</li><li>• Training</li><li>• Major moves, adds, and changes</li><li>• Design review and product staging</li><li>• Access to software updates 24 hours</li><li>• Web access to technical repositories</li><li>• Telephone support through the Cisco Technical Assistance Center (TAC)</li><li>• Advance replacement of hardware parts</li></ul>	<ul style="list-style-type: none"><li>• Supplements existing staff</li><li>• Helps ensure that functions meet needs</li><li>• Mitigates risk</li><li>• Helps enable proactive or expedited issue resolution</li><li>• Lowers TCO by taking advantage of Cisco expertise and knowledge</li><li>• Minimizes network downtime</li></ul>

For more information about Cisco products, contact:

- United States and Canada: 800 553-6387
- Europe: 32 2 778 4242
- Australia: 612 9935 4107
- Other: 408 526-7209
- URL: <http://www.cisco.com>



Americas Headquarters  
Cisco Systems, Inc.  
San Jose, CA

Asia Pacific Headquarters  
Cisco Systems (USA) Pte. Ltd.  
Singapore

Europe Headquarters  
Cisco Systems International BV Amsterdam,  
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at [www.cisco.com/go/offices](http://www.cisco.com/go/offices).

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: [www.cisco.com/go/trademarks](http://www.cisco.com/go/trademarks). Third party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)