LSF0102-Q100

2-bit bidirectional multi-voltage level translator; open-drain; push-pull

Rev. 2 — 4 September 2020

Product data sheet

1. General description

The LSF0102-Q100 is a 2 channel bidirectional multi-voltage level translator for open-drain and push-pull applications. It supports up to 100 MHz up translation and \geq 100 MHz down translation at \leq 30 pF capacitive load. There is no need for a direction pin which minimizes system effort. The LSF0102-Q100 supports 5 V tolerant I/O pins for compatibility with TTL levels in a variety of applications. The ability to set up different voltage translation levels on each channel makes the device very flexible and suitable for a lot of different applications.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

2. Features and benefits

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)

 Specified from -40 °C to +125 °C
- Bidirectional voltage translation with no direction pin
- Up translation
 - ≤ 100 MHz; C_L = 30 pF
 - ≤ 40 MHz; C_L = 50 pF
- Down translation
 - ≥ 100 MHz; C_L = 30 pF
 - \leq 40 MHz; C_L = 50 pF
- Hot insertion
- Bidirectional voltage level translation between:
 - 0.95 V and 1.8 V, 2.5 V, 3.3 V and 5.0 V
 - 1.2 V and 1.8 V, 2.5 V, 3.3 V and 5.0 V
 - 1.8 V and 2.5 V, 3.3 V and 5.0 V
 - 2.5 V and 3.3 V and 5.0 V
 - 3.3 V and 5.0 V
- Low standby current
- 5 V tolerant I/O pins to support TTL
- Low R_{ON} provides less signal distortion
- High-impedance I/O pins for EN = Low.
- Flow-through pinout for easy PCB trace routing.
- Latch-up performance exceeds 100 mA per JESD78 class II level A
- ESD protection:
 - HBM ANSI/ESDA/JEDEC JS-001 Class 2 exceeds 2000 V
 - CDM ANSI/ESDA/JEDEC JS-002 Class C3 exceeds 1000 V

3. Applications

- GPIO, MDIO, PMBus, SMBus, SDIO, UART, I²C, and other interfaces in Telecom infrastructure
- Industrial
- Personal computing

ne<mark>x</mark>peria

4. Ordering information


Type number Package											
Temperature range Name Description											
LSF0102DP-Q100	-40 °C to +125 °C	TSSOP8	plastic thin shrink small outline package; 8 leads; body width 3 mm; lead length 0.5 mm	SOT505-2							
LSF0102DC-Q100	-40 °C to +125 °C	VSSOP8	plastic very thin shrink small outline package; 8 leads; body width 2.3 mm	SOT765-1							

5. Marking

Table 2. Marking									
Type number	Marking code[1]								
LSF0102DP-Q100	h2								
LSF0102DC-Q100	h2								


[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

6. Functional diagram



7. Pinning information

7.1. Pinning



7.2. Pin description

Table 3. Pin description									
Symbol	Pin	Description							
GND	1	ground (0 V)							
refA	2	reference voltage A							
A1, A2	3, 4	data input/output A							
B1, B2	6, 5	data input/output B							
refB	7	reference voltage B							
EN	8	enable input (active HIGH)							

8. Functional description

Table 4. Function table

H = HIGH voltage level; *L* = LOW voltage level; *Z* = high-impedance OFF-state.

Input	input/output
EN	An, Bn channel
Н	An = Bn
L	Z

9. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit	
VI	input voltage	pins refA, refB, An, Bn and EN	[1]	-0.5	+7.0	V
I _{I/O}	input/ouput current	pins refA, refB, An and Bn; continuous channel current		-	+128	mA
I _{IK}	input clamping current	V _I < 0 V		-50	-	mA
T _{stg}	storage temperature			-65	+150	°C
P _{tot}	total power dissipation	T _{amb} = -40 °C to +125 °C	[2]	-	250	mW

[1] The minimum input voltage rating may be exceeded if the input current rating is observed.

[2] For SOT505-2 (TSSOP8) package: P_{tot} derates linearly with 4.6 mW/K above 96 °C.

For SOT765-1 (VSSOP8) package: P_{tot} derates linearly with 4.9 mW/K above 99 °C.

10. Recommended operating conditions

10010 0.1	able 6. Recommended operating conditions											
Symbol	Parameter	Conditions	Min	Мах	Unit							
VI	input voltage	pins refA, refB, An, Bn and EN	0.0	5.0	V							
I _{I/O}	input/ouput current	pins refA, refB, An and Bn; continuous channel current	-	+64	mA							
T _{amb}	ambient temperature		-40	+125	°C							

Table 6. Recommended operating conditions

11. Static characteristics


Table 7. Static characteristics

At recommended operating conditions voltages are referenced to GND (ground = 0 V).

Symbol	I Parameter Conditions		T _{amb} =	Unit		
			Min	Min Typ[1]		1
V _{IK}	input clamping voltage	V _{EN} = 0 V; I _I = -18 mA	-1.2	-	-	V
l _l	leakage current	pins An, Bn, refA, refB and EN; V _I = GND to 5.0 V	-	1	5	μA
Cı	input capacitance	pins refA, refB and EN; V _I = 0 V or 3 V	-	6	-	pF
C _{io(off)}	OFF-state input/output capacitance	pins An, Bn; V _O = 0 V or 3 V; V _{EN} = 0.0 V	-	3	6.0	pF
C _{io(on)}	ON-state input/output capacitance	pins An, Bn; V _O = 0 V or 3 V; V _{EN} = 3.0 V	-	6	12.5	pF
R _{ON}	ON resistance	see <u>Fig. 3</u> [2]				
		V _I = 0 V; V _{pu} = 5.0 V; I _O = 64 mA				
		V _{refA} = 3.3 V	-	3	-	Ω
		V _{refA} = 1.8 V	-	4	-	Ω
		V _{refA} = 1.0 V	-	7	-	Ω
		V _I = 0 V; V _{pu} = 5.0 V; I _O = 32mA				
		V _{refA} = 1.8 V	-	4	-	Ω
		V _{refA} = 2.5 V	-	3	-	Ω
		V _I = 1.8 V; V _{pu} = 5.0 V; I _O = 15 mA				
		V _{refA} = 3.3 V	-	4	-	Ω
		V _I = 1.0 V; V _{pu} = 3.3 V; I _O = 10 mA				
		V _{refA} = 1.8 V	-	7	-	Ω
		V _I = 0 V; V _{pu} = 3.3 V; I _O = 10 mA				
		V _{refA} = 1.0 V	-	5	-	Ω
		V _I = 0 V; V _{pu} = 1.8 V; I _O = 10 mA				
		V _{refA} = 1.0 V	-	6	-	Ω

[1] All typical values are measured at T_{amb} = 25 °C.

[2] Measured by the voltage drop between the An and Bn pins at the indicated current through the switch. ON resistance is determined by the lowest voltage of the two (An or Bn) pins.



12. Dynamic characteristics


Table 8. Switching characteristics

GND = 0 V; for waveform see Fig. 4; for test circuit see Fig. 5

Symbol	Parameter	Conditions	T _{amb}	25 °C	Unit		
			Min	Typ[1]	Max		
Translat	ing down						
t _{PLH}	LOW to HIGH	An to Bn or Bn to An;					
ľ	propagation delay	V _{IH} = V _{pu} = V _{refA} + 1 V					
		V _{refA} = 1.5 V; C _L = 15 pF	-	0.35	-	ns	
		V _{refA} = 1.5 V; C _L = 30 pF	-	0.8	-	ns	
		V _{refA} = 1.5 V; C _L = 50 pF	-	1.2	-	ns	
		V _{refA} = 2.3 V; C _L = 15 pF	-	0.3	-	ns	
		V _{refA} = 2.3 V; C _L = 30 pF	-	0.7	-	ns	
		V _{refA} = 2.3 V; C _L = 50 pF	-	1.1	-	ns	
t _{PHL}	HIGH to LOW	An to Bn or Bn to An;					
-rnL	propagation delay	V _{IH} = V _{pu} = V _{refA} + 1 V					
		V _{refA} = 1.5 V; C _L = 15 pF	-	0.5	-	ns	
		V _{refA} = 1.5 V; C _L = 30 pF	-	1.0	-	ns	
		V _{refA} = 1.5 V; C _L = 50 pF	-	1.3	-	ns	
		V _{refA} = 2.3 V; C _L = 15 pF	-	0.4	-	ns	
		V _{refA} = 2.3 V; C _L = 30 pF	-	0.8	-	ns	
		V _{refA} = 2.3 V; C _L = 50 pF	-	1.2	-	ns	
Translat	ing up	1					
t _{PLH}	LOW to HIGH	An to Bn or Bn to An;					
	propagation delay	V _{IH} = V _{refA} ; V _{EXT} = V _{pu} = V _{refA} + 1 V					
		V _{refA} = 1.5 V; C _L = 15 pF	-	0.5	-	ns	
		V _{refA} = 1.5 V; C _L = 30 pF	-	0.9	-	ns	
		V _{refA} = 1.5 V; C _L = 50 pF	-	1.1	-	ns	
		V _{refA} = 2.3 V; C _L = 15 pF	-	0.4	-	ns	
		V _{refA} = 2.3 V; C _L = 30 pF	-	0.8	-	ns	
		V _{refA} = 2.3 V; C _L = 50 pF	-	1.0	-	ns	
t _{PHL}	HIGH to LOW	An to Bn or Bn to An;					
	propagation delay	$V_{IH} = V_{refA}; V_{EXT} = V_{pu} = V_{refA} + 1 V$					
		V _{refA} = 1.5 V; C _L = 15 pF	-	0.6	-	ns	
		V _{refA} = 1.5 V; C _L = 30 pF	-	1.1	-	ns	
		V _{refA} = 1.5 V; C _L = 50 pF	-	1.3	-	ns	
		V _{refA} = 2.3 V; C _L = 15 pF	-	0.4	-	ns	
		V _{refA} = 2.3 V; C _L = 30 pF	-	0.9	-	ns	
		V _{refA} = 2.3 V; C _L = 50 pF	-	1.0	-	ns	

[1] All typical values are measured at T_{amb} = 25 °C.

12.1. Waveforms and test circuit



LSF0102_Q100

Table 9. Test data

Input		Output	Load				
t _r , t _f	V _M	V _M	C _L C _{EN} [1] R _L [1] R _{pu}				
≤ 2 ns	0.5V _{refA}	0.5V _{refA}	15 pF, 30 pF, 50 pF	100 nF	300 Ω	200 kΩ	

[1] All typical values are measured at T_{amb} = 25 °C.

LSF0102_Q100

13. Package outline




Fig. 6. Package outline SOT505-2 (TSSOP8)

LSF0102-Q100

2-bit bidirectional multi-voltage level translator; open-drain; push-pull

VSSOP8: plastic very thin shrink small outline package; 8 leads; body width 2.3 mm SOT765-1 D Α Е Х ДУ = v (M) A H_{E} 7 5 ŧ Q ł ٩2 A₁ (A_3) pin 1 index Lp detail X 4 е ⊕ w M bp 0 5 mm scale

Dimen	sions (mm ar	e the c	original	dimer	isions)														
U	nit	A max.	A ₁	A ₂	A ₃	bp	с	D ⁽¹⁾	E ⁽²⁾	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ	
	max		0.15	0.85	0.40	0.27	0.23	2.1	2.4	0.5	3.2	<u> </u>	0.40	0.21		0.00	0.4	0.4	8°	
mm	nom min	1	0.00	0.60	0.12	0.17	0.08	1.9	2.2	0.5	3.0	0.4	0.15	0.19	0.2	0.08	0.1	0.1	0°	
Note 1. Plas	stic or r	netal p	orotrusi	ons of	0.15 n	nm ma	ximum	per si	de are	not inc	cluded.									
2. Plas	stic or r	netal p	orotrus	ons of	0.25 n	nm ma	ximum	per si	de are	not ind	cluded.									sot765-1_po
C	Dutline							Re	eferenc	es							Europ	bean		lagua data
v	ersion			IEC	;		JED	EC		JE	ITA						proje	ction		Issue date
SC	DT765-	1					MO-	187				i				ł	\leq] ()		- 07-06-02- 16-05-31



14. Abbreviations

Table 10. Abbreviations							
Acronym	Description						
CDM	Charged Device Model						
ESD	ElectroStatic Discharge						
HBM	Human Body Model						
TTL	Transistor-Transistor Logic						

15. Revision history

Table 11. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
LSF0102_Q100 v.2	20200904	LSF0102_Q100 v.1		
Modifications:	Type number LSF	0102DC-Q100 (SOT765-	1/VSSOP8) added.	
LSF0102_Q100 v.1	20200611	Product data sheet	-	-

16. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description	1
2. Features and benefits	1
3. Applications	1
4. Ordering information	2
5. Marking	2
6. Functional diagram	2
7. Pinning information	2
7.1. Pinning	2
7.2. Pin description	3
8. Functional description	3
9. Limiting values	3
10. Recommended operating conditions	3
11. Static characteristics	4
12. Dynamic characteristics	5
12.1. Waveforms and test circuit	6
13. Package outline	8
14. Abbreviations	
15. Revision history	10
16. Legal information	

© Nexperia B.V. 2020. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 4 September 2020

LSF0102_Q100