



**RoHS
Compliant**



Specifications

Rated Current	: 15Amp AC300V
Insulation Withstands Volt	: AC2000V min
Insulation Resistance	: >2000MΩ at DC500V
Operating Temperature	: -40°C to +120°C
Wire Range	: 14~22 AWG
Screw Torque	: 12 lb-in

Diagram



Part Number	Number of Poles	A (mm)	B (mm)
MC24351	4	39.2	28.5
MC24352	6	58.2	47.5
MC24353	8	77.2	66.5
MC24354	10	96.2	85.5

Item	Material	Plating / Finish
1	Insulating Body, PBT (UL94V-0)	Black
2	Terminal, Brass	Tin Plated
3	Screw, Steel	Ni plated

Part Number Table

Description	Part Number
Wire-To-Board Terminal Block, 9.53mm, 4 Positions, Screw	MC24351
Wire-To-Board Terminal Block, 9.53mm, 6 Positions, Screw	MC24352
Wire-To-Board Terminal Block, 9.53mm, 8 Positions, Screw	MC24353
Wire-To-Board Terminal Block, 9.53mm, 10 Positions, Screw	MC24354

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro