

**GRM  
02-  
KIT-  
DE**

**01005 Class  
1 & 2**

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GRM0225C1HR20BA03	0402M/01005	COG	50Vdc	0.2pF	±0.1pF	0.22max	20
2	GRM0225C1HR30BA03	0402M/01005	COG	50Vdc	0.3pF	±0.1pF	0.22max	20
3	GRM0225C1HR40BA03	0402M/01005	COG	50Vdc	0.4pF	±0.1pF	0.22max	20
4	GRM0225C1HR50BA03	0402M/01005	COG	50Vdc	0.5pF	±0.1pF	0.22max	20
5	GRM0225C1HR60BA03	0402M/01005	COG	50Vdc	0.6pF	±0.1pF	0.22max	20
6	GRM0225C1HR70BA03	0402M/01005	COG	50Vdc	0.7pF	±0.1pF	0.22max	20
7	GRM0225C1HR80BA03	0402M/01005	COG	50Vdc	0.8pF	±0.1pF	0.22max	20
8	GRM0225C1HR90BA03	0402M/01005	COG	50Vdc	0.9pF	±0.1pF	0.22max	20
9	GRM0225C1H1R0CA03	0402M/01005	COG	50Vdc	1.0pF	±0.25pF	0.22max	100
10	GRM0225C1H1R1CA03	0402M/01005	COG	50Vdc	1.1pF	±0.25pF	0.22max	20
11	GRM0225C1H1R2CA03	0402M/01005	COG	50Vdc	1.2pF	±0.25pF	0.22max	20
12	GRM0225C1H1R3CA03	0402M/01005	COG	50Vdc	1.3pF	±0.25pF	0.22max	20
13	GRM0225C1H1R4CA03	0402M/01005	COG	50Vdc	1.4pF	±0.25pF	0.22max	20
14	GRM0225C1H1R5CA03	0402M/01005	COG	50Vdc	1.5pF	±0.25pF	0.22max	20
15	GRM0225C1H1R6CA03	0402M/01005	COG	50Vdc	1.6pF	±0.25pF	0.22max	20
16	GRM0225C1H1R7CA03	0402M/01005	COG	50Vdc	1.7pF	±0.25pF	0.22max	20
17	GRM0225C1H1R8CA03	0402M/01005	COG	50Vdc	1.8pF	±0.25pF	0.22max	20
18	GRM0225C1H1R9CA03	0402M/01005	COG	50Vdc	1.9pF	±0.25pF	0.22max	20
19	GRM0225C1H2R0CA03	0402M/01005	COG	50Vdc	2.0pF	±0.25pF	0.22max	20
20	GRM0225C1H2R1CA03	0402M/01005	COG	50Vdc	2.1pF	±0.25pF	0.22max	20
21	GRM0225C1H2R2CA03	0402M/01005	COG	50Vdc	2.2pF	±0.25pF	0.22max	20
22	GRM0225C1H2R3CA03	0402M/01005	COG	50Vdc	2.3pF	±0.25pF	0.22max	20
23	GRM0225C1H2R4CA03	0402M/01005	COG	50Vdc	2.4pF	±0.25pF	0.22max	20
24	GRM0225C1H2R5CA03	0402M/01005	COG	50Vdc	2.5pF	±0.25pF	0.22max	20
25	GRM0225C1H2R6CA03	0402M/01005	COG	50Vdc	2.6pF	±0.25pF	0.22max	20
26	GRM0225C1H2R7CA03	0402M/01005	COG	50Vdc	2.7pF	±0.25pF	0.22max	20
27	GRM0225C1H2R8CA03	0402M/01005	COG	50Vdc	2.8pF	±0.25pF	0.22max	20
28	GRM0225C1H2R9CA03	0402M/01005	COG	50Vdc	2.9pF	±0.25pF	0.22max	20
29	GRM0225C1H3R0CA03	0402M/01005	COG	50Vdc	3.0pF	±0.25pF	0.22max	20
30	GRM0225C1H3R3CA03	0402M/01005	COG	50Vdc	3.3pF	±0.25pF	0.22max	20
31	GRM0225C1H3R6CA03	0402M/01005	COG	50Vdc	3.6pF	±0.25pF	0.22max	20
32	GRM0225C1H3R9CA03	0402M/01005	COG	50Vdc	3.9pF	±0.25pF	0.22max	20

33	GRM0225C1H4R0CA03	0402M/01005	COG	50Vdc	4.0pF	±0.25pF	0.22max	20
34	GRM0225C1H4R3CA03	0402M/01005	COG	50Vdc	4.3pF	±0.25pF	0.22max	20
35	GRM0225C1H4R7CA03	0402M/01005	COG	50Vdc	4.7pF	±0.25pF	0.22max	20
36	GRM0225C1H5R1CA03	0402M/01005	COG	50Vdc	5.1pF	±0.25pF	0.22max	20
37	GRM0225C1H5R6CA03	0402M/01005	COG	50Vdc	5.6pF	±0.25pF	0.22max	20
38	GRM0225C1H6R2CA03	0402M/01005	COG	50Vdc	6.2pF	±0.25pF	0.22max	20
39	GRM0225C1H6R8CA03	0402M/01005	COG	50Vdc	6.8pF	±0.25pF	0.22max	20
40	GRM0225C1H7R5CA03	0402M/01005	COG	50Vdc	7.5pF	±0.25pF	0.22max	20
41	GRM0225C1H8R2CA03	0402M/01005	COG	50Vdc	8.2pF	±0.25pF	0.22max	20
42	GRM0225C1H9R1CA03	0402M/01005	COG	50Vdc	9.1pF	±0.25pF	0.22max	20
43	GRM0225C1H100JA03	0402M/01005	COG	50Vdc	10pF	±5%	0.22max	100
44	GRM0225C1H120JA03	0402M/01005	COG	50Vdc	12pF	±5%	0.22max	20
45	GRM0225C1H150JA03	0402M/01005	COG	50Vdc	15pF	±5%	0.22max	20
46	GRM0225C1H180JA02	0402M/01005	COG	50Vdc	18pF	±5%	0.22max	20
47	GRM0225C1H220JA02	0402M/01005	COG	50Vdc	22pF	±5%	0.22max	20
48	GRM0225C1H270JA02	0402M/01005	COG	50Vdc	27pF	±5%	0.22max	20
49	GRM0225C1H330JA02	0402M/01005	COG	50Vdc	33pF	±5%	0.22max	20
50	GRM0225C1H390JA02	0402M/01005	COG	50Vdc	39pF	±5%	0.22max	20
51	GRM0225C1H470JA02	0402M/01005	COG	50Vdc	47pF	±5%	0.22max	20
52	GRM0225C1H560JA02	0402M/01005	COG	50Vdc	56pF	±5%	0.22max	20
53	GRM0225C1H680JA02	0402M/01005	COG	50Vdc	68pF	±5%	0.22max	20
54	GRM0225C1H820JA02	0402M/01005	COG	50Vdc	82pF	±5%	0.22max	20
55	GRM0225C1H101JA02	0402M/01005	COG	50Vdc	100pF	±5%	0.22max	100
56	GRM0225C1E221JA02	0402M/01005	COG	25Vdc	220pF	±5%	0.22max	20
57	GRM022R61C222KE01	0402M/01005	X5R	16Vdc	2200pF	±10%	0.22max	20
58	GRM022R61C472KE01	0402M/01005	X5R	16Vdc	4700pF	±10%	0.22max	20
59	GRM022R61C103KE01	0402M/01005	X5R	16Vdc	0.01μF	±10%	0.22max	100
60	GRM022R60J223KE15	0402M/01005	X5R	6.3Vdc	0.022μF	±10%	0.22max	20
61	GRM022R60J473ME15	0402M/01005	X5R	6.3Vdc	0.047μF	±20%	0.22max	20
62	GRM022R60J104KE15	0402M/01005	X5R	6.3Vdc	0.1μF	±10%	0.22max	100
63	GRM022R60J224ME14	0402M/01005	X5R	6.3Vdc	0.22μF	±20%	0.22max	20
64	GRM022R60J474ME05	0402M/01005	X5R	6.3Vdc	0.47μF	±20%	0.22max	20
65	GRM022D80E474ME01	0402M/01005	X6T	2.5Vdc	0.47μF	±20%	0.25max	20
66	GRM022R71C471KE14	0402M/01005	X7R	16Vdc	470pF	±10%	0.22max	20
67	GRM022R71C102KE14	0402M/01005	X7R	16Vdc	1000pF	±10%	0.22max	100