

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GRM033C80J105ME05	0603M/0201	X6S	6.3Vdc	1μF	±20%	0.39max	20
2	GRM033C81A105ME05	0603M/0201	X6S	10Vdc	1μF	±20%	0.39max	20
3	GRM155C81C105KE11	1005M/0402	X6S	16Vdc	1μF	±10%	0.6max	20
4	GRM155C81E105KE11	1005M/0402	X6S	25Vdc	1μF	±10%	0.6max	20
5	GRM033C80G225ME01	0603M/0201	X6S	4Vdc	2.2μF	±20%	0.39max	20
6	GRM155D80G225ME95	1005M/0402	X6T	4Vdc	2.2μF	±20%	0.55max	20
7	GRM035C80J225ME01	0603M/0201	X6S	6.3Vdc	2.2μF	±20%	0.55max	20
8	GRM155D80J225ME95	1005M/0402	X6T	6.3Vdc	2.2μF	±20%	0.55max	20
9	GRM155C81A225ME15	1005M/0402	X6S	10Vdc	2.2μF	±20%	0.55max	20
10	GRM155C81C225KE11	1005M/0402	X6S	16Vdc	2.2μF	±10%	0.7max	20
11	GRM155D81E225ME11	1005M/0402	X6T	25Vdc	2.2μF	±20%	0.65max	20
12	GRM188C81E225KE11	1608M/0603	X6S	25Vdc	2.2μF	±10%	1max	20
13	GRM155C80J475MEAA	1005M/0402	X6S	6.3Vdc	4.7μF	±20%	0.65max	20
14	GRM188C81C475KE11	1608M/0603	X6S	16Vdc	4.7μF	±10%	0.95max	20
15	GRM188C81E475KE11	1608M/0603	X6S	25Vdc	4.7μF	±10%	1max	20
16	GRM21BC81H475ME11	2012M/0805	X6S	50Vdc	4.7μF	±20%	1.45max	20
17	GRM188C80J106MA73	1608M/0603	X6S	6.3Vdc	10μF	±20%	1max	20
18	GRM188C81A106KA73	1608M/0603	X6S	10Vdc	10μF	±10%	1max	20
19	GRM188C81C106MA73	1608M/0603	X6S	16Vdc	10μF	±20%	1max	20
20	GRM21BC81C106KA73	2012M/0805	X6S	16Vdc	10μF	±10%	1.4max	20
21	GRM21BC81E106KE51	2012M/0805	X6S	25Vdc	10μF	±10%	1.4max	20
22	GRM31CC81E106KA12	3216M/1206	X6S	25Vdc	10μF	±10%	1.8max	20
23	GRM188C80G226ME15	1608M/0603	X6S	4Vdc	22μF	±20%	1max	20
24	GRM188C80J226ME15	1608M/0603	X6S	6.3Vdc	22μF	±20%	1max	20
25	GRM21BC81A226ME44	2012M/0805	X6S	10Vdc	22μF	±20%	1.45max	20
26	GRM21BC81C226ME44	2012M/0805	X6S	16Vdc	22μF	±20%	1.45max	20
27	GRM31CC81E226KE11	3216M/1206	X6S	25Vdc	22μF	±10%	1.9max	20
28	GRM21BC80G476ME15	2012M/0805	X6S	4Vdc	47μF	±20%	1.45max	20
29	GRM31CC81A476ME44	3216M/1206	X6S	10Vdc	47μF	±20%	1.9max	20
30	GRM32EC81C476ME15	3225M/1210	X6S	16Vdc	47μF	±20%	2.7max	20
31	GRM21BC80E107ME15	2012M/0805	X6S	2.5Vdc	100μF	±20%	1.45max	20
32	GRM21BC80G107ME15	2012M/0805	X6S	4Vdc	100μF	±20%	1.45max	20
33	GRM31CD80G107MEA8	3216M/1206	X6T	4Vdc	100μF	±20%	1.9max	20

34	GRM31CD80J107MEA8	3216M/1206	X6T	6.3Vdc	100µF	±20%	1.9max	20
35	GRM31CC80E227ME11	3216M/1206	X6S	2.5Vdc	220µF	±20%	1.9max	20
36	GRM32EC80G227ME05	3225M/1210	X6S	4Vdc	220µF	±20%	2.8max	20
37	GRM32EC80E337ME05	3225M/1210	X6S	2.5Vdc	330µF	±20%	2.8max	20
38	GRM033D70G105ME01	0603M/0201	X7T	4Vdc	1µF	±20%	0.39max	20
39	GRM033D70J105ME01	0603M/0201	X7T	6.3Vdc	1µF	±20%	0.39max	20
40	GRM155C70J105KE11	1005M/0402	X7S	6.3Vdc	1µF	±10%	0.6max	20
41	GRM155C71A105KE11	1005M/0402	X7S	10Vdc	1µF	±10%	0.6max	20
42	GRM21BC72A105KE01	2012M/0805	X7S	100Vdc	1µF	±10%	1.45max	20
43	GRM035D70G225ME01	0603M/0201	X7T	4Vdc	2.2µF	±20%	0.55max	20
44	GRM155C70J225KE11	1005M/0402	X7S	6.3Vdc	2.2µF	±10%	0.7max	20
45	GRM155D71A225KE11	1005M/0402	X7T	10Vdc	2.2µF	±10%	0.65max	20
46	GRM155D71C225ME11	1005M/0402	X7T	16Vdc	2.2µF	±20%	0.65max	20
47	GRM188C71C225KE11	1608M/0603	X7S	16Vdc	2.2µF	±10%	1max	20
48	GRM188C71E225KE11	1608M/0603	X7S	25Vdc	2.2µF	±10%	1max	20
49	GRM21BD72A225KE01	2012M/0805	X7T	100Vdc	2.2µF	±10%	1.45max	20
50	GRM188C71C475KE21	1608M/0603	X7S	16Vdc	4.7µF	±10%	1max	20
51	GRM21BC71E475KE11	2012M/0805	X7S	25Vdc	4.7µF	±10%	1.45max	20
52	GRM21BC71H475KE11	2012M/0805	X7S	50Vdc	4.7µF	±10%	1.45max	20
53	GRM31CC72A475ME11	3216M/1206	X7S	100Vdc	4.7µF	±20%	1.9max	20
54	GRM188D70J106MA73	1608M/0603	X7T	6.3Vdc	10µF	±20%	1max	20
55	GRM188D71A106KA73	1608M/0603	X7T	10Vdc	10µF	±10%	1max	20
56	GRM21BC71C106KE11	2012M/0805	X7S	16Vdc	10µF	±10%	1.45max	20
57	GRM21BC71E106ME11	2012M/0805	X7S	25Vdc	10µF	±20%	1.45max	20
58	GRM31CR71E106MA12	3216M/1206	X7R	25Vdc	10µF	±20%	1.8max	20
59	GRM31CD71H106KE11	3216M/1206	X7T	50Vdc	10µF	±10%	1.9max	20
60	GRM32EC72A106ME05	3225M/1210	X7S	100Vdc	10µF	±20%	2.7max	20
61	GRM21BE70G226ME51	2012M/0805	X7U	4Vdc	22µF	±20%	1.4max	20
62	GRM21BD70J226ME44	2012M/0805	X7T	6.3Vdc	22µF	±20%	1.45max	20
63	GRM21BD71A226ME44	2012M/0805	X7T	10Vdc	22µF	±20%	1.45max	20
64	GRM31CR71A226ME15	3216M/1206	X7R	10Vdc	22µF	±20%	1.8max	20
65	GRM31CC71C226ME11	3216M/1206	X7S	16Vdc	22µF	±20%	1.9max	20
66	GRM32ER71E226KE15	3225M/1210	X7R	25Vdc	22µF	±10%	2.7max	20
67	GRM31CE70G476ME15	3216M/1206	X7U	4Vdc	47µF	±20%	1.8max	20
68	GRM31CE70J476ME15	3216M/1206	X7U	6.3Vdc	47µF	±20%	1.8max	20
69	GRM32ER71A476ME15	3225M/1210	X7R	10Vdc	47µF	±20%	2.7max	20
70	GRM31CE70G107MEA8	3216M/1206	X7U	4Vdc	100µF	±20%	1.9max	20
71	GRM32EE70G107ME19	3225M/1210	X7U	4Vdc	100µF	±20%	2.7max	20
72	GRM32EE70J107ME15	3225M/1210	X7U	6.3Vdc	100µF	±20%	2.7max	20