



GCM-KIT-X7-DE-B

**Class2 Automotive AEC-Q200
Qualified**

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GCM155R71H102KA37	1005M/0402	X7R	50Vdc	1000pF	±10%	0.55max	20
2	GCM155R71H222KA37	1005M/0402	X7R	50Vdc	2200pF	±10%	0.55max	20
3	GCM155R71H472KA37	1005M/0402	X7R	50Vdc	4700pF	±10%	0.55max	20
4	GCM155R71H103KA55	1005M/0402	X7R	50Vdc	0.01μF	±10%	0.55max	20
5	GCM155R71H223KA55	1005M/0402	X7R	50Vdc	0.022μF	±10%	0.55max	20
6	GCM155R71H473KE02	1005M/0402	X7R	50Vdc	0.047μF	±10%	0.55max	20
7	GCM155R71H104KE02	1005M/0402	X7R	50Vdc	0.1μF	±10%	0.55max	20
8	GCM155R71C224KE02	1005M/0402	X7R	16Vdc	0.22μF	±10%	0.55max	20
9	GCM155C71A474KE36	1005M/0402	X7S	10Vdc	0.47μF	±10%	0.6max	20
10	GCM155C71A105KE38	1005M/0402	X7S	10Vdc	1μF	±10%	0.7max	20
11	GCM188R71H224KA64	1608M/0603	X7R	50Vdc	0.22μF	±10%	0.9max	20
12	GCM188R71E474KA64	1608M/0603	X7R	25Vdc	0.47μF	±10%	0.9max	20
13	GCM188R71C105KA64	1608M/0603	X7R	16Vdc	1μF	±10%	0.9max	20
14	GCM188R71E105KA64	1608M/0603	X7R	25Vdc	1μF	±10%	0.9max	20
15	GCM188R70J225KE22	1608M/0603	X7R	6.3Vdc	2.2μF	±10%	0.9max	20
16	GCM21BR71H474KA55	2012M/0805	X7R	50Vdc	0.47μF	±10%	1.4max	20
17	GCM21BR71H105KA03	2012M/0805	X7R	50Vdc	1μF	±10%	1.4max	20
18	GCM21BR71A225KA37	2012M/0805	X7R	10Vdc	2.2μF	±10%	1.4max	20
19	GCM21BR71C225KA64	2012M/0805	X7R	16Vdc	2.2μF	±10%	1.4max	20
20	GCM21BR71E225KA73	2012M/0805	X7R	25Vdc	2.2μF	±10%	1.4max	20
21	GCM21BC7YA225KE02	2012M/0805	X7S	35Vdc	2.2μF	±10%	1.4max	20
22	GCM21BC71A475KA73	2012M/0805	X7S	10Vdc	4.7μF	±10%	1.4max	20
23	GCM21BR71C475KA73	2012M/0805	X7R	16Vdc	4.7μF	±10%	1.4max	20
24	GCM21BC71E475KE36	2012M/0805	X7S	25Vdc	4.7μF	±10%	1.45max	20
25	GCM21BC7YA475KE36	2012M/0805	X7S	35Vdc	4.7μF	±10%	1.45max	20
26	GCM21BR70J106KE22	2012M/0805	X7R	6.3Vdc	10μF	±10%	1.4max	20
27	GCM21BR71A106KE22	2012M/0805	X7R	10Vdc	10μF	±10%	1.4max	20
28	GCM21BC71C106KE36	2012M/0805	X7S	16Vdc	10μF	±10%	1.45max	20
29	GCM31CR71H225KA55	3216M/1206	X7R	50Vdc	2.2μF	±10%	1.8max	20
30	GCM31CC72A225KE02	3216M/1206	X7S	100Vdc	2.2μF	±10%	1.8max	20
31	GCM31CC71H475KA03	3216M/1206	X7S	50Vdc	4.7μF	±10%	1.8max	20
32	GCM31CC71E106KA03	3216M/1206	X7S	25Vdc	10μF	±10%	1.9max	20
33	GCM31CR70J226KE23	3216M/1206	X7R	6.3Vdc	22μF	±10%	1.8max	20

34	GCM31CR71A226KE02	3216M/1206	X7R	10Vdc	22 μ F	\pm 10%	1.8max	20
35	GCM32DC72A475KE02	3225M/1210	X7S	100Vdc	4.7 μ F	\pm 10%	2.2max	20
36	GCM32EC71H106KA03	3225M/1210	X7S	50Vdc	10 μ F	\pm 10%	2.7max	20
37	GCM32ER71C226KE19	3225M/1210	X7R	16Vdc	22 μ F	\pm 10%	2.7max	20
38	GCM32EC71E226KE36	3225M/1210	X7S	25Vdc	22 μ F	\pm 10%	2.85max	20
39	GCM32ER70J476KE19	3225M/1210	X7R	6.3Vdc	47 μ F	\pm 10%	2.7max	20
40	GCM32EC71A476KE02	3225M/1210	X7S	10Vdc	47 μ F	\pm 10%	2.7max	20