



GCQ15-KIT-5R1-47-A-DE

**0402 Class1 Hi-Q Capacitor
Automotive AEC-Q200 Qualified**

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GCQ1555C1H5R1BB01	1005M/0402	C0G	50Vdc	5.1pF	±0.1pF	0.55max	20
2	GCQ1555C1H5R2BB01	1005M/0402	C0G	50Vdc	5.2pF	±0.1pF	0.55max	20
3	GCQ1555C1H5R3BB01	1005M/0402	C0G	50Vdc	5.3pF	±0.1pF	0.55max	20
4	GCQ1555C1H5R4BB01	1005M/0402	C0G	50Vdc	5.4pF	±0.1pF	0.55max	20
5	GCQ1555C1H5R5BB01	1005M/0402	C0G	50Vdc	5.5pF	±0.1pF	0.55max	20
6	GCQ1555C1H5R6BB01	1005M/0402	C0G	50Vdc	5.6pF	±0.1pF	0.55max	20
7	GCQ1555C1H5R7BB01	1005M/0402	C0G	50Vdc	5.7pF	±0.1pF	0.55max	20
8	GCQ1555C1H5R8BB01	1005M/0402	C0G	50Vdc	5.8pF	±0.1pF	0.55max	20
9	GCQ1555C1H5R9BB01	1005M/0402	C0G	50Vdc	5.9pF	±0.1pF	0.55max	20
10	GCQ1555C1H6R0BB01	1005M/0402	C0G	50Vdc	6.0pF	±0.1pF	0.55max	20
11	GCQ1555C1H6R1BB01	1005M/0402	C0G	50Vdc	6.1pF	±0.1pF	0.55max	20
12	GCQ1555C1H6R2BB01	1005M/0402	C0G	50Vdc	6.2pF	±0.1pF	0.55max	20
13	GCQ1555C1H6R3BB01	1005M/0402	C0G	50Vdc	6.3pF	±0.1pF	0.55max	20
14	GCQ1555C1H6R4BB01	1005M/0402	C0G	50Vdc	6.4pF	±0.1pF	0.55max	20
15	GCQ1555C1H6R5BB01	1005M/0402	C0G	50Vdc	6.5pF	±0.1pF	0.55max	20
16	GCQ1555C1H6R6BB01	1005M/0402	C0G	50Vdc	6.6pF	±0.1pF	0.55max	20
17	GCQ1555C1H6R7BB01	1005M/0402	C0G	50Vdc	6.7pF	±0.1pF	0.55max	20
18	GCQ1555C1H6R8BB01	1005M/0402	C0G	50Vdc	6.8pF	±0.1pF	0.55max	20
19	GCQ1555C1H6R9BB01	1005M/0402	C0G	50Vdc	6.9pF	±0.1pF	0.55max	20
20	GCQ1555C1H7R0BB01	1005M/0402	C0G	50Vdc	7.0pF	±0.1pF	0.55max	20
21	GCQ1555C1H7R1BB01	1005M/0402	C0G	50Vdc	7.1pF	±0.1pF	0.55max	20
22	GCQ1555C1H7R2BB01	1005M/0402	C0G	50Vdc	7.2pF	±0.1pF	0.55max	20
23	GCQ1555C1H7R3BB01	1005M/0402	C0G	50Vdc	7.3pF	±0.1pF	0.55max	20
24	GCQ1555C1H7R4BB01	1005M/0402	C0G	50Vdc	7.4pF	±0.1pF	0.55max	20
25	GCQ1555C1H7R5BB01	1005M/0402	C0G	50Vdc	7.5pF	±0.1pF	0.55max	20
26	GCQ1555C1H7R6BB01	1005M/0402	C0G	50Vdc	7.6pF	±0.1pF	0.55max	20
27	GCQ1555C1H7R7BB01	1005M/0402	C0G	50Vdc	7.7pF	±0.1pF	0.55max	20
28	GCQ1555C1H7R8BB01	1005M/0402	C0G	50Vdc	7.8pF	±0.1pF	0.55max	20
29	GCQ1555C1H7R9BB01	1005M/0402	C0G	50Vdc	7.9pF	±0.1pF	0.55max	20
30	GCQ1555C1H8R0BB01	1005M/0402	C0G	50Vdc	8.0pF	±0.1pF	0.55max	20
31	GCQ1555C1H8R1BB01	1005M/0402	C0G	50Vdc	8.1pF	±0.1pF	0.55max	20
32	GCQ1555C1H8R2BB01	1005M/0402	C0G	50Vdc	8.2pF	±0.1pF	0.55max	20
33	GCQ1555C1H8R3BB01	1005M/0402	C0G	50Vdc	8.3pF	±0.1pF	0.55max	20

34	GCQ1555C1H8R4BB01	1005M/0402	COG	50Vdc	8.4pF	±0.1pF	0.55max	20
35	GCQ1555C1H8R5BB01	1005M/0402	COG	50Vdc	8.5pF	±0.1pF	0.55max	20
36	GCQ1555C1H8R6BB01	1005M/0402	COG	50Vdc	8.6pF	±0.1pF	0.55max	20
37	GCQ1555C1H8R7BB01	1005M/0402	COG	50Vdc	8.7pF	±0.1pF	0.55max	20
38	GCQ1555C1H8R8BB01	1005M/0402	COG	50Vdc	8.8pF	±0.1pF	0.55max	20
39	GCQ1555C1H8R9BB01	1005M/0402	COG	50Vdc	8.9pF	±0.1pF	0.55max	20
40	GCQ1555C1H9R0BB01	1005M/0402	COG	50Vdc	9.0pF	±0.1pF	0.55max	20
41	GCQ1555C1H9R1BB01	1005M/0402	COG	50Vdc	9.1pF	±0.1pF	0.55max	20
42	GCQ1555C1H9R2BB01	1005M/0402	COG	50Vdc	9.2pF	±0.1pF	0.55max	20
43	GCQ1555C1H9R3BB01	1005M/0402	COG	50Vdc	9.3pF	±0.1pF	0.55max	20
44	GCQ1555C1H9R4BB01	1005M/0402	COG	50Vdc	9.4pF	±0.1pF	0.55max	20
45	GCQ1555C1H9R5BB01	1005M/0402	COG	50Vdc	9.5pF	±0.1pF	0.55max	20
46	GCQ1555C1H9R6BB01	1005M/0402	COG	50Vdc	9.6pF	±0.1pF	0.55max	20
47	GCQ1555C1H9R7BB01	1005M/0402	COG	50Vdc	9.7pF	±0.1pF	0.55max	20
48	GCQ1555C1H9R8BB01	1005M/0402	COG	50Vdc	9.8pF	±0.1pF	0.55max	20
49	GCQ1555C1H9R9BB01	1005M/0402	COG	50Vdc	9.9pF	±0.1pF	0.55max	20
50	GCQ1555C1H100JB01	1005M/0402	COG	50Vdc	10pF	±5%	0.55max	20
51	GCQ1555C1H120JB01	1005M/0402	COG	50Vdc	12pF	±5%	0.55max	20
52	GCQ1555C1H150JB01	1005M/0402	COG	50Vdc	15pF	±5%	0.55max	20
53	GCQ1555C1H180JB01	1005M/0402	COG	50Vdc	18pF	±5%	0.55max	20
54	GCQ1555C1H200JB01	1005M/0402	COG	50Vdc	20pF	±5%	0.55max	20
55	GCQ1555C1H220JB01	1005M/0402	COG	50Vdc	22pF	±5%	0.55max	20
56	GCQ1555C1H240JB01	1005M/0402	COG	50Vdc	24pF	±5%	0.55max	20
57	GCQ1555C1H270JB01	1005M/0402	COG	50Vdc	27pF	±5%	0.55max	20
58	GCQ1555C1H300JB01	1005M/0402	COG	50Vdc	30pF	±5%	0.55max	20
59	GCQ1555C1H330JB01	1005M/0402	COG	50Vdc	33pF	±5%	0.55max	20
60	GCQ1555C1H360JB01	1005M/0402	COG	50Vdc	36pF	±5%	0.55max	20
61	GCQ1555C1H390JB01	1005M/0402	COG	50Vdc	39pF	±5%	0.55max	20
62	GCQ1555C1H430JB01	1005M/0402	COG	50Vdc	43pF	±5%	0.55max	20
63	GCQ1555C1H470JB01	1005M/0402	COG	50Vdc	47pF	±5%	0.55max	20