

Chip beads For power line Large current / Low DC resistance **MPZ-H** series









MPZ0603-H type














FEATURES

- Noise reduction solution for power line.
- This product achieves a 50% reduction in resistance in the 「-C」 series of standards.
- O Reduced from the -C on the standard series power loss in circuits.
- O A 50% improvement in the rated current compared to conventional power beads facilitates downsizing from 1005 shapes.
- Operating temperature range: -55 to +125°C

APPLICATION

- O Noise removal for mobile devices such as smartphones and tablet terminals, and various modules.
- O Noise removal for PCs and recorders, household appliances such as STBs, smart grids, and industrial equipment.
- O Application guides: Smart phones/tablets

PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

| Impedance | | DC resistance | Rated current* | Part No. |
|---------------------|-----------|------------------|----------------|------------------|
| [100MHz] | | | | |
| (Ω) | Tolerance | (Ω)max. | (mA)max. | |
| 22 | ±25% | 0.036 | 1900 | MPZ0603S220HT000 |
| 33 | ±25% | 0.050 | 1600 | MPZ0603S330HT000 |
| 80 | ±25% | 0.095 | 1200 | MPZ0603S800HT000 |
| 120 | ±25% | 0.130 | 1000 | MPZ0603S121HT000 |


^{*} Please refer to the graph of rated current vs. temperature characteristics (derating) about the rating current at 85°C or more in temperature of the product.

Measurement equipment

| Measurement item | Product No. | Manufacturer |
|------------------|---------------|-----------------------|
| Impedance | E4991A+16192A | Keysight Technologies |
| DC resistance | Type-7556 | Yokogawa |

^{*} Equivalent measurement equipment may be used.

Rated current vs. temperature characteristics (derating)








MPZ0603-H type


Z VS. FREQUENCY CHARACTERISTICS (BY SERIES)

MPZ0603S series




Z, X, R VS. FREQUENCY CHARACTERISTICS


MPZ0603S220H




MPZ0603S330H



MPZ0603S800H




MPZ0603S121H






MPZ0603-H type

■SHAPE & DIMENSIONS



■ RECOMMENDED LAND PATTERN



Solder Resist


Pattern

| Rated current | Pad thickness & d | | |
|---------------|-------------------|------|------|
| (A) | 18um | 35um | 70um |
| 0.9max. | 0.3 | 0.3 | 0.3 |
| 2.0max. | 1.2 | 0.7 | 0.3 |

Dimensions in mm


■PACKAGING STYLE

□REEL DIMENSIONS




Dimensions in mm

TAPE DIMENSIONS



| Туре | Α | В | K |
|-----------|-----------|-----------|---------|
| MPZ0603-H | 0.38±0.05 | 0.68±0.05 | 0.5max. |



Dimensions in mm

□PACKAGE QUANTITY


| Package quantity | 15,000 pcs/reel |
|------------------|-----------------|

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

| Operating temperature range | Storage temperature range* | Individual weight |
|-----------------------------|----------------------------|----------------------|
| −55 to +125°C | −55 to +125°C | 0.3 mg |

^{*} The storage temperature range is for after the assembly.

■ RECOMMENDED REFLOW PROFILE



^{*} It is necessary to design the land pattern in consideration of heat dissipation.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

| ⚠ REMINDERS |
|--|
| The storage period is less than 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH (less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. |
| Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.). |
| Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperatur does not exceed 150°C. |
| Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur. |
| When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions. |
| Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermadesign. |
| Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference. |
| Use a wrist band to discharge static electricity in your body through the grounding wire. |
| Do not expose the products to magnets or magnetic fields. |
| Do not use for a purpose outside of the contents regulated in the delivery specifications. |
| The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to societ |

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment

person or property.

(4) Power-generation control equipment

set forth in the each catalog, please contact us.

- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions