




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.51 – 1.03 mm²**

Quick Disconnect Mating Tab Width: **2.8 mm [.11 in]**

Quick Disconnect Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Standard
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.03 – 3 mm[.08 – .118 in]
Overall Length	14 mm[.551 in]
Receptacle Terminal Stock Thickness	.25 mm[.01 in]
Wire Size	.51 – 1.03 mm ²
Quick Disconnect Mating Tab Width	2.8 mm[.11 in]
Quick Disconnect Mating Tab Thickness	.51 mm[.02 in]

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Industry Standards

UL Rating	Listed
CSA Certified	Yes

Packaging Features

Packaging Quantity	10000
Quick Disconnect Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free





Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 160597-4 FASTON 110 REC 0.05-0.15MM2 TPBR	 TE Part # 444149-2 .110S FASTON REC	 TE Part # 881608-1 FASTON 110 REC 0.5-1.0 MM2 0.25 X12.30 BR	 TE Part # 151614-1 MINI FASTON 110 REC 24-20 AWG PTPBR
 TE Part # 63202-2 FASTON 110 REC 18-14 AWG PTPBR	 TE Part # 2150203-1 OCEAN_2.0_APPLICATOR-E-070F120F	 TE Part # 7-2150203-7 OCEAN_2.0_SPARE_PART_KIT-070F120F	 TE Part # 737107-1 FASTON .110 REC 0.5-1.0 MM2 PLAIN BR
 TE Part # 170033-1 FASTON 110 16-20AWG BR	 TE Part # 2-2150203-1 OCEAN_2.0_APPLICATOR-E-070F120F	 TE Part # 2-2150203-2 OCEAN_2.0_APPLICATOR-E-070F120FA	 TE Part # 2150203-2 OCEAN_2.0_APPLICATOR-E-070F120FA



TE Part # 7-2150203-1
OCEAN_2.0_APPLICATOR-E-070F120F

TE Part # 7-2150203-2
OCEAN_2.0_APPLICATOR-E-070F120FA

TE Part # 881608-2
.110 S. FASTON REC.

Also in the Series | **FASTON 110**

Crimp Terminal Housings(17)

Insertion & Extraction Tools(2)

PCB Terminals(22)

Quick Disconnects(182)

Customers Also Bought

TE Part #6609065-4
CORCOM EDP SERIES SINGLE PHASE FILTERS

TE Part #216604-5
2X 5P HV190FEDERLEI

TE Part #1-1658527-9
622-0641LF=FSKT IDC S 06 30AU

TE Part #34853
TERMINAL,PG R 12-10 8

TE Part #160534-2
FASTON 110 REC 0.5-1.0MM2 .009X. 450 TPBR

TE Part #170359-3
MINI UNIVERSAL M-N-L PIN

TE Part #1-929504-1
TIMER, CONNECTOR HOUSING

TE Part #5-968972-1
AMP MCP, UN-SEALED CONNECTOR HOUSING

TE Part #179228-6
AMP COMMON TERMINATION HOUSINGS

TE Part #1-167019-0
10P. RIBBCBL 28AWG P1.27



Documents

Product Drawings

FASTON 110 REC 0.5-1.0MM2 .009X.450 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160484-4_AY_c-160484-4-ay.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160484-4_AY_c-160484-4-ay.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160484-4_AY_c-160484-4-ay.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

FASTON conn. .110 srs. rec. ctc.

Application Specification

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English