

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE300SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE300SH1%23

## "#" indicates a package specification code.


BLM15PE300SH1D

In Production AEC-Q200 RoHS REACH

< List of part numbers with package codes > BLM15PE300SH1J BLM15PE300SH1B BLM15PE300SH1D

## Appearance & Shape









(in mm)

0.5±0.05

0.5±0.05

# Packaging Information

Packaging	Specifications	Standard Packing Quantity
J	330mm Paper Tape	50000
В	Bulk(Bag)	1000
D	180mm Paper Tape	10000

## Applications

Automotive Usage

Powertrain/Safety

1 of 4

## Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Product Search Data Sheet

# BLM15PE300SH1D

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE300SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE300SH1%23

"#" indicates a package specification code.



- The chip ferrite beads BLM series is designed to function nearly as a resistor at noise frequencies, which greatly reduces the possibility of resonance and leaves signal wave forms undistorted.
  BLM series is effective in circuits without stable ground lines because BLM series does not need a connection to ground.
- 2.The nickel barrier structure of the external electrodes provides excellent solder heat resistance.3.BLM\_P series can be used in high current circuits
- due to its low DC resistance. It can match power lines to a maximum of 2.3ADC.

2 of 4

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

- without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





**Product Search Data Sheet** 

# BLM15PE300SH1D

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE300SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE300SH1%23

"#" indicates a package specification code.



## Specifications

Shape	SMD
Size Code (in inch)	0402
Length	1.0mm
Length Tolerance	±0.05mm
Width	0.5mm
Width Tolerance	±0.05mm
Thickness	0.5mm
Thickness Tolerance	±0.05mm
Operating Temperature Range	-55°C to 125°C
Mass(typ.)	0.001g
Number of Circuit	1
Rated Current (at 85°C)	2.3A
Rated Current (at 125°C)	1.4A
DC Resistance(max.)	0.035Ω
Impedance (at 100MHz)	30Ω
Impedance (at 100MHz) Tolerance	±25%
Size Code (in mm)	1005

3 of 4

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.






Product Search Data Sheet


BLM15PE300SH1D

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE300SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE300SH1%23

## "#" indicates a package specification code.






In operating temperature exceeding +85°C, derating of current is necessary for this series. Please apply the derating curve shown in chart according to

the operating temperature.

Derating of Rated Current



Impedance-Frequency Characteristics

## Derating of Rated Current

(Resistance element becomes dominant at high frequencies.)

Equivalent Circuit

4 of 4

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

