

Product Search Data Sheet


BLM15PE331SH1D

In Production AEC-Q200 RoHS REACH

< List of part numbers with package codes > BLM15PE331SH1J BLM15PE331SH1B BLM15PE331S

Appearance & Shape











0.5±0.05

Applications

Automotive Usage

Powertrain/Safety

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE331SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE331SH1%23

"#" indicates a package specification code.

BLM15PE331SH1D



Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|------------------|---------------------------------|
| J | 330mm Paper Tape | 50000 |
| В | Bulk(Bag) | 1000 |
| D | 180mm Paper Tape | 10000 |

1 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.





Product Search Data Sheet

BLM15PE331SH1D

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE331SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE331SH1%23

"#" indicates a package specification code.



Features

- 1. The chip ferrite beads BLM series is designed to function nearly as a resistor at noise frequencies, which greatly reduces the possibility of resonance and leaves signal wave forms undistorted. BLM series is effective in circuits without stable ground lines because BLM series does not need a connection to ground.
- 2. The nickel barrier structure of the external electrodes provides excellent solder heat resistance. 3.BLM_P series can be used in high current circuits
- due to its low DC resistance. It can match power lines to a maximum of 2.3ADC.

2 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

- without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.





Rata Product Search Data Sheet

BLM15PE331SH1D

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE331SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE331SH1%23

"#" indicates a package specification code.



Specifications

| Shape | SMD |
|------------------------------------|----------------|
| Size Code (in inch) | 0402 |
| Length | 1.0mm |
| Length Tolerance | ±0.05mm |
| Width | 0.5mm |
| Width Tolerance | ±0.05mm |
| Thickness | 0.5mm |
| Thickness Tolerance | ±0.05mm |
| Operating Temperature Range | -55°C to 125°C |
| Mass(typ.) | 0.001g |
| Number of Circuit | 1 |
| Rated Current (at 85°C) | 1A |
| Rated Current (at 125°C) | 580mA |
| DC Resistance(max.) | 0.21Ω |
| Impedance (at 100MHz) | 330Ω |
| Impedance (at 100MHz) Tolerance | ±25% |
| Size Code (in mm) | 1005 |

3 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.



Product Search Data Sheet

BLM15PE331SH1D

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15PE331SH1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=BLM15PE331SH1%23

"#" indicates a package specification code.




600 500 400 300 200 100 0 100 100 100 100 100 1000 3000 Frequency (MHz)

In operating temperature exceeding +85°C, derating of current is necessary for this series. Please apply the derating curve shown in chart according to

the operating temperature.

Derating of Rated Current



Impedance-Frequency Characteristics

Derating of Rated Current

(Resistance element becomes dominant at high frequencies.)

Equivalent Circuit

4 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

