

# Samsung V-NAND SSD 980 PRO

---

2021 Data Sheet

---

Revision 2.0



## LEGAL DISCLAIMER

SAMSUNG ELECTRONICS CO., LTD. RESERVES THE RIGHT TO CHANGE PRODUCTS, INFORMATION AND SPECIFICATIONS WITHOUT NOTICE.

Products and specifications discussed herein are provided for reference purposes only. All information discussed herein may change without notice and is provided on an "AS IS" basis, without warranties of any kind. This document and all information discussed herein remain the sole and exclusive property of Samsung Electronics Co., Ltd. No license of any patent, copyright, mask work, trademark or any other intellectual property right is granted under this document, by implication, estoppels or otherwise. Samsung products are not intended for use in life support, critical care, medical, safety equipment, or similar applications where product failure could result in loss of life or personal or physical harm, or any military or defense application, or any governmental procurement to which special terms or provisions may apply. For updates or additional information about Samsung products, contact your nearest Samsung representative. All brand names, trademarks and registered trademarks belong to their respective owners.

## COPYRIGHT © 2021

This material is copyrighted by Samsung Electronics Co., Ltd. Any unauthorized reproductions, use or disclosure of this material, or any part thereof, is strictly prohibited and is a violation under copyright law.

## TRADEMARKS & SERVICE MARKS

The Samsung logo is the trademark of Samsung Electronics Co., Ltd. All other company and product names may be trademarks of the respective companies with which they are associated.

For more information, please visit [www.samsung.com/ssd](http://www.samsung.com/ssd) and [www.samsungssd.com](http://www.samsungssd.com).

To download the latest software & manuals, please visit [www.samsung.com/samsungssd](http://www.samsung.com/samsungssd)

## TECHNICAL SPECIFICATIONS

Samsung SSD 980 PRO							
Usage Application	Client PCs						
Interface	PCIe Gen 4.0 x4, NVMe 1.3c						
Hardware Information	Capacity <sup>1)</sup>	250GB	500GB	1TB	2TB		
	Controller	Samsung Elpis Controller					
	NAND Flash Memory	Samsung V-NAND 3bit MLC					
	DRAM Cache Memory	512MB LPDDR4		1GB LPDDR4	2GB LPDDR4		
	Dimension	Max 80.15 x Max 22.15 x Max 2.38 (mm)					
	Form Factor	M.2 (2280)					
Performance (Up to.) <sup>2) 3) 4)</sup>	Sequential Read	6,400 MB/s	6,900 MB/s	7,000 MB/s	7,000 MB/s		
	Sequential Write	2,700 MB/s	5,000 MB/s	5,000 MB/s	5,100 MB/s		
	QD 1 Thread 1	Ran. Read	22K IOPS	22K IOPS	22K IOPS	22K IOPS	
		Ran. Write	60K IOPS	60K IOPS	60K IOPS	60K IOPS	
	QD 32 Thread 16	Ran. Read	500K IOPS	800K IOPS	1,000K IOPS	1,000K IOPS	
		Ran. Write	600K IOPS	1,000K IOPS	1,000K IOPS	1,000K IOPS	
Power Consumption (Up to) <sup>5)</sup>	Idle (ASPT on)		35mW				
	Active (Avg.)	Read	5.0 W	5.9 W	6.2 W	6.1W	
		Write	3.9 W	5.4 W	5.7 W	5.6W	
	L1.2 mode		5 mW				
Reliability	Temp.	Operating	0°C to 70°C (Measured by S.M.A.R.T. Temperature Proper airflow recommended)				
		Non-Operating	-40°C to 85°C				
	Humidity		5% to 95% non-condensing				
	Shock	Non-Operating	1,500G(Gravity), duration: 0.5ms, 3 axis				
	Vibration	Non-Operating	20~2,000Hz, 20G				
	MTBF		1.5 million hours				
Warranty <sup>6)</sup>	TBW	150TB	300TB	600TB	1,200TB		
	Period	5 years limited					
Supporting Features	TRIM (Required OS support), Garbage Collection, S.M.A.R.T						
Data Security	AES 256-bit Full Disk Encryption, TCG/Opal V2.0, Encrypted Drive (IEEE1667)						

- 1GB = 1,000,000,000 bytes by IDEMA. A certain portion of capacity may be used for system file and maintenance use, thus the actual available capacity may differ from the labeled capacity.
- 980 PRO is backward compatible with PCIe 3.0. Sequential performances (up to): 3500 MB/s for reads, 2700MB/s (250GB), 3400MB/s (500GB), 3450 MB/s (1TB), 3470MB/s (2TB) for writes. Random performances (up to): 560K (250GB), 690K IOPS (500GB/1TB), 680K IOPS (2TB) for reads, 620K (250/500GB), 660K IOPS (1TB), 630K IOPS (2TB) for writes.
- Sequential and random performance measurements are based on Iometer1.1.0. Performance may vary based on SSD's firmware version, system hardware & configuration. Test System: AMD Ryzen 9 3900X 12-Core Processor CPU@3.79GHz, DDR4 2666MHz 16GBx2, OS-Windows 10 Pro 64bit, Chipset-ASUS-X570-ROG CROSSHAIR VIII FORMULA v
- Sequential and random write performance was measured with Intelligent TurboWrite technology being activated. The sequential write performances for the portion of data exceeding Intelligent TurboWrite buffer size are (up to): 500 MB/s for 250GB, 1,000 MB/s for 500GB, 2,000 MB/s for 1/2TB, the random write performances over Intelligent TurboWrite buffer size (tested with QD 32 Thread 16) are (up to): 150K IOPS for 250GB, 300K IOPS for 500GB, 500K IOPS for 1/2TB. Performance may vary depending on SSD's firmware, system hardware & configuration and other factors.
- Power consumption is measured with Iometer1.1.0 version with AMD Ryzen 7 3700X 8 Core @3.6GHz, DDR4 8GBx2, OS-Windows 10 Pro 64bit, Chipset-GIGABYTE-X570-AORUS MASTER
- All documented endurance test results are in compliance with JESD218 Standards. Please visit [www.jedec.org](http://www.jedec.org) for detailed information on JESD218 Standards. TBW means Terabytes Written, Warranty provides coverage for the stated time period or the TBW, whichever comes first. Please refer to the detailed warranty statement here at <http://www.samsung.com/samsungssd>.

## PRODUCT LINEUP

Density	Model Name	Box Contents	Model Code
250GB*	MZ-V8P250	Samsung SSD 980 PRO 250GB Warranty Statement	MZ-V8P250BW MZ-V8P250B/AM
500GB*	MZ-V8P500	Samsung SSD 980 PRO 500GB Warranty Statement	MZ-V8P500BW MZ-V8P500B/AM
1TB (1,000GB*)	MZ-V8P1T0	Samsung SSD 980 PRO 1TB Warranty Statement	MZ-V8P1T0BW MZ-V8P1T0B/AM
2TB (2,000GB*)	MZ-V8P2T0	Samsung SSD 980 PRO 2TB Warranty Statement	MZ-V8P2T0BW MZ-V8P2T0B/AM

\* GB: 1GB = 1,000,000,000 bytes. The actual usable capacity may be less than the labeled capacity.

For more information, including but not limited to the warranty provided for this product, and to download the latest software & manuals, please visit [www.samsung.com/ssd](http://www.samsung.com/ssd) and [www.samsungssd.com](http://www.samsungssd.com).

## TEST CONFIGURATION

Below you will find a list of system configurations Samsung used to obtain the results reported in this Data Sheet. All performance data was measured with the SSD as a secondary drive

	Read/Write Performance	Power Consumption
Interface	PCIe Gen 4.0 x4	PCIe Gen 4.0 x4
OS	Windows 10 Pro 64bit	Windows 10 Pro 64bit
CPU	AMD Ryzen 9 3900X 12-Core CPU@3.79GHz	AMD Ryzen 7 3700X 8 Core @3.6GHz
Memory	DDR4 2666MHz 16GBx2	DDR4 8GBx2
Chipset	ASUS-X570-ROG CROSSHAIR VIII FORMULA v	GIGABYTE-X570-AORUS MASTER
Test Program	IOmeter 1.1.0	IOmeter 1.1.0

The test values in the review were obtained under the following BIOS settings.

- 1) BIOS version: 1201(2019/11/18)
- 2) Advanced/AMD CBS/CPU Common Options/Global C-state Control: Auto -> Disabled
- 3) Overclock
  - 3-1) Ai Overclock Tuner: Default -> Manual
  - 3-2) Memory Frequency: Auto -> DDR4-3600MHz
  - 3-3) Core Performance Boost: Auto -> Disabled
  - 3-4) CPU Core Ratio: Auto -> 43.75
  - 3-5) Precision Boost Overdrive/Precision Boost Overdrive: Auto -> Disabled
  - 3-6) DRAM Timing Control/DRAM CAS# Latency: Auto -> 17
    - DRAM Timing Control/Trcdrd : Auto -> 19
    - DRAM Timing Control/Trcdwr : Auto -> 19
    - DRAM Timing Control/DRAM RAS# PRE Time: Auto -> 18
    - DRAM Timing Control/DRAM RAS# ACT Time: Auto -> 36
  - 3-7) DRAM Voltage: Auto -> 1.35

## Revision History

Revision Number	Description	Revision Date
1.0	Initial Release	August, 2020
1.1	SKU information and test configuration is added	September, 2020
2.0	2TB Model added	January, 2021