

# **SPECIFICATION FOR APPROVAL**

Customer.	
Description : DC FAN	
Customer Part No.:	REV.:
Delta Model No. : PFB0412EN-E	REV.: 02
Sample Issue No. :	_
Sample Issue Date : JAN.09 2019	
PLEASE SEND ONE COPY OF THIS SPEC	
YOU SIGNED APPROVAL FOR PRODUCT	ION PRE-ARRANGINENT.
APPROVED BY:	
DATE :	

DELTA ELECTRONICS, INC.
TAOYUAN PLANT
252, SHANG YING ROAD, KUEI SAN INDUSTRIAL ZONE
TAOYUAN SHIEN, TAIWAN, R.O.C.

TEL:886-(0)3-3591968 FAX:886-(0)3-3591991

## \*\*\* SAMPLE HISTORY\*\*\*

CUSTOMER: STD

CUSTOMER P/N:

DELTA MODEL: PFB0412EN-E

	LTA MODEL: PFB041ZEN-E CHECKED IS					ISSUE	
REV.	DESCRIPTION	DRAWN	ME	EE	CE	APPROVED	DATE
00	ISSUE SPEC	王柏鈞 09/10'18	王柏鈞 09/10'18	杜紹章 09/10'18		陳浩明 09/10'18	09/10'18
01	1.UPDATE PQ CURVE & DATA Q :CHANGE FROM 37.25 TO 38.00CFM $(1.054 \text{ M}^3 / \text{MIN TO } 1.076 \text{ M}^3 / \text{MIN.})$ P: CHANGE FROM 7.44 TO 7.43 inchH <sub>2</sub> O $(188.976 \text{mmH}_2 \text{O TO } 188.722 \text{mmH}_2 \text{O})$ 2.NOISE FROM 70.0 TO 70.5, 74.0 TO 74.5dB 3.SPEED FROM 32000+/-10% TO 32500 +/-10%	王柏鈞 12/26'18	王柏鈞 12/26'18	杜紹章 12/26'18		洪文傑 沈柏輝 12/26'18	12/26'18
02	1.ADD SAFETY MARK 2.MODIFY TOLERANGE FROM 28.0 +/-0.3 TO 28.0 +0.1/-0.3	王柏鈞 01/08'19	王柏鈞 01/08'19	杜紹章 01/09'19		沈柏輝 洪文傑 01/09'19	01/09'19

Delta Electronics, Inc. No.252, Shanying Rd., Guishan Dist., Taoyuan City 333, Taiwan (R.O.C.)

# **STATEMENT OF DEVIATION**

TEL: 886-(0)3-3591968

FAX: 886-(0)3-3591991

■ NONE  □ DESCRIPTION:		

Delta Electronics, Inc.

No.252, Shanying Rd., Guishan Dist., Taoyuan City 333, Taiwan (R.O.C.)

## **Specification For Approval**

TEL: 886-(0)3-3591968

FAX: 886-(0)3-3591991

Customer :	STD		
Description :	DC FAI	N	
Customer P/	N :		rev.:
Delta model	no. : PFE	30412EN-E	Delta Safety Model No.: N/A
Sample revis	sion. :	02	Issue no.:
Sample issue	e date : .	AN.09 2019	Quantity :

#### 1. SCOPE:

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE DC BRUSHLESS AXIAL FLOW FAN.

#### 2. CHARACTERS:

ITEM	DESCRIPTION	
RATED VOLTAGE	12V	
OPERATION VOLTAGE	10.8 - 13.2 VDC	
START VOLTAGE	10.8 VDC	
INPUT CURRENT(AVG.) #	2.60 (MAX. 3.5) A CURRENT ON LABEL: 4.00A	
INPUT POWER(AVG.)	31.20 (MAX. 42.0) W	
SPEED	32500± 10% R.P.M.	
FAN FEEDBACK FUNCTION	THIS FAN IS OPEN LOOP DESIGN	
MAX. AIR FLOW (AT ZERO STATIC PRESSURE)	1.076(MIN. 0.968) M <sup>3</sup> /MIN. 38.00 (MIN.34.20) CFM	
MAX. AIR PRESSURE (AT ZERO AIRFLOW)	188.722(MIN. 152.865) mmH <sub>2</sub> O 7.43 (MIN. 6.018) inchH <sub>2</sub> O	
ACOUSTICAL NOISE (AVG.)	70.5 ( MAX. 74.5 ) dB-A	
INSULATION TYPE	UL: CLASS A	
INSULATION STRENGTH	10 MEG OHM MIN. AT 500 VDC (BETWEEN FRAME AND (+) TERMINAL)	
DIELECTRIC STRENGTH	5 mA MAX. AT 500 VAC 50/60 Hz ONE MINUTE, (BETWEEN FRAME AND (+) TERMINAL)	

#: THE MAX VALUE OF CONSUMING CURRENT DOES NOT REPRESENT THE PEAK VALUE, THE PEAK VALUE NEED MEASURE BY OSCILLOSCOPE.

(continued)

PAGE 1


PART NO:				
		·	·	

LIFE EXPECTANCE(L10) (AT LABEL VOLTAGE)	70,000 HOURS CONTINUOUS OPERATION AT 40 $^{\circ}$ C WITH 15 $\sim$ 65 %RH.
ROTATION	CLOCKWISE VIEW FROM NAME PLATE SIDE
LOCKED ROTOR PROTECTION	THE CURRENT WILL SHUT DOWN, WHEN ROTOR LOCKED AND FIXED. AUTO RESTART AFTER 10 SECONDS(MAX.)

#### NOTES:

DELTA MODEL: PFB0412EN-E

- 1. ALL READINGS ARE MEASURED AFTER STABLY WARMING UP THROUGH 10 MINUTES.
- 2. STANDARD AIR PROPERTY IS AIR AT (Td) 25°C TEMPERATURE, (RH) 65% RELATIVE HUMIDITY, AND (Pb) 760 mmHg BAROMETRIC PRESSURE.
- 3. THE VALUES WRITTEN IN PARENS, ( ), ARE LIMITED SPEC.
- 4. ACOUSTICAL NOISE MEASURING CONDITION:



NOISE IS MEASURED AT RATED VOLTAGE IN FREE AIR IN ANECHOIC CHAMBER WITH B & K SOUND LEVEL METER WITH MICROPHONE AT A DISTANCE OF ONE METER FROM THE FAN INTAKE.

DELTA MODEL: PFB0412EN-E

#### 3.MECHANICAL:

3-1. DIMENSIONS	SEE DIMENSIONS DRAWING
3-2. FRAME	PLASTIC UL: 94V-0
3-3. IMPELLER	PLASTIC UL: 94V-0
3-4. BEARING SYSTEM	TWO BALL BEARINGS
3-5. WEIGHT	51 GRAMS(REF.)

#### 4. ENVIRONMENTAL:

4-1. OPERATING TEMPERATURE	
4-2. STORAGE TEMPERATURE	
4-3. OPERATING HUMIDITY	5 TO 90 % RH
4-4. STORAGE HUMIDITY	5 TO 95 % RH

#### 5. PROTECTION:

- 5-1. LOCKED ROTOR PROTECTION
  IMPEDANCE OF MOTOR WINDING PROTECTS MOTOR FROM FIRE IN
  96 HOURS OF LOCKED ROTOR CONDITION AT THE RATED VOLTAGE.
- 5-2. POLARITY PROTECTION

  BE CAPABLE OF WITHSTANDING IF REVERSE CONNECTION FOR POSITIVEAND NEGATIVE LEADS.

#### 6. RE OZONE DEPLETING SUBSTANCES:


6-1. NO CONTAINING PBBs, PBBOs, CFCs, PBBEs, PBDPEs AND HCFCs.

#### 7. PRODUCTION LOCATION

7-1. PRODUCTS WILL BE PRODUCED IN CHINA OR THAILAND.

DELTA MODEL: PFB0412EN-E

### 8. P & Q CURVE:




\*TEST CONDITION: INPUT VOLTAGE-----OPERATION VOLTAGE TEMPERATURE-----ROOM TEMPERATURE HUMIDITY-----65%RH

DELTA MODEL: PFB0412EN-E

#### 9. DIMENSION DRAWING:

#### LABEL:



#### NOTES:

1.LEAD WIRE: UL 10368 AWG #26

BLACK WIRE ----(-)

RED WIRE -----(+)

BLUE WIRE ----(PWM)


YELLOW WIRE ----(F00)

2.THIS PRODUCT IS RoHS COMPLIANT.

DELTA MODEL: PFB0412EN-E

#### FREQUENCY GENERATOR (FG) SIGNAL:

1. OUTPUT CIRCUIT - OPEN COLLECTOR MODE:




GENERAL CONDITION: VFG is 3.3V, R is 8.2Kohm, and Cx is 4nF CAUTION:

THE LEAD WIRE OF FG SIGNAL CAN NOT TOUCH THE LEAD WIRE OF POSITIVE OR NEGATIVE.

#### 2. SPECIFICATION:

VFG= 13.2V MAX. Ic = 5mA MAX. VCE= 0.5V MAX.  $R \ge VFG /Ic$ 


#### 3. FREQUENCY GENERATOR WAVEFORM:



PAGE 6

#### **DELTA MODEL PFB0412EN-E**

#### 12.PWM CONTROL SIGNAL:




- \*THE PREFERRED OPERATING POINT FOR THE FAN IS 25KHZ.
- \*AT 100% DUTY CYCLE, THE ROTOR WILL SPIN AT MAXIMUM SPEED.
- \*AT 0% DUTY CYCLE, THE ROTOR WILL STOP.
- \*WITH CONTROL SIGNAL LEAD DISCONNECTED, THE FAN WILL SPIN AT MAXIMUM SPEED.
- \*AT 25°C, 25KHZ,12V, 10% DUTY CYCLE, THE FAN WILL BE ABLE TO START FROM A DEAD STOP.

### 13. SPEED VS PWM CONTROL SIGNAL:


(AT 25°C, RATED 12V & PWM SIGNAL AS FOLLOW)

DUTY CYCLE (%)	SPEED R.P.M.	CURRENT (A) TYP.
100	32500±10%	2.6
0	0	0.02

## \*PWM SIGNAL PWM FREQUENCY = 25KHz



#### 14. PWM CONTROL LEAD WIRE INPUT IMPEDANCE:



PAGE 7



# **Application Notice**

- 1. Delta will not guarantee the performance of the products if the application condition falls outside the parameters set forth in the specification.
- 2. A written request should be submitted to Delta prior to approval if deviation from this specification is required.
- 3. Please exercise caution when handling fans. Damage may be caused when pressure is applied to the impeller, if the fans are handled by the lead wires, or if the fan was hard-dropped to the production floor.
- 4. Except as pertains to some special designs, there is no guarantee that the products will be free from any such safety problems or failures as caused by the introduction of powder, droplets of water or encroachment of insect into the hub.
- 5. The above-mentioned conditions are representative of some unique examples and viewed as the first point of reference prior to all other information.
- 6. It is very important to establish the correct polarity before connecting the fan to the power source. Positive (+) and Negative (-). Damage may be caused to the fans if connection is with reverse polarity, if there is no foolproof method to protect against such error specifically mentioned in this spec.
- 7. Delta fans without special protection are not suitable where any corrosive fluids are introduced to their environment.
- 8. Please ensure all fans are stored according to the storage temperature limits specified. Do not store fans in a high humidity environment. We highly recommend performance testing is conducted before shipping, if the fans have been stored over 6 months.
- 9. Not all fans are provided with the Lock Rotor Protection feature. If you impair the rotation of the impeller for the fans that do not have this function, the performance of those fans will lead to failure.
- 10. Please be cautious when mounting the fan. Incorrect mounting of fans may cause excess resonance, vibration and subsequent noise.
- 11. It is important to consider safety when testing the fans. A suitable fan guard should be fitted to the fan to guard against any potential for personal injury.
- 12. Except where specifically stated, all tests are carried out at room (ambient) temperature and relative humidity conditions of 25°C, 65% RH. The test value is only for fan performance itself.
- 13. Be certain to connect an " $4.7\mu F$  or greater" capacitor to the fan externally when the application calls for using multiple fans in parallel, to avoid any unstable power.

Doc. No: FMBG-ES Form 001 Rev. 0001 Date: June 24, 2009