

Technical Data



ADHESIVE 120 MULTI-PURPOSE ADHESIVE



ADHESIVE 120 is a permanent, high-strength adhesive, specially formulated without chlorinated solvents.

APPLICATIONS

Ideal for a wide range of materials and substrates, including wood, metal, plastic, rubber, glass, paper, card and felt.

Suitable for applications such as fixing television cabinet veneers and speaker coverings.

Apply an even coating to both surfaces to be bonded from 9" – 12" (25 – 30 cm). Do not bond until the adhesive is tack-dry and bond the surfaces together using firm pressure.

N.B. May affect certain plastics. Always test a small, inconspicuous area before general use. To prevent blockages, invert the can after use and spray to clear the nozzle.

TECHNICAL DATA

Appearance	:	Clear, amber liquid
Odour	:	Acetone
SG @ 25 °C	:	0.81
Pressure @ 25°C	:	3 Bar
Discharge rate	:	1.3 g/sec
Polymer type	:	Styrene butadiene rubber
Open joint time	:	2 to 4 minutes
Bonding time	:	Approximately 60 minutes. Maximum adhesion in 12 - 24 hrs
Solubility	:	Soluble in some solvents, insoluble in water
Recommended solvents	:	Coldklene 110
Flammability	:	Classified as extremely flammable under the EC Classification, Labelling and Packaging regulation (CLP) 1272/2008
Flashpoint	:	Not applicable in sealed aerosol
Packaging	:	500 ml aerosol

STORAGE

The product may be stored at normal ambient temperatures and has a shelf life of not less than 36 months with correct storage. Aerosols should always be stored below 50°C, away from direct heat and naked flame.

HEALTH AND SAFETY

Health and Safety sheet available separately.

TECHNICAL SERVICE

CRC Industries UK Ltd provides a technical support service and maintains a constant programme of research and development. We are able to assist customers by specific product development to meet particular requirements.

MISREPRESENTATION ACT 1967

TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

CRC Industries UK Limited, Wylds Road, Bridgwater, Somerset, TA6 4DD

Tel: +44 (0) 1278 727200

Fax: +44 (0) 1278 425644

Web: www.ambersil.com

E-mail: sales.uk@crcind.com

Version 2

Updated: June 2015