




AMPMODU

TE Internal #: 1-6437006-8  
Ribbon Cable Connectors, Wire-to-Board, 26 Position, 5.08mm [.2in] Centerline, Vertical, Through Hole - Solder, Insulation Displacement Crimp (IDC)

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**  
Number of Positions: **26**  
Centerline (Pitch): **5.08 mm [ .2 in ]**  
PCB Mount Orientation: **Vertical**  
Termination Method to Printed Circuit Board: **Through Hole - Solder**

Features

Product Type Features

Ribbon Cable Connector Header Type	Shrouded
Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Plug
Connector & Contact Terminates To	Printed Circuit Board, Wire & Cable

Configuration Features

Number of Positions	26
PCB Mount Orientation	Vertical
Number of Rows	4

Contact Features

PCB Contact Termination Area Plating Material Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin



PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1 A

Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.71 mm[.028 in]
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)

Mechanical Attachment

Mating Retention	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Blue
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1437000-6

779-2100=HAND TOOL FRAME W/O D

Customers Also Bought



TE Part #T4140L12051-000

M12 Panel Mount PCB



TE Part #4525DO-DS5AI001DP

BOARD LEVEL PRESSURE STOCK LIST



TE Part #9-1879208-1

CPF 0402 56K 0.1% 25PPM 1K RL



TE Part #796640-4

4 POS 5.0 MM R/A PLUG,TRM BLK



TE Part #1622298-1

LR1 1% 10K



TE Part #8-1879507-9

CRGH0603 1% 22R 0.2W



TE Part #1488991-1

MCON, CONNECTOR HOUSING



TE Part #7-1452656-1

MCON, RECEPTACLE AND TAB



TE Part #5053092090  
[RNF-100-1/4-0-STK](#)



TE Part #2331394-1  
[DET SW4.7X3.5X2.25 GW VERT. NOH AG RL](#)

Documents

Product Drawings

[609-2603LF = PCB IDC P 26 ST .062](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-6437006-8\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-6437006-8\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-6437006-8\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ribbon Cable Interconnect Solutions](#)

English

Product Specifications

[micro-match crimp on snap in male on wire connector](#)

English

[Application Specification](#)

English

[Application Specification](#)

English

[micro match miniature connector system](#)

English