Honeywell

MICRO SWITCH Force Sensors

Force Sensor

FS Series

FEATURES

- Robust performance characteristics
- Precision force sensing
- Adaptable product design
- Highly reliable
- Signal conditioning available
- Electrically ratiometric output
- Extremely low deflection (30 microns typical @ Full Scale)
- Low repeatability errors (± 0.2% Span)
- Low linearity errors (± 0.5% Span)
- Low off-center loading errors
- Resolution to 1.0 gram force
- Fast response time
- Low power consumption
- High ESD resistance 10 KV

TYPICAL APPLICATIONS

- Medical infusion pumps
- Kidney dialysis machines
- Robotic end-effectors
- Variable tension control
- Load and compression sensing
- Contact sensing



The FS Series Force Sensor provides precise, reliable force sensing performance in a compact commercial grade package. The sensor features a proven sensing technology that utilizes a specialized piezoresistive micro-machined silicon sensing element. The low power, unamplified, non-compensated Wheatstone bridge circuit design provides inherently stable mV outputs over the 1,500 gram force range.

The force sensor operates on the principle that the resistance of silicon implanted piezoresistors will increase when the resistors flex under an applied force The sensor concentrates force from the application through the stainless steel plunger directly to the silicon sensing element. The amount of resistance changes in proportion to the amount of force being applied. This change in circuit resistance results in a corresponding mV output level.

The sensor package design incorporates a patented modular construction. The use of innovative elastomeric technology and engineered molded plastics results in load capacities of 5.5 Kg overforce. The stainless steel plunger provides excellent mechanical stability and is adaptable to a variety of applications. Various electrical interconnects can accept pre-wired connectors, printed circuit board mounting, and surface mounting. The unique sensor design also provides a variety of mounting options including mounting brackets, as well as application-specific mounting requirements.

MICRO SWITCH Force Sensors

Force Sensor

PERFORMANCE CHARACTERISTICS @ 10 ± 0.01 VDC, 25°C

Preliminary, based on limited test data

| Parameter | Min. | Тур. | Max. | Units |
|---|------|-----------|------|--------------|
| Excitation* | _ | 10 | 12 | VDC |
| Null shift, 25 to 0°, 25 to 50°C | _ | ± 0.5 | _ | mV |
| Null offset | -30 | 0 | +30 | mV |
| Linearity (BFSL) | _ | ± 0.5 | _ | % Span |
| Sensitivity | | 0.24 | | mV/grf |
| Sensitivity shift 25 to 0°, 25 to 50°C | | ± 5.0 | | % Span |
| Repeatability | _ | ± 0.2 | _ | % Span |
| Response time | _ | _ | 1.0 | msec |
| Input resistance | _ | 5.0 K | _ | ohms |
| Output resistance | _ | 5.0 K | _ | ohms |
| Plunger deflection | _ | 30 | | microns |
| Weight | _ | 2.0 | | grams |
| ESD (direct contact - terminals and plunger) | 10 | | | kVolts |
| | | | | (. - |

* Non-compensated force sensors, excited by constant current (1.5 mA) instead of voltage, exhibit partial temperature compensation of Span.

ENVIRONMENTAL SPECIFICATIONS

| Operating temperature | -40 to +85°C (-40 to +185°F) |
|-----------------------|---|
| Storage temperature | -55 to +105°C (-67 to +221°F) |
| Shock | Qualification tested to 150 g |
| Vibration | Qualification tested to 0 to 2 kHz, 20 g sine |
| | |

Note: All force related specifications are established using dead weight or compliant force.

ORDER GUIDE

| Catalog | Force Range | | | | Overforce grams |
|-----------|----------------|------|------|------|--------------------|
| Listing | (grams) | Min. | Тур. | Max. | Max. |
| FSG-15N1A | 1,500 | 290 | 360 | 430 | 5,500 |

MOUNTING


The sensor output characteristics do not change with respect to mounting orientation. Care should be taken not to obstruct the vent hole in the bottom of the sensor housing. Improper venting may result in unstable output.

Mounting bracket mounting torque: 2-5 in. lb. (,21-,56 Nm).

APPLYING FORCE

Evaluation of the sensor is to be performed using dead-weight or compliant force. Application of a rigid, immobile force will result in output drift (decrease) as elastomeric seals relax. Offcenter plunger loading has minimal effect on sensor performance and maintains operation within design specifications.

EXCITATION SCHEMATIC



FS SERIES CIRCUIT

- 1. Circled numbers refer to sensor terminals (pins). Pin 1 is designated with a notch. Pin 1 = Supply V_s (+) Pin 2 = Output, (+) Pin 3 = Ground, (-) Pin 4 = Output, (-)
- 2.The force sensor may be powered by voltage or current. Maximum supply voltage is not to exceed 12 volts. Maximum supply current is not to exceed 1.6 mA. Power is applied across Pin 1 and Pin 3.
- 3. The sensor output should be measured as a differential voltage across Pin 2 and Pin 4 $(V_o = V_2 - V_4)$. The output is ratiometric to the supply voltage. Shifts in supply voltage will cause shifts in output. Neither Pin 2 nor Pin 4 should be tied to ground or voltage supply.




MICRO SWITCH Force Sensors

Force Sensor


FS Series

MOUNTING DIMENSIONS (for reference only)



ACCESSORY

| Catalog Listing | Description | |
|-----------------|--------------------------|--|
| PC15132 | Plastic mounting bracket | |



MICRO SWITCH Force Sensors

Force Sensor



SALES AND SERVICE

Honeywell's MICRO SWITCH Division serves its customers through a worldwide network of sales offices and distributors. For application assistance, current specifications, pricing or name of the nearest Authorized Distributor, contact a nearby sales office. Or call:

1-800-537-6945 USA 1-416-293-8111 Canada 1-815-235-6847 International

INTERNET

http://www.sensing.honeywell.com info@micro.honeywell.com

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this printing. However, we assume no responsibility for its use.

While we provide application assistance, personally and through our literature, it is up to the customer to determine the suitability of the product in the application.



Sensing & Control Honeywell Inc. 11 West Spring Street Freeport, Illinois 61032

Printed with Soy Ink on 50% Recycled Paper

84-08028-0 796 Printed in USA

Helping You Control Your World