


- According to DIN EN 61810-1, DIN EN 61810-3 (Type A resp. Type B)
- With forcibly guided contacts
- Clearance and creepage distances  
contact-coil  $\geq 8$  mm,  
contact - contact  $\geq 5.5$  mm
- **Double and reinforced insulation between contact sets**
- Low rated power consumption
- High mechanical service life
- Compact size, small height
- Wash proof model as option

### Application

- Switchgear for safety technology
- Escalators and walkways
- Elevators for men and load
- Press controls
- Railway technology

### Approvals and Markings



### Technical Data

Relay type		OA/OW 5669	
<b>1.0 Relay coil</b>			
1.1 Nominal voltage	DC V	6, 12, 20, 24, 48, 60, 110 (other on request)	
1.2 Nominal consumption	W	0.7	
1.11 Voltage range	$U_N$	0.8 ... 1.6	
1.3 Holding power (at $0.5 \times U_N$ )	W	0.18	
<b>2.0 Contacts</b>			
2.1 Contact arrangement		1 NC / 1NO (type A) 2 changeover contacts (type B)	
2.2 Contact material		AgSnO <sub>2</sub> + 0.2 $\mu$ m Au; AgNi + 0.2 $\mu$ m Au, AgNi + 5 $\mu$ m Au	
2.3 Rated insulation voltage	AC V	250	
Switching voltage min./max.	V	AC/DC 10 / DC 250, AC 400 (AC/DC 2 V / 60 V) <sup>1)</sup>	
2.4 Limiting continuous current $I_{th}$	A	2 x 5 (see operating voltage limit curve)	
Switching current min./max.	A	10 mA <sup>3)</sup> / 8 (2 mA / 0.3 A) <sup>1)</sup>	
2.5 Switching power min./max.	VA	0,1 / 2000 (10 mVA / 12 VA) <sup>1)</sup>	
Switching power min./max.	W	0,1 <sup>3)</sup> / 200 (10 mW / 12 W) <sup>1)</sup> (see limit curve for arc-free operation)	
2.6 Switching capacity to IEC/EN 60947-5-1			
AC 15 <sup>4)</sup>	AC V/A	NO: 250 / 2	NC: 250 / 1
AC 15 <sup>5)</sup>	AC V/A	NO: 250 / 3	NC: 250 / 2
DC 13 <sup>4)</sup>	DC V/A	NO: 24 / 2	NC: 24 / 1
DC 13 <sup>4)</sup> at 0.1 Hz	DC V/A	NO: 24 / 4	NC: 24 / 4
to UL 508		R300	
2.7 Electrical life <sup>2)</sup>		at 1 s On, 1 s Off (see contacts service life)	
AC 230 V 6 A $\cos \varphi = 1$	switching cycles	$> 2 \times 10^5$ AgSnO <sub>2</sub>	$> 2 \times 10^5$ AgNi
2.8 Switching frequency max.	switching cycles / s	10	
2.9 Response time / Release time	ms	typically 15 / typically 5	
2.10 Contact force	cN	$\geq 10 / \geq 8$	
<b>3.0 Other</b>			
3.1 Mechanical life	switching cycles	$\geq 50 \times 10^6$	
3.2 Temperature range	°C	- 40 ... + 70 <sup>6)</sup> mounted without distance ( $I_{th} = 2 \times 5$ A)	
3.3 Degree of protection		Solder line proof RT II as option wash proof RT III	
3.4 Test procedure		A (group mounting)	
3.5 Vibration resistance		10 ... 200 Hz; NC 2 g; NO 10 g; IEC/EN 60068-2-6	
3.6 Climate resistance		40 / 070 / 04; A / B / D IEC/EN 60068-1	
3.7 Short circuit strength 1 kA / AC 250 V	AgSnO <sub>2</sub> AgNi	10 A gL IEC/EN 60947-5-1 6 A gL IEC/EN 60947-5-1	

<sup>1)</sup> Values for AgNi-contacts + 5  $\mu$ m Au

<sup>2)</sup> 10 A total current at  $t = 20^\circ\text{C}$  and coil voltage  $U_N$

<sup>3)</sup> Typical values for AgSnO<sub>2</sub> and AgNi

<sup>4)</sup> Values for AgNi-contacts

<sup>5)</sup> Values for AgSnO<sub>2</sub>-contacts

<sup>6)</sup> UL: + 60 °C

## Technical Data

3.8	Insulation acc. to IEC 60664-1, EN 50178		<b>double and reinforced insulation</b>
	Rated insulation voltage	AC V	250
	Pollution degree		2
	Overtoltage category		III
	Test voltage		
	Contact-coil (1 min)	AC kV eff.	≥ 4
	Contact-contact (1min)	AC kV eff.	≥ 4
	Open contact acc. to DIN EN 61810-1	AC kV eff.	1.5
	Transient voltage		
	Contact-coil (1.2 - 50 μs)	kV	≥ 6
	Clearance and creepage distances		
	Contact-coil	mm	≥ 8
	Contact-contact	mm	≥ 5.5
3.9	Weight	g	approx. 19
<b>4.0 Packing</b>			
4.1	on cardboard in slipcase	piece	56
4.2	in case package	piece	280
<b>5.0 Solder method</b>			
5.1	Solder method /-temperature /-duration	°C / s	Wave soldering / 260 / 5

## Design versions


U <sub>N</sub> DC V	Voltage range V	Resistance Ω (± 10%)	AgNi - contacts + 0.2 μm Au			AgNi - contacts + 5 μm Au		AgSnO <sub>2</sub> - contacts + 0.2 μm Au	
			OA5669.12	OA5669.16		OA5669.12	OA5669.16	OA5669.12	OA5669.16
6	4.8 ... 9.6	50	981	992	462	691	771	581	
12	9.6 ... 19.2	210	982	993	463	692	772	582	553
20	16.0 ... 32.0	580	987	998	468	697	777	587	558
24	19.2 ... 38.4	820	983	994	464	693	773	583	554
48	38.4 ... 76.8	3200	984	995	465	694	774	584	555
60	48.0 ... 96.0	5200	985	996	466	695	775	585	556
110	88.0 ... 176.0	16000	986	997	467	696	776	586	557
				1)	2)		1)		1)

1) = Pin configuration standard

2) = Pin configuration reverse

## Ordering example


O\_ 5669.\_ \_ / \_ \_ / 61\*)




\*) /61 cURus approval

## Note


For the use and processing of our PCB relays, please refer to the **application and processing instructions** at [www.dold.com](http://www.dold.com)




Operating voltage limit curve



Arc limit curve (at  $t_u = 20^\circ C$ )  
Contact material AgNi




Reduction factor for reactive loads





Electrical life for contact material AgNi


Drilling plan (solder side)





Pin configuration standard






OA5669.16  
OW5669.16






Pin configuration reverse



OA5669.16  
OW5669.16




OA5669.12  
OW5669.12



OA5669.20  
OW5669.20

Connection for basic grid dimensions 2.5 mm as well as 2.54 mm according to IEC/EN 60097 and IEC 60326 average

Drilling plan (solder side)



Connection for basic grid dimensions 2.5 mm as well as 2.54 mm according to IEC/EN 60097 and IEC 60326 average

Accessories

Relay socket ET 1415.021 for OA/OW 5669 Fixing clip ET 1415.025	Socket ET 1415.041	Socket ET 1415.044	Socket ET 1415.047
	<ul style="list-style-type: none"> <li>Socket for DIN-rail</li> <li>Incl. fixing clip</li> </ul>	<ul style="list-style-type: none"> <li>Socket for DIN-rail</li> <li>Incl. fixing clip</li> </ul>	
		<ul style="list-style-type: none"> <li>Incl. safe separation between coil and contacts according to DIN EN 60947-1, DIN EN 61140, DIN EN 60204</li> </ul>	
Article number: 0034769	Article number: 0055571	Article number: 0059274	Article number: 0059270
	Wire connection solid / stranded: 0.14 ... 2.5 mm <sup>2</sup> (14 - 20 AWG) Wire connection with sleeved end: 0.14 ... 1.5 mm <sup>2</sup> (14 - 25 AWG)	Wire connection solid / stranded: 0.14 ... 2.5 mm <sup>2</sup> (14 - 20 AWG) Wire connection with sleeved end: 0.14 ... 1.5 mm <sup>2</sup> (14 - 25 AWG)	Wire connection solid / stranded / sleeved end: 2 x (0.2 ... 1.5) mm <sup>2</sup> (16 - 25 AWG)
Fixing clip (wire): 0034770 Fixing clip (plastic): 0047726	<b>Function modules</b> <b>ET1415.913:</b> DC 24 V, with free-wheel diode and green LED Article number: 0056828 <b>ET1415.911:</b> DC 24 V, with free-wheel diode and red LED Article number: 0055909 <b>ET1415.924:</b> DC 60 V, with free-wheel diode and red LED Article number: 0062552 <b>ET1415.912:</b> AC/DC 24 V, with varistor and green LED Article number: 0055910		

