

## Section 1 - Chemical Product and Company Identification

Description : Polymer Lithium-ion Battery  
Details of the Supplier : Premier Farnell plc  
150 Armley Road  
Leeds  
LS12 2QQ  
+44 (0) 8701 202530  
Emergency Telephone : +44 1865 407333

## Section 2 - Hazards Identification

Emergency overview : This product is a battery. Intended use of the product should not result in exposure to the chemical substance. In case of rupture the below hazards exist.

### Classification according to GHS

Acute toxicity, oral (4)  
Skin corrosion/irritation (2)  
Serious eye damage/eye irritation (2A)  
Specific target organ toxicity, single exposure; Respiratory tract irritation (3)

### Label elements

Hazard pictogram(s):



Signal word : Warning

### Hazard statement(s):

H302 Harmful if swallowed  
H315 Causes skin irritation  
H319 Causes serious eye irritation  
H335 May cause respiratory irritation

### Precautionary statement(s):

#### Prevention:

P264 Wash skin and clothing thoroughly after handling.  
P270 Do not eat, drink or smoke when using this product.  
P280 Wear protective gloves, protective clothing, eye protection, face protection.  
P261 Avoid breathing dust, fume, gas, mist, vapours, spray.  
P271 Use only outdoors or in a well-ventilated area.

#### Response:

P301 + P312 IF SWALLOWED: Call a POISON CENTER if you feel unwell.  
P330 Rinse mouth.  
P302 + P352 IF ON SKIN: Wash with plenty water.  
P321 Specific treatment (See additional emergency instructions).  
P333 + P313 If skin irritation or rash occurs: Get medical advice.  
P362 + P364 Take off contaminated clothing and wash it before reuse.  
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P337 + P313 If eye irritation persists: Get medical advice.

# Safety Data Sheet

**multicomp** PRO

P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P312 Call a POISON CENTER, if you feel unwell.

## Storage

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

## Disposal:

P501 Send contents to approved waste treatment plants.

## Other hazards

Physical and chemical hazards : See Section 10

Human health hazards : See Section 11

Environmental hazards : See Section 12

## Section 3 - Composition/Information on Ingredients

Chemical characterization : Mixture

Chemical Composition	CAS No.	EC#	Weight(%)
cobalt lithium manganese nickel oxide	346417-97-8	620-032-4	32.0
Graphite	7782-42-5	231-955-3	20.6
Copper	7440-50-8	231-159-6	6.1
Aluminium	7429-90-5	231-072-3	2.8
Phosphate(1-), hexafluoro-, lithium	21324-40-3	244-334-7	12.6
Polyethylene	9002-88-4	618-339-3	2.3
Stainless steel	12597-68-1	603-108-1	10.3

## Section 4 - First Aid Measures

### Description of first aid measures

**General information No special measures required.**

### After eye contact

Flush eyes with plenty of water for several minutes while holding eyelids open. Get medical attention if irritation persists.

### After skin contact

Remove contaminated clothing and shoes. Immediately wash with water and soap and rinse thoroughly. Wash clothing and shoes before reuse. If irritation occurs, get medical attention.

### After inhalation

Remove victim to fresh area. Administer artificial respiration if breathing is difficult. Seek medical attention.

### After swallowing

Do not induce vomiting. Get medical attention.

Personal protective equipment for first-aid responders: No data available.

Most important symptoms/effects, acute and delayed: No data available.

Indication of immediate medical attention and special treatment needed: Treat symptomatically.

## Section 5 - Fire Fighting Measures

### Suitable extinguishing media:

Small Fire: Dry chemical, CO<sub>2</sub>, water spray or regular foam. Large Fire: Water spray, fog or regular foam. Move containers from fire area if you can do it without risk.

### Unsuitable extinguishing media:

No data available.

### Specific Hazards arising from the chemical:

Special hazards arising from the substance or mixture

Battery may burst and release hazardous decomposition products when exposed to a fire situation. Lithium ion batteries contain flammable electrolyte that may vent, ignite and produce sparks when subjected to high temperature (>150°C(302°F)), when damaged or abused (e.g. mechanical damage or electrical overcharging); may burn rapidly with flare-burning effect; may ignite other batteries in close proximity.

### Specific protective actions for fire-fighters:

Wear positive pressure self-contained breathing apparatus (SCBA). Structural firefighters' protective clothing will only provide limited protection.

## Section 6 -Accidental Release Measures

### Personal precautions:

As an immediate precautionary measure, isolate spill or leak area for at least 25 meters (75 feet) in all directions. Keep unauthorized personnel away. Stay upwind, uphill and/or upstream. Ventilate closed spaces before entering. Large Spill: Consider initial downwind evacuation for at least 100 meters (330 feet).

### Protective equipment:

No data available.

### Emergency procedures:

ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Do not touch or walk through spilled material. Absorb with earth, sand or other non-combustible material. Leaking batteries and contaminated absorbent material should be placed in metal containers.

### Environmental precautions:

Do not allow material to be released to the environment without proper governmental permits.

### Methods and materials for containment and cleaning up:

For all waste handling must refer to United Nations, National and Local Regulations for disposal.

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

## Section 7 - Handling and Storage

### Precautions for safe handling:

Avoid short circuiting the battery. Avoid mechanical damage of the battery. Do not open or disassemble. Batteries may explode or cause burns, if disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect polarity. Avoid all personal contact, including inhalation. Wear protective clothing when risk of exposure occurs. Use in a well-ventilated area. Prevent concentration in hollows and sumps.

### Conditions for safe storage, including any incompatibilities:

Store in a cool, dry, well-ventilated place. Keep away from heat, avoiding the long time of sunlight.

## Section 8 - Exposure Controls/Personal Protection

### Control parameters

CAS No.	ACGIH	NIOSH	OSHA
346417-97-8	N/A	N/A	N/A
7782-42-5	TLV-TWA 2mg/m <sup>3</sup>	REL-TWA 2.5mg/m <sup>3</sup>	PEL-TWA 15mppcf PEL-TWA 20mppcf
7440-50-8	TLV-TWA 0.2mg/m <sup>3</sup> TLV-TWA 1mg/m <sup>3</sup>	REL-TWA 1 mg/m <sup>3</sup> REL-TWA0.1mg/m <sup>3</sup>	PEL-TWA 0.1 mg/m <sup>3</sup> PEL-TWA 1 mg/m <sup>3</sup>
7429-90-5	TLV-TWA 1mg/m <sup>3</sup>	REL-TWA 2mg/m <sup>3</sup> REL-TWA 5mg/m <sup>3</sup> REL-TWA 10mg/m <sup>3</sup>	PEL-TWA 5mg/m <sup>3</sup> PEL-TWA 15mg/m <sup>3</sup>
21324-40-3	N/A	N/A	N/A
9002-88-4	N/A	N/A	N/A
12597-68-1	N/A	N/A	N/A

### Appropriate engineering controls:

The usual precautionary measures for handling chemicals should be followed.

Keep away from foodstuffs, beverages and feed.

Remove all soiled and contaminated clothing immediately.

Wash hands before breaks and at the end of work.

### Personal Protective Equipment:

- Respiratory protection : Wear suitable protective mask. For a large large number of battery leakages, wear chemical protective clothing, including self-contained breathing apparatus.
- Hand Protection : Wear appropriate protective gloves to reduce skin contact.
- Eye Protection : Wear safety goggles or eye protection combined with respiratory protection.
- Skin and Body Protection : Working environment required, wear suitable protective clothing to minimize contact with skin. The type of protective equipment must be according to the concentration and the content of certain hazardous substances in the workplace.

## Section 9 - Physical and Chemical Properties

### Information on basic physical and chemical properties

- Colour : Black
- Physical State : Prismatic
- Odour : Not available.
- Odour threshold : Not available.
- pH : Not available.
- Melting point/freezing point : Not available.
- Initial boiling point and boiling range : Not available.
- Flash Point : Not available.
- Evaporation rate : Not available.
- Flammability (solid, gas) : Not available.
- Explosion Limits (vol% in air) : Not available.
- Vapour pressure, kPa at 20°C : Not available.
- Vapor density : Not available.

# Safety Data Sheet

multicomp<sup>PRO</sup>

Density/Relative density (water= 1) : Not available.  
Solubility(ies) : Not available.  
Partition coefficient: n-octanol/water : Not available.  
Auto-ignition temperature : Not available.  
Decomposition temperature : Not available.  
Viscosity : Not available.  
Other information  
Voltage : 3.7V  
Electric capacity : 13200mAh  
Electric Energy : 48.84Wh

## Section 10 - Stability and Reactivity

Reactivity : No data available.  
Chemical stability : Stable.  
Possibility of hazardous reactions : No data available.  
Conditions to Avoid : Flames, sparks, and other sources of ignition, incompatible materials.  
Incompatible materials : Oxidizing agents, acid base.  
Hazardous decomposition products: Carbon monoxide, carbon dioxide, lithium oxide fumes.

## Section 11 - Toxicological Information

### Acute Toxicity:

CAS No.	LC50/LD50
346417-97-8	No data available.
7782-42-5	No data available.
7440-50-8	No data available.
7429-90-5	No data available.
21324-40-3	No data available.
9002-88-4	No data available.
12597-68-1	No data available.

Skin corrosion/irritation : No data available.  
Serious eye damage/irritation : No data available.  
Respiratory or Skin sensitization : No data available.  
Germ Cell mutagenicity : No data available.  
Carcinogenicity : No data available.  
Reproductive toxicity : No data available.  
Specific target organ toxicity-Single exposure : No data available.  
Specific target organ toxicity-Repeated exposure : No data available.  
Aspiration hazard : No data available.  
Information on the likely routes of exposure : No data available.  
Eye : No data available.  
Skin : No data available.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

multicomp<sup>PRO</sup>

Ingestion : No data available.  
Inhalation : No data available.

## Section 12 - Ecological Information

Ecological Toxicity : No data available.  
Persistence and degradability : No data available.  
Bioaccumulative Potential : No data available.  
Mobility in Soil : No data available.  
Other adverse effects : No data available.

## Section 13 - Disposal Considerations

### Disposal methods:

Recommendation : Consult state, local or national regulations to ensure proper disposal.

### Uncleaned packaging

Recommendation : Disposal must be made according to official regulations.

## Section 14- Transport Information

### UN Number

IATA UN3481  
IMDG UN3481

### UN Proper shipping name

IATA Lithium ion batteries packed with equipment  
IMDG LITHIUM ION BATTERIES PACKED WITH EQUIPMENT

### Transport hazard class(es)

IATA 9  
IMDG 9

### Packing group

IATA N/A  
IMDG N/A

### Packaging Sign

IATA N/A  
IMDG N/A

### Environmental hazards

Marine pollutant No

**Special precautions for user** No information available.

Transport information : The Polymer Lithium-ion Battery XDS has passed the test UN38.3, according to the report ID: MOIUMG8T17403721 .

According to the Packing Instruction 966 section II of IATA DGR 61 51 Edition for transportation.

According to the special provision 188 of IMDG (39-18), the goods are not subject to other provision of this code.

Note: Batteries weight in the package< 5kg. (By air, Batteries packed with equipment)

Transport Fashion : By air, by sea.

## Section 15- Regulatory Information

Safety, health and environmental regulations/legislation specific for the substance or mixture

CAS No.	TSCA	IECSC	DSL/NDSL	EINECS/ ELINCS/ NLP
346417-97-8	Listed	Listed	Listed DSL	Listed
7782-42-5	Listed	Listed	Listed DSL	Listed
7440-50-8	Listed	Listed	Listed DSL	Listed
7429-90-5	Listed	Listed	Listed DSL	Listed
21324-40-3	Listed	Listed	Listed DSL	Listed
9002-88-4	Listed	Listed	Listed DSL	Listed
12597-68-1	Listed	Listed	Listed DSL	Listed

## Section 16 - Other Information

Modification record:

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Other Information:

CAS: (Chemical Abstracts Service);

EC: (European Commission);

ACGIH: (American Conference of Governmental Industrial Hygienists);

NIOSH: (US National Institute for Occupational Safety and Health);

OSHA: (US Occupational Safety and Health);

TLV: (Threshold Limit Value)

TWA: (Time Weighted Average);

STEL: (Short Term Exposure Limit);

PEL: (Permissible Exposure Level);

REL: (Recommended Exposure Limit);

PC-STEL: (Permissible concentration-short time exposure limit);

PC-TWA: (Permissible concentration-time weighted average);

LC50: (Lethal concentration, 50 percent kill);

LD50: (Lethal dose, 50 percent kill);

IARC: (International Agency for Research on Cancer);

EC50: (Median effective concentration);

BCF: (Bioconcentration Factor);

BOD: (Biochemical oxygen demand);

NOEC: (No observed effect concentration);

NTP: (US National Toxicology Program);

RTECS: (Registry of Toxic Effects of Chemical Substances);

IATA: (International Air Transport Association);

IMDG: (International Maritime Dangerous Goods);

TOG: (Recommendations on the TRANSPORT OF DANGEROUS GOODS Model Regulations);

Newark.com/multicomp-pro

Farnell.com/multicomp-pro

Element14.com/multicomp-pro

# Safety Data Sheet

**multicomp** PRO

TOC: (Total Organic Carbon);  
TSCA: (Toxic Substances Control Act of USA);  
DSL: (the Domestic Substances List of Canada);  
NDSL: (the Non-domestic Substances List of Canada)

<b>Part Number</b>
MP720417

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO