


PRODUCT DATA SHEET

Part Number: **G987**

| Type | Size | Rating | Description |
|--------------|------|----------|------------------------|
| Incandescent | G11 | 12V 2.2W | G-3½ Edison screw lamp |



Dimensions in millimetres

| TEST VOLTS | CURRENT (mA) | | | LIGHT OUTPUT (Lm) | | | LIFE Hours |
|------------|--------------|------|------|-------------------|------|------|------------|
| | Min. | Nom. | Max. | Min. | Nom. | Max. | |
| 13.5 | 177 | 196 | 216 | 12.8 | 16.0 | 19.2 | 3,000 |

Notes:

- 1 **Base Type** E10/13 Nickel plated brass
- 2 **Filament Shape** C-2V
- 3 **Lamp Marking** CML 12V 2.2W
- 4 **Bead Colour** White or clear
- 5 **Environmental** RoHS & REACH SVHC compliant