


Part Number: **G198**

Type	Size	Rating	Description
Incandescent	G11	6V 60mA	G-3½ Edison screw lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
6	54	60	66	0.75	1.00	1.25	10,000

Notes:

- 1 **Base Type** E10/13 Nickel plated brass
- 2 **Filament Shape** C-2R
- 3 **Lamp Marking** CML 6V 60mA
- 4 **Bead Colour** White or clear
- 5 **Environmental** RoHS & REACH SVHC compliant