


PRODUCT DATA SHEET

Part Number: 00000248

Type	Size	Rating	Description
Incandescent	G18	24V 5W	Automotive Bayonet Lamp



Dimensions in millimetres

TEST VOLTS	Power (W)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
24		5			-		

Notes:

- 1 **Filament Shape** C-2F
- 2 **Base type** BA15s Nickel plated
- 3 **Lamp Marking** 24V R5W with E marking
- 4 **Environmental** RoHS & REACH SVHC compliant