


Part Number: 1199

Type	Size	Rating	Description
Incandescent	T5	28V 40mA	T-1½ Wedge Base Lamp



Dimensions in mm.

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	36	40	44	2.9	3.8	4.7	10,000

Notes:

- 1 Base Type W2x4.6d to BE EN 60061-1
- 2 Filament Shape C-2F
- 3 Bead Colour White or clear
- 4 Marking CML 28V 40mA
- 5 Environmental RoHS & REACH SVHC compliant