


PRODUCT DATA SHEET

Part Number: W1309

Type	Size	Rating	Description
Incandescent	T10	12V 2.2W	T-3¼ Miniature Edison Screw Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
13.5	177	196	216	12.8	16.0	19.2	3,000

Notes:

- 1 **Base Type** E10/13 Nickel plated brass
- 2 **Filament Shape** C-2V
- 3 **Bead colour** White or clear
- 4 **Lamp Marking** CML 12V 2.2W
- 5 **Environmental** RoHS & REACH SVHC compliant