



Part Number: 513

Type	Size	Rating	Description
Incandescent	T10	24V 2W	T-3¼ Wedge Base Lamp



TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	86	95	104	9.8	13.0	16.2	5,000

Notes:

- 1 **Base** W2.1x9.5d
- 2 **Filament Shape** C-2F
- 3 **Marking** CML 513
24V 2W
- 4 **Bead Colour** White or clear
- 5 **Environmental** RoHS and REACH SVHC compliant