


# PRODUCT DATA SHEET

Part Number: 00H01205

Type	Size	Rating	Description
Halogen	T10	12V 5W	Bayonet Halogen Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
12	374	416	457	67	75	94	100

Notes:

- 1 **Base Type** BA9s/13 Nickel plated brass
- 2 **Filament Shape** C-2R
- 3 **Lamp Marking** Halogen 12V 5W
- 4 **Environmental** RoHS & REACH SVHC compliant