

# UHF Male Crimp

**multicomp**PRO


**RoHS  
Compliant**



## Specifications

Connector Type	: UHF Coaxial
Voltage Rating	: 500 Vrms @ Sea Level
Frequency Range	: 0 ~ 300 MHz
Connector Body Style	: Straight Plug
Coaxial Termination	: Crimp
Contact Material	: Brass
Contact Plating	: Silver Plated Contacts
Frequency Max	: 300MHz
Connector Mounting	: Cable Mount
Coaxial Cable Types	: RG58, RG58A, RG58C, RG141, LMR-200

## Diagram



Item	Description	Material	Finish	Qty.
1	Body	Brass	Silver	1
2	Contact			
3	Dielectric	PTFE	None	
4	Shell	Brass	Silver	
5	Ferrule			

## Part Number Table

Description	Part Number
UHF Male Crimp	1534

Dimensions : Inches (Millimetres)

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp**PRO