Contact Grease CG53A

Product Code: CG53A

PRODUCT DESCRIPTION

The CG series of Contact Lubricants is an extension of the extremely popular 2X range. The main advantages of these products is reduced contact resistance (even on extremely heavy usage), improved plastics compatibility and improved mechanical lubrication. The use of CG53A on switches and connectors guarantees a very low and stable contact resistance over the long lifetimes required by the automotive industry.

The exceptionally low wear characteristics make this lubricant ideal for high quality audio and automotive applications, providing a very smooth, high quality feel operation. The plastics compatibility of this grease is very good although it is always advisable to test prior to full scale production.

TYPICAL PROPERTIES

Colour: Drop Point (ISO 2176): 1/4 Cone Penetration (ASTM 217):20°C -40°C Worked Penetration (ASTM 217): 20°C Consistency (DIN 51818): Fließdruck (DIN 51805): -40°C Oil Separation (DIN 51817/IP121: Copper Corrosion (DIN 51759/IP112): Silver Corrosion (DIN 51759): Infra Red (DIN 51820): Base Oil:

Pour Point: Density (base oil @ 20°C): Thickener: **Temperature Range**

Cream 200°C 65 to 75 50 to 60 (Typical) 295 to 340(Typical 320) NLGI 1-2 350 mBar <8% Class 1a (4h @ 150°C)

No colour change (3h 100°C) According to standard Complex mixture of synthetic polyols containing antioxidants, anti-corrosives and metal protection additives. -41°C 0.995 g/ml (ASTM D1298)

Complex inorganic thickener -35°C to +130°C



Copyright Electrolube 2003

All information is given in good faith but without warranty. **Properties are** given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.



ELECTROLUBE, A division of H K Wentworth, Kingsbury Park, Midland Road, Swadlincote, Derbyshire, DE11 0AN Tel: +44(0) 1283-222111 Fax: +44(0) 1283-550177 www.electrolube.com ISO 9002 Registered Firm. Certificate No. FM 32082

<u>Contact Grease CG53A</u> – Page 2

PACKAGING

35ml Syringe 1 Kg Bulk 5 Kg Bulk 12.5 Kg Bulk 25 Kg Bulk ORDER CODE

CG53A35SL CG53A01K CG53A05K CG53A12.5K CG53A25K

The 12.5 and 25 kg grease drums have parallel sides for use with "follower plate" dispensing equipment for automated manufacturing lines. The drum dimensions are:

12.5 kg254mm (inside diameter) x 330mm (height)25 kg305mm (inside diameter) x 406mm (height)

NATO stock no: 6850-99-186-8879

Copyright Electrolube 2003 All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer. who must satisfy themselves as to the suitability of the product.

TECHNICAL DATA

SHEET



ELECTROLUBE, A division of H K Wentworth, Kingsbury Park, Midland Road, Swadlincote, Derbyshire, DE11 0AN Tel: +44(0) 1283-222111 Fax: +44(0) 1283-550177 www.electrolube.com ISO 9002 Registered Firm. Certificate No. FM 32082