LQH3NPH330MME#

Note: This datasheet may be out of date.

Please download the latest datasheet of LQH3NPH330MME# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=LQH3NPH330MME%23

### "#" indicates a package specification code.























< List of part numbers with package codes > LQH3NPH330MMEL



## Appearance & Shape





## References

Packaging	Specifications	Standard Packing Quantity
L	180Embossed Tape	2000

Mass (typ.)	
1 piece	0.051g



## **Notices**

When rated current is applied to the products, inductance will be within ±30% of initial inductance value range. Keep the temperature (ambient temperature plus self-generation of heat) under 125°C. When rated current is applied to the products, the self-temperature rise shall be limited to 40°C max. (ambient temperature 85°C). When rated current is applied to the products, the selftemperature rise shall be limited to 20°C max. (ambient temperature 85°C to 105°C).

1 of 2

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



Note: This datasheet may be out of date.

Please download the latest datasheet of LQH3NPH330MME# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=LQH3NPH330MME%23

"#" indicates a package specification code.

# LQH3NPH330MME#



## **Specifications**

L size	3.0±0.2mm
W size	3.0±0.2mm
T size	1.4±0.1mm
Size code inch (mm)	1212 (3030)
Inductance	33µH±20%
Inductance Test Frequency	1MHz
Rated current (Isat) (Based on Inductance change)	440mA
Rated current (Itemp) (Based on Temperature rise)	760mA(Ambient temp.85°C) 460mA(Ambient temp.105°C)
Max. of DC resistance	0.66Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C
Class of magnetic shield	Magnetic Resin
Self resonance frequency (min.)	8MHz
Operating Temperature Range(Self-temperature rise is not included)	-40°C to 105°C
DC Resistance Intermediate Values	0.55Ω±20%
Series	LQH3NPH_ME

2 of 2

### Attentior

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

