

# H51A405NN00580100000 ✓ ACTIVE

TE Internal #: HSA405N00580100000

Standard Circular Connectors, Cable-to-Cable, Power, Signal & Data, Cable Mount (Free-Hanging), Electrodeposited Nickel, Zinc Alloy, PA66+PA6

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Sealable: **No**

Circuit Application: **Power, Signal & Data**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Shell Plating Material: **Electrodeposited Nickel**

## Features

### Product Type Features

Product Type	Connector
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

### Electrical Characteristics

Operating Voltage	30 VAC, 630 VAC
-------------------	-----------------

### Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PA66+PA6

### Mechanical Attachment

Mating Retention Type	Speedtec (Triple Start Threaded)
-----------------------	----------------------------------



Connector Mounting Type

Cable Mount (Free-Hanging)

**Housing Features**

Circular Connector Shell Size

23

**Dimensions**

Cable Diameter Range

9.5 – 14.5 mm [.37 – .57 in]

**Usage Conditions**

Operating Temperature Range

-20 – 130 °C [-4 – 266 °F]

**Operation/Application**

Durability Rating

500 Cycles

Circuit Application

Power, Signal & Data

Shielded

Yes

**Industry Standards**

UL Flammability Rating

UL 94V-0

Approved Standards

UL

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUN 2020 (209)  
 Candidate List Declared Against: JAN 2020 (205)  
 SVHC > Threshold:  
 Pb (3.5% in Component)

**Article Safe Usage Statements:**  
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability


Not reviewed for solder process capability

**Product Compliance Disclaimer**


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



TE Part # C0-0265-000-000  
LOCATOR FOR CRIMPING TOOL




TE Part # C0-0324-000-000  
DIGITAL CRIMPING TOOL



TE Part # C0-0138-000-000  
POSITIONING INSERT FOR 2 MM CONTACTS



TE Part # C0-0201-000-000  
CRIMPING TOOL MID-SIZE



TE Part # HEC402N00000200000  
723 HTEC RECEPTACLE, SPEEDTEC

## Customers Also Bought



TE Part #1623723-2  
Wirewound Resistor: Axial Mount, 17 Watt



TE Part #1-2329389-1  
PB OFF/ON FC YLW M1 TERM WHI LED IP68 50



TE Part #2176406-9  
3560 2R2 1%



TE Part #YDTS20F13-98JAC001  
D38999: Square Flange, 13-98 insert



TE Part #2-456406-5  
WIRE CRIMPER .090



TE Part #2170773-1  
CAGE ASSY, QSFP28 1X1, SPRING, LP



TE Part #2825213-1  
VAL-U-LOK SKT HCS SN 22-18 LP



TE Part #YDTS26F13-04SEV001  
PLUG ASSY



## Documents

### CAD Files

[3D PDF](#)

[3D](#)

**Customer View Model**

[ENG\\_CVM\\_CVM\\_HSA405N00580100000\\_A.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_HSA405N00580100000\\_A.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_HSA405N00580100000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[Y6-F970-000-000](#)

English

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English