

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15BD152SZ1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=BLM15BD152SZ1%23

### "#" indicates a package specification code.

# BLM15BD152SZ1D




< List of part numbers with package codes > BLM15BD152SZ1J BLM15BD152SZ1B BLM15BD152SZ1D



### Appearance & Shape





0.5±0.05

Electrode



## Applications

Automotive Usage

Infotainment



### Packaging Information

Packaging	Specifications	Standard Packing Quantity
J	330mm Paper Tape	50000
В	Bulk(Bag)	1000
D	180mm Paper Tape	10000



### Features

The chip ferrite beads BLM series is designed to work nearly as a resistor at noise frequencies, which greatly reduces the possibility of resonance and leaves signal wave forms undistorted. BLM series is effective in circuits without stable ground lines because BLM series does not need a connection to ground.

BLM\_B series can minimize attenuation of the signal waveform due to its sharp impedance characteristics. Various impedances are available to match signal frequency.

The nickel barrier structure of the external electrodes provides excellent solder heat resistance.

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Product Search Data Sheet

# BLM15BD152SZ1D

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15BD152SZ1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=BLM15BD152SZ1%23

### "#" indicates a package specification code.



## Specifications

Shape	SMD
Size Code (in inch)	0402
Length	1.0mm
Length Tolerance	±0.05mm
Width	0.5mm
Width Tolerance	±0.05mm
Thickness	0.5mm
Thickness Tolerance	±0.05mm
Operating Temperature Range	-55℃ to 125℃
Mass(typ.)	0.001g
Number of Circuit	1
Rated Current (at 85°C)	190mA
Rated Current (at 125°C)	190mA
DC Resistance(max.)	1Ω
Impedance (at 100MHz)	1500Ω
Impedance (at 100MHz) Tolerance	±25%
Size Code (in mm)	1005

2 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Product Search Data Sheet


# BLM15BD152SZ1D


**Product Data** 

Note: This datasheet may be out of date. Please download the latest datasheet of BLM15BD152SZ1# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=BLM15BD152SZ1%23

"#" indicates a package specification code.





Impedance-Frequency Characteristics

**Equivalent Circuit** 

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



3 of 3