

Productname : Foam 2-in-1  
 Ref.Nr.: BDS002535\_3\_20200323 (EN)

Creationdate : 23.03.20 Version : 1.0  
 Replaces:

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

Foam 2-in-1  
 Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Sealants and Isolation

### 1.3. Details of the supplier of the safety data sheet

CRC Industries Europe BV  
 Touwslagerstraat 1  
 9240 Zele  
 Belgium  
 Tel.: +32(0)52/45.60.11  
 Fax.: +32(0)52/45.00.34  
 E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Smedsgatan 3-5 LT4, PL62, 08101 LOJO	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

### 1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1  
 Extremely flammable aerosol.  
 Pressurised container: May burst if heated.

Classification is based on test data.



**Productname :** Foam 2-in-1  
**Ref.Nr.:** BDS002535\_3\_20200323 (EN)

**Creationdate :** 23.03.20 Version : 1.0  
**Replaces:**

**Health:** Not classified  
 Classification based on calculation method.  
**Environment:** Not classified  
 Classification based on calculation method.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

#### Hazard pictogram(s):



<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P301/310 : IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
tris (2-chloro-1-methylethyl)-phosphate	01-2119486772-26	1244733-77-4	911-815-4	10-20	Acute Tox. 4	H302	
isobutane	01-2119485395-27	75-28-5	200-857-2	10-20	Flam. Gas 1, Press. Gas	H220,H280	K
dimethyl ether	01-2119472128-37	115-10-6	204-065-8	5-10	Flam. Gas 1, Press. Gas	H220,H280	A
propane	01-2119486944-21	74-98-6	200-827-9	5-10	Flam. Gas 1, Press. Gas	H220,H280	B
1-Propanol, 2,2-dimethyl-, tribromo deriv.	01-2119935159-32	36483-57-5	253-057-0	1-5	Eye Irrit. 2, Aquatic Chronic 3	H319,H412	

**Productname :** Foam 2-in-1  
**Ref.Nr.:** BDS002535\_3\_20200323 (EN)

**Creationdate :** 23.03.20 Version : 1.0  
**Replaces:**

Castor oil		8001-79-4	232-293-8	1-5	Skin Irrit. 2, Eye Irrit. 2	H315,H319	G
<b>Explanation notes</b>							
A : substance with Community workplace exposure limit							
B : substance with national established workplace exposure limit							
G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006							
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)							

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	May cause irritation. Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products



**Productname :** Foam 2-in-1  
**Ref.Nr.:** BDS002535\_3\_20200323 (EN)

**Creationdate :** 23.03.20 Version : 1.0  
**Replaces:**

CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep in a cool, dry, well ventilated place  
Keep out of reach of children.



**Productname :** Foam 2-in-1  
**Ref.Nr.:** BDS002535\_3\_20200323 (EN)

**Creationdate :** 23.03.20 Version : 1.0  
**Replaces:**

### 7.3. Specific end use(s)

Sealants and Isolation

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
dimethyl ether	115-10-6	TWA	1000 ppm
<b>National established exposure limits, United Kingdom</b>			
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
<b>National established exposure limits, Ireland</b>			
dimethyl ether	115-10-6	TWA	1000 ppm
		STEL	-
propane	74-98-6	TWA	1000 ppm

### 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). Use a reusable glove with a minimum breakthrough time of 30 minutes. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.
<b>Consumer exposure protection:</b>	Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. IF exposed or if you feel unwell: Call a POISON CENTER or doctor/physician.

## SECTION 9: Physical and chemical properties



**Productname :** Foam 2-in-1  
**Ref.Nr.:** BDS002535\_3\_20200323 (EN)

**Creationdate :** 23.03.20 Version : 1.0  
**Replaces:**

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

**Appearance : physical state :** Liquid under pressure.  
**colour :** White.  
**odour :** Characteristic odor.  
**pH :** Not applicable.  
**Boiling point/range :** Not available.  
**Flash point :** - 97 °C  
**Evaporation rate :** Not available.  
**Explosion limits : upper limit :** 8.5 %  
**lower limit :** 1.8 %  
**Vapour pressure :** 300 kPa (@ 20°C).  
**Relative density :** 1.00 g/cm<sup>3</sup> (@ 20°C).  
**Solubility in water :** Insoluble in water  
**Auto-ignition :** 235 °C  
**Viscosity :** Not available.

### 9.2. Other information

**VOC = volatile organic compounds** 245 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO<sub>2</sub>



Productname : Foam 2-in-1  
 Ref.Nr.: BDS002535\_3\_20200323 (EN)

Creationdate : 23.03.20 Version : 1.0  
 Replaces:

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	based on available data the classification criteria are not met
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

### Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis Repeated exposure may cause skin dryness or cracking.
Eye contact :	May cause irritation.

### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
dimethyl ether	115-10-6	LC50 inhal.rat	309 mg/l
tris (2-chloro-1-methylethyl)-phosphate	1244733-77-4	LD50 oral rat	> 2000 mg/kg
		LC50 inhal.rat	7 mg/l

## SECTION 12: Ecological information

### 12.1. Toxicity

Not classified

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
dimethyl ether	115-10-6	IC50 algae	154.9 mg/l
		LC50 fish	4.1 mg/l
		EC50 daphnia	4.4 mg/l
tris (2-chloro-1-methylethyl)-phosphate	1244733-77-4	LC50 fish	51 mg/l



Productname : Foam 2-in-1  
Ref.Nr.: BDS002535\_3\_20200323 (EN)

Creationdate : 23.03.20 Version : 1.0  
Replaces:

		EC50 daphnia	131 mg/l
--	--	--------------	----------

### 12.2. Persistence and degradability

No experimental data available

### 12.3. Bioaccumulative potential

No experimental data available

### 12.4. Mobility in soil

Insoluble in water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No experimental data available  
GWP (global warming potential): 1

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Contaminated packaging : 160504  
National regulations : Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

### 14.4. Packing group





Productname : Foam 2-in-1  
Ref.Nr.: BDS002535\_3\_20200323 (EN)  
Creationdate : 23.03.20 Version : 1.0  
Replaces:

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

#### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H280 : Contains gas under pressure; may explode if heated.  
H302 : Harmful if swallowed.  
H315 : Causes skin irritation.  
H319 : Causes serious eye irritation.  
H412 : Harmful to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistent bioaccumulative toxic  
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.



---

<b>Productname :</b>	Foam 2-in-1	<b>Creationdate :</b>	23.03.20 Version : 1.0
<b>Ref.Nr.:</b>	BDS002535_3_20200323 (EN)	<b>Replaces:</b>	

---

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

