



Electronic Component Part No.:	JANTX1N5618
Electronic Req. Qty:	1
Engineering PDF:	 TJSE20701_C.pdf
Dimension Image:	
Bussing or Circuit Configuration:	Contact factory for drawing.

TJSE20702

Series:	Series 1
Type:	Electronic Splice
Number of Contacts:	4
Number of Contacts per Size:	4
Contact Size:	20
Contact Type:	Socket
Contact Part Number:	M39029/1-101
QPL:	M81714/24
Mil-Spec:	Non-Active Mil-Spec
Temperature (Degrees C):	-65 to 200
Insulation Resistance:	5000 Megahms at 25 degrees Celcius
Dielectric Withstanding Voltage:	1500 VRMS at Sea Level 200 VRMS at 100,000 Ft.
Amperage:	Available upon request
Vibration and Shock:	MIL-T-81714 Paragraph 3.5.5 and 3.5.8
Body:	Polyetherimide per ASTM-D5205
Grommet:	Silicone Blend Elastomer per A-A-59588

Contact Retainers:	Stainless Steel
Socket/Pin Contacts:	Copper Alloy, Hard Gold Plated in Accordance with MIL-G-45204
With/Without:	With
Color:	Blue
Electronic Component Type:	Diode
Electronic Component Part No.:	1N5618
Electronic Req. Qty:	2
Engineering PDF:	
Dimension Image:	
Bussing or Circuit Configuration:	Contact factory for drawing.

TJSE20703

Series:	Series 1
Type:	Electronic Splice
Number of Contacts:	4
Number of Contacts per Size:	4
Contact Size:	20
Contact Type:	Socket
Contact Part Number:	M39029/1-101
QPL:	M81714/24
Mil-Spec:	Non-Active Mil-Spec
Temperature (Degrees C):	-65 to 200
Insulation Resistance:	5000 Megahms at 25 degrees Celcius