

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN)

Creationdate : 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

BRIGHT COLD GALVANISE
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture




Classification according to Regulation (EC) No 1272/2008

Physical:	Aerosols, category 1 Extremely flammable aerosol. Pressurised container: May burst if heated.
Classification is based on test data.	
Health:	Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness. Specific Target Organ Toxicity - Repeated Exposure Category 2 May cause damage to organs through prolonged or repeated exposure .
Classification based on calculation method.	
Environment:	Hazardous to the aquatic environment, chronic category 3 Harmful to aquatic life with long lasting effects.
Classification based on calculation method.	

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN) **Creationdate :** 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier:	Contains: Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic
Hazard pictogram(s):	  
Signal word:	Danger
Hazard statement(s):	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H336 : May cause drowsiness or dizziness. H373 : May cause damage to organs through prolonged or repeated exposure H412 : Harmful to aquatic life with long lasting effects.
Precautionary statement(s):	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P261-1 : Avoid breathing vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
Supplemental Hazard information:	None

Dir. 2004/42/EC on the limitation of emissions of volatile organic compounds (VOC) of organic solvents in certain paints and varnishes and vehicle refinishing products

Cat.II B(e) VOC max 840 g/L < 675 g/L

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
dimethyl ether	01-2119472128-37	115-10-6	204-065-8	50-75	Flam. Gas 1, Press. Gas	H220,H280	A
ethyl acetate	01-	141-78-	205-	5-10	Flam. Liq. 2, Eye Irrit. 2	H225, H319, H336	B

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN)

Creationdate : 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

	2119475103-46	6	500-4		STOT SE 3		
Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic	01-2119458049-33	64742-82-1	(919-446-0)	5-10	Flam. Liq. 3, Asp. Tox. 1, STOT SE 3, STOT RE 1, Aquatic Chronic 2	H226,H304,H336,H372,H411	B,Q
n-butyl acetate	01-2119485493-29	123-86-4	204-658-1	1-5	Flam. Liq. 3, STOT SE 3	H226,H336	
Hydrocarbons, C9, aromatics	01-2119455851-35	-	(918-668-5)	<2.5	Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H226,H335,H336,H304,H411	Q
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119463258-33	-	(919-857-5)	<2.5	Flam. Liq. 3, Asp. Tox. 1, STOT SE 3	H226,H304,H336	B,Q
zinc oxide	01-2119463881-32	1314-13-2	215-222-5	<1.1	Aquatic Acute 1, Aquatic Chronic 1	H400,H410	B
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	01-2119539477-28	96-29-7	202-496-6	<0.1	Carc. 2, Acute Tox. 4, Eye Dam. 1, Skin Sens. 1	H351,H312,H318,H317	B

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures**4.1. Description of first aid measures**

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water If eye irritation persists: Get medical advice/attention.
Contact with skin :	Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor



3 / 11

CRC Industries UK Limited
 Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
 Somerset, TA6 4DD
 Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN)

Creationdate : 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent
Do not use water jet extinguishing media, due to the risk of spreading fire.

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.
In case of insufficient ventilation, wear suitable respiratory equipment.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed



Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN) **Creationdate :** 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 In case of insufficient ventilation, wear suitable respiratory equipment.
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Anti Corrosion Products

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
dimethyl ether	115-10-6	TWA	1000 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm
National established exposure limits, United Kingdom			
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm
National established exposure limits, Ireland			
dimethyl ether	115-10-6	TWA	1000 ppm
		STEL	-
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	96-29-7	TWA	3 ppm
		STEL	10 ppm

8.2. Exposure controls

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN) **Creationdate :** 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. It is good practice to wear gloves and to provide adequate ventilation whenever using the product. In all cases handle and use the product in accordance with good industrial hygiene practices.
Inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
hands and skin :	Depending on amount and duration of use and the risk of contact with the product the gloves manufacturer can assist you in the selection of the right glove material and breakthrough time.
Recommended gloves:	Nitrile
eyes :	Wear safety eyewear according to EN 166.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state :	DME propelled liquid.
colour :	Grey.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	Not available.
Flash point :	< 0 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	0.969 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not applicable.

9.2. Other information

VOC = volatile organic compounds < 675 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose



6 / 11

CRC Industries UK Limited
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN)

Creationdate : 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	May cause damage to organs through prolonged or repeated exposure .
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis Repeated exposure may cause skin dryness or cracking.
Eye contact :	May cause irritation.

Toxicological data :



7 / 11

CRC Industries UK Limited

Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
Somerset, TA6 4DD

Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN)

Creationdate : 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

Hazardous ingredient	CAS-nr.	method	
dimethyl ether	115-10-6	LC50 inhal.rat	309 mg/l
n-butyl acetate	123-86-4	LD50 oral rat	10760 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 1400 mg/kg
zinc oxide	1314-13-2	LD50 oral rat	7950 mg/kg
		LC50 inhal.rat	> 5.7 mg/l
ethyl acetate	141-78-6	LD50 oral rat	5620 mg/kg
		LC50 inhal.rat	30 mg/l
		LD50 derm.rabit	> 20000 mg/kg
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	96-29-7	LD50 oral rat	2326 mg/kg
		LD50 derm.rabit	1000 mg/kg
Hydrocarbons, C9, aromatics	-	LD50 oral rat	3492 mg/kg
		LC50 inhal.rat	> 6.393 mg/l
		LD50 derm.rabit	> 3160 mg/kg
Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic	64742-82-1	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 10 mg/l
		LD50 derm.rabit	> 4 mg/kg
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	>5000 mg/kg
		LC50 inhal.rat	4951 mg/m3
		LD50 derm.rabit	>5000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 3
 Harmful to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
dimethyl ether	115-10-6	IC50 algae	154.9 mg/l
		LC50 fish	4.1 mg/l
		EC50 daphnia	4.4 mg/l
n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l
zinc oxide	1314-13-2	IC50 algae	0.136 mg/l
		LC50 fish	0.169 mg/l
		EC50 daphnia	1.7 mg/l
ethyl acetate	141-78-6	IC50 algae	5600 mg/l
		LC50 fish	230 mg/l
		EC50 daphnia	610 mg/l
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	96-29-7	IC50 algae	11.8 mg/l
		LC50 fish	> 100 mg/l
		EC50 daphnia	201 mg/l

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN)

Creationdate : 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic	64742-82-1	IC50 algae	4.6-10 mg/l
		LC50 fish	10-30 mg/l
		EC50 daphnia	10-22 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available
GWP (global warming potential): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group



9 / 11

CRC Industries UK Limited
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : BRIGHT COLD GALVANISE
Ref.Nr.: BDS002118_3_20200609 (EN) **Creationdate :** 09.06.20 Version : 4.0
Replaces: BDS002118_20200504

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
Regulation (EC) No 1907/2006 (REACH)
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H312 : Harmful in contact with skin.
H317 : May cause an allergic skin reaction.
H318 : Causes serious eye damage.
H319 : Causes serious eye irritation.
H335 : May cause respiratory irritation.
H336 : May cause drowsiness or dizziness.
H351 : Suspected of causing cancer .
H372 : Causes damage to organs through prolonged or repeated exposure.

Productname :	BRIGHT COLD GALVANISE	Creationdate :	09.06.20 Version : 4.0
Ref.Nr.:	BDS002118_3_20200609 (EN)	Replaces:	BDS002118_20200504

H400 : Very toxic to aquatic life.
H410 : Very toxic to aquatic life with long lasting effects.
H411 : Toxic to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE : Labelling according to Regulation (EC) No 1272/2008
acronyms and synonyms: TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistant bioaccumulative toxic
vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.