



1001 Trout Brook Crossing  
 Rocky Hill, CT 06067-3910  
 Telephone: (860) 571-5100  
 FAX: (860) 571-5465

# Product Description Sheet

## Superflex® Clear RTV Silicone Adhesive Sealant

Maintenance, Repair & Operations, September 2002

### PRODUCT DESCRIPTION

Loctite® Superflex® Clear RTV Silicone Adhesive Sealant is a single component, room temperature vulcanizing compound designed to provide an excellent adhesive sealant for mechanical assemblies. This material cures on exposure to moisture in the air to form a tough, flexible, silicone rubber seal. The product resists aging, weathering and thermal cycling without hardening, shrinking or cracking. Designed for superior bonding and sealing properties to most surfaces (not recommended for concrete). Formulated to withstand extreme temperature cycling, UV light and ozone.

### PRODUCT BENEFITS

- Non-slumping
- Superior adhesion and flexibility
- Seals out moisture and contaminants
- Excellent adhesive properties
- Fills large cracks and seams
- Non-flammable, Non-toxic

### TYPICAL APPLICATIONS

- Electrical insulation
- Protects leads from mechanical shock
- Bonds trim
- Seals ductwork, vents, flues, doors, windows

### DIRECTIONS FOR USE

1. Clean and dry surfaces. Remove all oil and grease.
2. Apply product to surface. For bonding applications, apply to one surface only and join surfaces immediately. When using pressurized cans and cartridges, apply silicone by pushing the product in the direction of use (forward) into the surface.
3. Wipe away excess material immediately.

### For Cleanup

1. Allow excess material to extend beyond the extension nozzle or aerosol tip to cure, sealing and protecting the remaining product from moisture. For reuse, simply remove the cured product from the tip.
2. Remove uncured product from parts and hand-tools with a dry cloth. If skinned over, break film with a dry cloth to remove as much as possible.
3. Clean hands with a dry cloth or hand cleaner.

### PROPERTIES OF UNCURED MATERIAL

	Typical Value
Chemical Type	Acetoxy silicone rubber
Appearance	Clear paste
Odor	Acetic acid
Specific Gravity	1.01
Viscosity	Thixotropic Paste
Flash Point °C (°F)	>93 (>200)

### TYPICAL CURING PERFORMANCE

Loctite® Superflex® Clear RTV Silicone Adhesive Sealant cures on exposure to moisture in the air. The product dries tack free in two hours and fully cures in 24 hours. Cure times will vary with temperature, humidity and gap.

### GENERAL INFORMATION

**This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.**

**For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).**

### Ordering Information

Part Number	Container Size
59530	80 ml Tube
59575	300 ml Cartridge
30562	7.25 oz. Net Wt. Pressurized Can

### Storage

Products shall be ideally stored in a cool, dry location in unopened containers at a temperature between 8° to 28°C (46° to 82°F) unless otherwise labeled. Optimal storage is at the lower half of this temperature range. To prevent contamination of unused product, do not return any material to its original container. For specific shelf-life information, contact your local Technical Service Center.

### Note

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Loctite Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Loctite Corporation's products. Loctite Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Loctite Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

NOT FOR PRODUCT SPECIFICATIONS.

THE TECHNICAL DATA CONTAINED HEREIN ARE INTENDED AS REFERENCE ONLY.

PLEASE CONTACT LOCTITE CORPORATION QUALITY DEPARTMENT FOR ASSISTANCE AND RECOMMENDATIONS ON SPECIFICATIONS FOR THIS PRODUCT.

ROCKY HILL, CT FAX: +1 (860)-571-5473

DUBLIN, IRELAND FAX: +353-(1)-451 - 9959