

Features

2 Pole relay range


44.52 - 2 Pole 6 A (5 mm pin pitch)

44.62 - 2 Pole 10 A (5 mm pin pitch)

PCB mount - direct or via PCB socket

35 mm rail mount - via screw and screwless sockets

- High physical separation between adjacent contacts
- DC coils (Standard or sensitive)
- Cadmium Free contact materials
- 8 mm, 6 kV (1.2/50 μ s) isolation, coil-contacts
- UL Listing (certain relay/socket combinations)
- Flux proof: RT II
- 95 series sockets
- Coil EMC suppression
- Timer accessories 86 series



FOR UL HORSEPOWER AND PILOT DUTY RATINGS
SEE "General technical information" page V

Contact specification

Contact configuration	2 CO (DPDT)	2 CO (DPDT)
Rated current/Maximum peak current A	6/10	10/20
Rated voltage/Maximum switching voltage V AC	250/400	250/400
Rated load AC1 VA	1,500	2,500
Rated load AC15 (230 V AC) VA	250	500
Single phase motor rating (230 V AC) kW	0.185	0.37
Breaking capacity DC1: 30/110/220 V A	6/0.3/0.13	10/0.3/0.13
Minimum switching load mW (V/mA)	300 (5/5)	300 (5/5)
Standard contact material	AgNi	AgNi

Coil specification

Nominal voltage (U_N) V AC (50/60 Hz)	—	—
V DC	6 - 9 - 12 - 14 - 24 - 28 - 48 - 60 - 110 - 125	—
Rated power AC/DC/sens. DC VA (50 Hz)/W/W	—/0.65/0.5	—/0.65/0.5
Operating range AC	—	—
DC/sens. DC	(0.73...1.5) U_N /(0.73...1.7) U_N	(0.73...1.5) U_N /(0.8...1.7) U_N
Holding voltage AC/DC	—/0.4 U_N	—/0.4 U_N
Must drop-out voltage AC/DC	—/0.1 U_N	—/0.1 U_N

Technical data



Mechanical life AC/DC cycles	—/20 · 10 ⁶	—/20 · 10 ⁶
Electrical life at rated load AC1 cycles	150 · 10 ³	100 · 10 ³
Operate/release time ms	8/5 - (12/5 sensitive)	8/5 - (12/5 sensitive)
Insulation between coil and contacts (1.2/50 μ s) kV	6 (8 mm)	6 (8 mm)
Dielectric strength between open contacts V AC	1,000	1,000
Ambient temperature range °C	−40...+85	−40...+85
Environmental protection	RT II	RT II

Approvals (according to type)

44.52




- 2 Pole, 6 A
- 5 mm contact pin pitch
- PCB or 95 series sockets





Copper side view

44.62



- 2 Pole, 10 A
- 5 mm contact pin pitch
- PCB or 95 series sockets



Copper side view

Ordering information

Example: 44 series PCB relay, 2 CO (DPDT) 10 A contacts, 24 V DC coil.

4	4	.	6	.	2	.	9	.	0	2	4	.	0	A	0	B	0	C	0	D	0
----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------

Series ————

Type ————
 5 = PCB - 5 mm pinning
 6 = PCB - 5 mm pinning

No. of poles ————
 2 = 2 pole for
 44.52, 6 A
 44.62, 10 A

Coil version ————
 7 = Sensitive DC
 9 = DC

Coil voltage ————
 See coil specifications

A: Contact material
 0 = Standard AgNi
 4 = AgSnO₂
 for 44.62 only
 5 = AgNi + Au (5 µm)
 for 44.52 only

B: Contact circuit
 0 = CO (DPDT)

D: Special versions
 0 = Flux proof (RT II)

C: Options
 0 = None

Selecting features and options: only combinations in the same row are possible.
 Preferred selections for best availability are shown in **bold**.


Type	Coil version	A	B	C	D
44.52	DC - sens. DC	0 - 5	0	0	0
44.62	DC - sens. DC	0 - 4	0	0	0

Technical data


Insulation according to EN 61810-1:2004					
Nominal voltage of supply system	V AC	230/400			
Rated insulation voltage	V AC	250		400	
Pollution degree		3		2	
Insulation between coil and contact set					
Type of Insulation		Reinforced (8 mm)			
Overvoltage category		III			
Rated impulse voltage	kV (1.2/50 µs)	6			
Dielectric strength	V AC	4,000			
Insulation between adjacent contacts					
Type of insulation		Basic			
Overvoltage category		III			
Rated impulse voltage	kV (1.2/50 µs)	4			
Dielectric strength	V AC	2,500			
Insulation between open contacts					
Type of disconnection		Micro-disconnection			
Dielectric strength	V AC/kV (1.2/50 µs)	1,000/1.5			
Conducted disturbance immunity					
Burst (5...50)ns, 5 kHz, on A1 - A2		EN 61000-4-4		level 4 (4 kV)	
Surge (1.2/50 µs) on A1 - A2 (differential mode)		EN 61000-4-5		level 3 (2 kV)	
Other data					
Bounce time: NO/NC	ms	4/4			
Vibration resistance (5...55)Hz: NO/NC	g	15/12			
Shock resistance	g	16			
Power lost to the environment	without contact current	W	0.6		
	with rated current	W	1.2 (44.52)	2.7 (44.62)	
Recommended distance between relays mounted on PCB	mm	≥ 5			

Contact specification

F 44 - Electrical life (AC) v contact current



H 44 - Maximum DC1 breaking capacity



- When switching a resistive load (DC1) having voltage and current values under the curve, an electrical life of $\geq 100 \cdot 10^3$ can be expected.
- In the case of DC13 loads, the connection of a diode in parallel with the load will permit a similar electrical life as for a DC1 load.
Note: the release time for the load will be increased.

Coil specifications

DC coil data - 0.65 W standard


Nominal voltage U_N	Coil code	Operating range		Resistance	Rated coil consumption I at U_N
V		U_{min} V	U_{max} V	R Ω	mA
6	9.006	4.4	9	55	109
9	9.009	6.6	13.5	125	72
12	9.012	8.8	18	220	55
14	9.014	10.2	21	300	47
24	9.024	17.5	36	900	27
28	9.028	20.5	42	1,200	23
48	9.048	35	72	3,500	14
60	9.060	43.8	90	5,500	11
110	9.110	80.3	165	18,000	6.2
125	9.125	91.2	187.5	23,500	5.3

DC coil data - 0.5 W sensitive

Nominal voltage U_N	Coil code	Operating range		Resistance	Rated coil consumption I at U_N
V		U_{min}^* V	U_{max} V	R Ω	mA
6	7.006	4.4	10.2	75	80
9	7.009	6.6	15.3	160	56
12	7.012	8.8	20.4	300	40
14	7.014	10.2	23.8	400	35
24	7.024	17.5	40.8	1,200	20
28	7.028	20.5	47.6	1,600	17.5
48	7.048	35	81.6	4,800	10
60	7.060	43.8	102	7,200	8.4
110	7.110	80.3	187	23,500	4.7
125	7.125	100	218.7	32,000	3.9


* $U_{min} = 0.8 U_N$ for 44.62

R 44 - DC coil operating range v ambient temperature
Standard coil



- 1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.


R 44 - DC coil operating range v ambient temperature
Sensitive coil



- 1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.



Module	Socket	Relay	Description	Mounting	Accessories
	95.05	44.52 44.62	Screw terminal (Box clamp) socket - Top terminals - Contacts - Bottom terminals - Coil	Panel or 35 mm rail (EN 50022) mount	- Coil indication and EMC suppression modules - Jumper link - Timer modules - Plastic retaining and release clip



Module	Socket	Relay	Description	Mounting	Accessories
	95.85.3	44.52 44.62	Screw terminal (Box clamp) socket	Panel or 35 mm rail (EN 50022) mount	- Coil indication and EMC suppression modules - Plastic retaining and release clip



Module	Socket	Relay	Description	Mounting	Accessories
	95.95.3	44.52 44.62	Screw terminal (Box clamp) socket - Top terminals - Contacts - Bottom terminals - Coil	Panel or 35 mm rail (EN 50022) mount	- Coil indication and EMC suppression modules - Plastic retaining and release clip




Module	Socket	Relay	Description	Mounting	Accessories
	95.55	44.52 44.62	Screwless terminal socket - For fast cable connections - Top terminals - Contacts - Bottom terminals - Coil	Panel or 35 mm rail (EN 50022) mount	- Coil indication and EMC suppression modules - Timer modules - Plastic retaining and release clip




Module	Socket	Relay	Description	Mounting	Accessories
	95.55.3	44.52 44.62	Screwless terminal socket - For fast cable connections - Top terminals - Contacts - Bottom terminals - Coil	Panel or 35 mm rail (EN 50022) mount	- Coil indication and EMC suppression modules - Plastic retaining and release clip



Module	Socket	Relay	Description	Mounting	Accessories
—	95.15.2	44.52 44.62	PCB socket	PCB mounting	- Metal retaining clip





95.05

Approvals
(according to type):



cULUS Certain relay/socket combinations




095.01




060.72

Screw terminal (Box clamp) socket panel or 35 mm rail mount		95.05 (blue)	95.05.0 (black)
For relay type		44.52, 44.62	
Accessories			
Metal retaining clip		095.71	
Plastic retaining and release clip (supplied with socket - packaging code SPA)		095.01	095.01.0
8-way jumper link		095.18	095.18.0
Identification tag		095.00.4	
Modules (see table below)		99.02	
Timer modules (see table below)		86.30	
Sheet of marker tags for retaining and release clip 095.01 plastic, 72 tags, 6x12 mm		060.72	
Technical data			
Rated values		10 A - 250 V	
Dielectric strength		6 kV (1.2/50 µs) between coil and contacts	
Protection category		IP 20	
Ambient temperature		°C -40...+70	
⊕ Screw torque	Nm	0.5	
Wire strip length	mm	8	
Max. wire size for 95.05 socket		solid wire	stranded wire
	mm²	1x6 / 2x2.5	1x4 / 2x2.5
	AWG	1x10 / 2x14	1x12 / 2x14



095.18

8-way jumper link for 95.05 socket	095.18 (blue)	095.18.0 (black)
Rated values	10 A - 250 V	



86.30

86 series timer modules	86.30.0.024.0000
(12...24)V AC/DC; Bi-function: AI, DI; (0.05s...100h)	

Approvals
(according to type):




99.02

Approvals
(according to type):



99.02 coil indication and EMC suppression modules for 95.05 socket		
Diode (+A1, standard polarity)	(6...220)V DC	99.02.3.000.00
LED	(6...24)V DC/AC	99.02.0.024.59
LED	(28...60)V DC/AC	99.02.0.060.59
LED	(110...240)V DC/AC	99.02.0.230.59
LED + Diode (+A1, standard polarity)	(6...24)V DC	99.02.9.024.99
LED + Diode (+A1, standard polarity)	(28...60)V DC	99.02.9.060.99
LED + Diode (+A1, standard polarity)	(110...220)V DC	99.02.9.220.99
LED + Varistor	(6...24)V DC/AC	99.02.0.024.98
LED + Varistor	(28...60)V DC/AC	99.02.0.060.98
LED + Varistor	(110...240)V DC/AC	99.02.0.230.98
RC circuit	(6...24)V DC/AC	99.02.0.024.09
RC circuit	(28...60)V DC/AC	99.02.0.060.09
RC circuit	(110...240)V DC/AC	99.02.0.230.09
Residual current by-pass	(110...240)V AC	99.02.8.230.07

DC Modules with
non-standard polarity
(+A2) on request.



95.85.3

Approvals
(according to type):




095.91.3



060.72

Screw terminal (Box clamp) socket panel or 35 mm rail mount	95.85.3 (blue)	95.85.30 (black)	
For relay type	44.52, 44.62		
Accessories			
Metal retaining clip	095.71		
Plastic retaining and release clip (supplied with socket - packaging code SPA)	095.91.3	095.91.30	
8-way jumper link	095.08	095.08.0	
Identification tag	095.80.3		
Modules (see table below)	99.80		
Sheet of marker tags for retaining and release clip 095.91.3 plastic, 72 tags, 6x12 mm	060.72		
Technical data			
Rated values	10 A - 250 V		
Dielectric strength	6 kV (1.2/50 μs) between coil and contacts		
Protection category	IP 20		
Ambient temperature	°C −40...+70		
⊕ Screw torque	Nm	0.5	
Wire strip length	mm	7	
Max. wire size for 95.85.3 sockets	solid wire	stranded wire	
	mm²	1x6 / 2x2.5	1x4 / 2x2.5
	AWG	1x10 / 2x14	1x12 / 2x14



095.08

8-way jumper link for 95.85.3 socket	095.08 (blue)	095.08.0 (black)
Rated values	10 A - 250 V	



99.80


Approvals
(according to type):



* Modules in Black
housing are
available on request.

Green LED is standard.
Red LED available
on request.

99.80 coil indication and EMC suppression modules for 95.85.3 socket		
		Blue*
Diode (+A1, standard polarity)	(6...220)V DC	99.80.3.000.00
LED	(6...24)V DC/AC	99.80.0.024.59
LED	(28...60)V DC/AC	99.80.0.060.59
LED	(110...240)V DC/AC	99.80.0.230.59
LED + Diode (+A1, standard polarity)	(6...24)V DC	99.80.9.024.99
LED + Diode (+A1, standard polarity)	(28...60)V DC	99.80.9.060.99
LED + Diode (+A1, standard polarity)	(110...220)V DC	99.80.9.220.99
LED + Varistor	(6...24)V DC/AC	99.80.0.024.98
LED + Varistor	(28...60)V DC/AC	99.80.0.060.98
LED + Varistor	(110...240)V DC/AC	99.80.0.230.98
RC circuit	(6...24)V DC/AC	99.80.0.024.09
RC circuit	(28...60)V DC/AC	99.80.0.060.09
RC circuit	(110...240)V DC/AC	99.80.0.230.09
Residual current by-pass	(110...240)V AC	99.80.8.230.07



95.95.3

Approvals
(according to type):




095.91.3




060.72

Screw terminal (Box clamp) socket panel or 35 mm rail mount		95.95.3 (blue)	95.95.30 (black)
For relay type		44.52, 44.62	
Accessories			
Metal retaining clip			095.71
Plastic retaining and release clip (supplied with socket - packaging code SPA)		095.91.3	095.91.30
8-way jumper link		095.08	095.08.0
Identification tag			095.80.3
Modules (see table below)			99.80
Sheet of marker tags for retaining and release clip 095.91.3 plastic, 72 tags, 6x12 mm			060.72
Technical data			
Rated values		10 A - 250 V	
Dielectric strength		6 kV (1.2/50 µs) between coil and contacts	
Protection category		IP 20	
Ambient temperature		°C -40...+70	
Screw torque		Nm	0.5
Wire strip length		mm	8
Max. wire size for 95.95.3 sockets		solid wire	stranded wire
		m ²	1x6 / 2x2.5
		AWG	1x10 / 2x14



095.08

8-way jumper link for 95.95.3 socket		095.08 (blue)	095.08.0 (black)
Rated values		10 A - 250 V	



99.80


Approvals
(according to type):



* Modules in Black
housing are
available on request.

Green LED is standard.
Red LED available
on request.


99.80 coil indication and EMC suppression modules for 95.95.3 socket			Blue*
Diode (+A1, standard polarity)	(6...220)V DC	99.80.3.000.00	
LED	(6...24)V DC/AC	99.80.0.024.59	
LED	(28...60)V DC/AC	99.80.0.060.59	
LED	(110...240)V DC/AC	99.80.0.230.59	
LED + Diode (+A1, standard polarity)	(6...24)V DC	99.80.9.024.99	
LED + Diode (+A1, standard polarity)	(28...60)V DC	99.80.9.060.99	
LED + Diode (+A1, standard polarity)	(110...220)V DC	99.80.9.220.99	
LED + Varistor	(6...24)V DC/AC	99.80.0.024.98	
LED + Varistor	(28...60)V DC/AC	99.80.0.060.98	
LED + Varistor	(110...240)V DC/AC	99.80.0.230.98	
RC circuit	(6...24)V DC/AC	99.80.0.024.09	
RC circuit	(28...60)V DC/AC	99.80.0.060.09	
RC circuit	(110...240)V DC/AC	99.80.0.230.09	
Residual current by-pass	(110...240)V AC	99.80.8.230.07	



Approvals
(according to type):



Screwless terminal socket panel or 35 mm rail mount		95.55 (blue)	95.55.0 (black)
For relay type		44.52, 44.62	
Accessories			
Metal retaining clip			095.71
Plastic retaining and release clip (supplied with socket - packaging code SPA)			095.91.3
Identification tag			095.00.4
Modules (see table below)			99.02
Timer modules (see table below)			86.30
Sheet of marker tags for retaining and release clip 095.91.3 plastic, 72 tags, 6x12 mm			060.72
Technical data			
Rated values		10 A - 250 V	
Dielectric strength		6 kV (1.2/50 µs) between coil and contacts	
Protection category		IP 20	
Ambient temperature		°C -25...+70	
Wire strip length		mm 8	
Max. wire size for 95.55 socket		solid wire	stranded wire
		mm ² 2x(0.2...1.5)	2x(0.2...1.5)
		AWG 2x(24...18)	2x(24...18)



86 series timer modules	
(12...24)V AC/DC; Bi-function: AI, DI; (0.05s...100h)	86.30.0.024.0000

Approvals

(according to type):




Approvals
(according to type):



99.02 coil indication and EMC suppression modules for 95.55 socket		
Diode (+A1, standard polarity)	(6...220)V DC	99.02.3.000.00
LED	(6...24)V DC/AC	99.02.0.024.59
LED	(28...60)V DC/AC	99.02.0.060.59
LED	(110...240)V DC/AC	99.02.0.230.59
LED + Diode (+A1, standard polarity)	(6...24)V DC	99.02.9.024.99
LED + Diode (+A1, standard polarity)	(28...60)V DC	99.02.9.060.99
LED + Diode (+A1, standard polarity)	(110...220)V DC	99.02.9.220.99
LED + Varistor	(6...24)V DC/AC	99.02.0.024.98
LED + Varistor	(28...60)V DC/AC	99.02.0.060.98
LED + Varistor	(110...240)V DC/AC	99.02.0.230.98
RC circuit	(6...24)V DC/AC	99.02.0.024.09
RC circuit	(28...60)V DC/AC	99.02.0.060.09
RC circuit	(110...240)V DC/AC	99.02.0.230.09
Residual current by-pass	(110...240)V AC	99.02.8.230.07

DC Modules with
non-standard polarity
(+A2) on request.



95.55.3

Approvals
(according to type):




095.91.3



060.72

Screwless terminal socket panel or 35 mm rail mount	95.55.3 (blue)	95.55.30 (black)
For relay type	44.52, 44.62	
Accessories		
Metal retaining clip		095.71
Plastic retaining and release clip (supplied with socket - packaging code SPA)		095.91.3
Identification tag		095.00.4
Modules (see table below)		99.80
Sheet of marker tags for retaining and release clip 095.91.3 plastic, 72 tags, 6x12 mm		060.72
Technical data		
Rated values	10 A - 250 V	
Dielectric strength	6 kV (1.2/50 µs) between coil and contacts	
Protection category	IP 20	
Ambient temperature	°C	-25...+70
Wire strip length	mm	8
Max. wire size for 95.55.3 socket	solid wire	stranded wire
	mm ²	2x(0.2...1.5)
	AWG	2x(24...18)



99.80

Approvals
(according to type):



* Modules in Black
housing are
available on request.

Green LED is standard.
Red LED available
on request.

99.80 coil indication and EMC suppression modules for 95.55.3 socket		Blue*
Diode (+A1, standard polarity)	(6...220)V DC	99.80.3.000.00
LED	(6...24)V DC/AC	99.80.0.024.59
LED	(28...60)V DC/AC	99.80.0.060.59
LED	(110...240)V DC/AC	99.80.0.230.59
LED + Diode (+A1, standard polarity)	(6...24)V DC	99.80.9.024.99
LED + Diode (+A1, standard polarity)	(28...60)V DC	99.80.9.060.99
LED + Diode (+A1, standard polarity)	(110...220)V DC	99.80.9.220.99
LED + Varistor	(6...24)V DC/AC	99.80.0.024.98
LED + Varistor	(28...60)V DC/AC	99.80.0.060.98
LED + Varistor	(110...240)V DC/AC	99.80.0.230.98
RC circuit	(6...24)V DC/AC	99.80.0.024.09
RC circuit	(28...60)V DC/AC	99.80.0.060.09
RC circuit	(110...240)V DC/AC	99.80.0.230.09
Residual current by-pass	(110...240)V AC	99.80.8.230.07




95.15.2

Approvals
(according to type):



PCB socket	95.15.2 (blue)	95.15.20 (black)
For relay type	44.52, 44.62	
Accessories		
Metal retaining clip (supplied with socket - packaging code SMA)		095.51
Plastic retaining clip		095.52
Technical data		
Rated values	10 A - 250 V	
Dielectric strength	6 kV (1.2/50 µs) between coil and contacts	
Protection category	IP 20	
Ambient temperature	°C -40...+70	



Packaging codes

How to code and identify retaining clip and packaging options for sockets.

Example:

