

Productname : ECO Foam Cleaner Creationdate : 04.03.21 Version : 4.1
 Ref.Nr.: BDS000489_3_20210304 (EN) Replaces: BDS000489_20180503

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

ECO Foam Cleaner
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe BV
 Touwslagerstraat 1
 9240 Zele
 Belgium
 Tel.: +32(0)52/45.60.11
 Fax.: +32(0)52/45.00.34
 E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Smedsgatan 3-5 LT4, PL62, 08101 LOJO	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosol, category 3
 Pressurised container: May burst if heated.

Classification is based on test data.

Health: Serious eye damage, category 1



Productname :	ECO Foam Cleaner	Creationdate :	04.03.21 Version : 4.1
Ref.Nr.:	BDS000489_3_20210304 (EN)	Replaces:	BDS000489_20180503

Causes serious eye damage.

Classification based on calculation method.

Environment: Not classified

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
Alcohol C10, ethoxylated

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H229 : Pressurised container: May burst if heated.
H318 : Causes serious eye damage.

Precautionary statement(s): P102 : Keep out of reach of children.
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P251 : Do not pierce or burn, even after use.
P305/351/338 : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P313 : Get medical advice/attention.
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501-2 : Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information: 7 % by mass of the contents are flammable.

Regulation (EC) No 648/2004 on detergents: aliphatic hydrocarbons < 5 %
anionic surfactants < 5 %
non-ionic surfactants < 5 %
benzisothiazolinone, methylchlorisothiazolinone,
methylisothiazolinone, methylisothiazolinone,
methylchlorisothiazolinone

Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.



Productname : ECO Foam Cleaner **Creationdate :** 04.03.21 Version : 4.1
Ref.Nr.: BDS000489_3_20210304 (EN) **Replaces:** BDS000489_20180503

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Alcohol C10, ethoxylated	-	26183-52-8	500-046-6	1-5	Acute Tox. 4, Eye Dam. 1	H302,H318	F,X
(2-methoxymethylethoxy)propanol	01-2119450011-60	34590-94-8	252-104-2	1-5	-	-	A
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926-20	68512-91-4	270-990-9	1-5	Press. Gas, Flam. Gas 1	H280,H220	K,G

Explanation notes

A : substance with Community workplace exposure limit

F : not registered due to polymer status (no longer polymer list - directive 92/32/EEC)

G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

X : SCL (specific concentration limit)in accordance with art.10 of CLP Regulation No 1272/2008

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with water for at least 15 minutes Seek immediate medical attention
Contact with skin :	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	Causes serious eye damage. Symptoms : redness and pain, impaired vision

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---



Productname : ECO Foam Cleaner
Ref.Nr.: BDS000489_3_20210304 (EN)

Creationdate : 04.03.21 Version : 4.1
Replaces: BDS000489_20180503

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container
This material and/or its container must be disposed of as hazardous waste.

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed



Productname : ECO Foam Cleaner
Ref.Nr.: BDS000489_3_20210304 (EN)
Creationdate : 04.03.21 Version : 4.1
Replaces: BDS000489_20180503

Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.
 Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Precision

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, United Kingdom			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, Ireland			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
		STEL	-

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with ABEK type cartridge
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
eyes :	Wear safety eyewear according to EN 166.



Productname : ECO Foam Cleaner Creationdate : 04.03.21 Version : 4.1
Ref.Nr.: BDS000489_3_20210304 (EN) Replaces: BDS000489_20180503

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state : Propane/butane propelled liquid.
colour : White.
odour : Neutral.
pH : 11
Boiling point/range : 100 °C
Flash point : None
Evaporation rate : Not available.
Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : Not available.
Relative density : 1.01 g/cm³ (@ 20°C).
Solubility in water : Soluble in water
Auto-ignition : > 200 °C
Viscosity : Not applicable.

9.2. Other information

VOC = volatile organic compounds 69 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent



Productname : ECO Foam Cleaner Creationdate : 04.03.21 Version : 4.1
 Ref.Nr.: BDS000489_3_20210304 (EN) Replaces: BDS000489_20180503

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity: based on available data the classification criteria are not met
skin corrosion/irritation: based on available data the classification criteria are not met
serious eye damage/irritation: Causes serious eye damage.
respiratory or skin sensitisation: based on available data the classification criteria are not met
germ cell mutagenicity: based on available data the classification criteria are not met
carcinogenicity: based on available data the classification criteria are not met
toxicity for reproduction: based on available data the classification criteria are not met
STOT-single exposure: based on available data the classification criteria are not met
STOT repeated exposure: based on available data the classification criteria are not met
aspiration hazard: based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact : Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis
Eye contact : Causes serious eye damage.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
Alcohol C10, ethoxylated	26183-52-8	LD50 oral rat	1000 mg/kg
		LD50 derm.rat	> 2000 mg/kg
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 10000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified

Ecotoxicological data:



Productname : ECO Foam Cleaner
Ref.Nr.: BDS000489_3_20210304 (EN)

Creationdate : 04.03.21 Version : 4.1
Replaces: BDS000489_20180503

Hazardous ingredient	CAS-nr.	method	
Alcohol C10, ethoxylated	26183-52-8	IC50 algae	< 47 mg/l
		LC50 fish	< 7 mg/l
		EC50 daphnia	5.3 mg/l
(2-methoxymethylethoxy)propanol	34590-94-8	IC50 algae	> 100 mg/l
		LC50 fish	> 10000 mg/l
		EC50 daphnia	> 100 mg/l

12.2. Persistence and degradability

Readily biodegradable - OECD 301B

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Soluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available
GWP (global warming potential): 0

SECTION 13: Disposal considerations

13.1. Waste treatment methods

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.2
ADR/RID - Classification code: 5A



Productname : ECO Foam Cleaner
Ref.Nr.: BDS000489_3_20210304 (EN)

Creationdate : 04.03.21 Version : 4.1
Replaces: BDS000489_20180503

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (E)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008 (CLP)
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: - : -
H220 : Extremely flammable gas.
H280 : Contains gas under pressure; may explode if heated.
H302 : Harmful if swallowed.
H318 : Causes serious eye damage.

acronyms and synonyms: TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistent bioaccumulative toxic
vPvB = very persistent very bioaccumulative



Productname :	ECO Foam Cleaner	Creationdate :	04.03.21 Version : 4.1
Ref.Nr.:	BDS000489_3_20210304 (EN)	Replaces:	BDS000489_20180503

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

