



SAFETY DATA SHEET

Isoclene 250ml Pump Spray

According to Preparation of Safety Data Sheets for Hazardous Chemicals Code of Practice, February 2016

SECTION 1: Identification: Product identifier and chemical identity

Product identifier

Product name Isoclene 250ml Pump Spray

Product No. AISO250, ZA

Relevant identified uses of the substance or mixture and uses advised against

Application Cleaning agent.

Uses advised against No specific uses advised against are identified.

Details of the supplier of the safety data sheet

Supplier GENERAL MANAGER
HK WENTWORTH PTY LIMITED
PO BOX 7336
WARRINGAH MALL
BROOKVALE NSW 2100
AUSTRALIA

SYNERGY ELECTRONICS LTD
39 RICHARD PEARSE DRIVE
AIRPORT OAKS
AUCKLAND 3045

AUSTRALIA TEL: +61 (0) 2 9938 1566, FAX: +61 (0) 2 9938 1467
NEW ZEALAND TEL: +64 (0) 9 836 6588, FAX: +64 (0) 9 836 9169
sales@hkwentworth.com.au

Emergency telephone number

Emergency telephone IN CASE OF EMERGENCY CALL:
+61 2 8014 4558 (Australia) (24hr, Provided by Carechem 24)
+64 9 929 1483 (New Zealand) (24hr, Provided by Carechem 24)

SECTION 2: Hazard(s) identification

Classification of the substance or mixture


Physical hazards Flam. Liq. 2 - H225

Health hazards Eye Irrit. 2A - H319 STOT SE 3 - H336

Environmental hazards Not Classified

Label elements

Hazard pictograms



Isoclene 250ml Pump Spray

Signal word	DANGER
Hazard statements	H225 Highly flammable liquid and vapour. H319 Causes serious eye irritation. H336 May cause drowsiness or dizziness.
Precautionary statements	P210 Keep away from heat/ sparks/ open flames/ hot surfaces. - No smoking. P240 Ground/ bond container and receiving equipment. P241 Use explosion-proof electrical equipment. P242 Use only non-sparking tools. P243 Take precautionary measures against static discharge. P261 Avoid breathing vapour/ spray. P264 Wash contaminated skin thoroughly after handling. P271 Use only outdoors or in a well-ventilated area. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower. P304+P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P312 Call a POISON CENTER or doctor/ physician if you feel unwell. P337+P313 If eye irritation persists: Get medical advice/ attention. P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog for extinction. P403+P233 Store in a well-ventilated place. Keep container tightly closed. P403+P235 Store in a well-ventilated place. Keep cool. P405 Store locked up. P501 Dispose of contents/ container in accordance with national regulations.
Contains	Propan-2-ol

Other hazards

This product does not contain any substances classified as PBT (persistent, bioaccumulative and toxic) or vPvB (very persistent and very bioaccumulative).

SECTION 3: Composition and information on ingredients

Mixtures

Propan-2-ol	60-100%
CAS number: 67-63-0	
Classification	
Flam. Liq. 2 - H225	
Eye Irrit. 2A - H319	
STOT SE 3 - H336	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

Description of first aid measures

General information Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.

Isoclene 250ml Pump Spray

Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Get medical attention. Place unconscious person on their side in the recovery position and ensure breathing can take place.
Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Never give anything by mouth to an unconscious person. Place unconscious person on their side in the recovery position and ensure breathing can take place. Keep affected person under observation. Get medical attention.
Skin Contact	Rinse with water.
Eye contact	Rinse with water. Do not rub eye. Remove any contact lenses and open eyelids wide apart. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.
Ingestion	No specific symptoms known.
Skin contact	No specific symptoms known.
Eye contact	Irritating to eyes.

Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures

Extinguishing media

Suitable extinguishing media	The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up. Flammable liquid and vapour. Vapours may be ignited by a spark, a hot surface or an ember. Vapours may form explosive mixtures with air. Fire-water run-off in sewers may create fire or explosion hazard.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

Advice for firefighters

Isoclene 250ml Pump Spray

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Keep upwind to avoid inhalation of gases, vapours, fumes and smoke. Ventilate closed spaces before entering them. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to Australia/New Zealand Standards AS/NZS 4967 (for clothing) AS/NZS 1801 (for helmets), AS/NZS 4821 (for protective boots), AS/NZS 1801 (for protective gloves) will provide a basic level of protection for chemical incidents.
Hazchem Code	•2YE

SECTION 6: Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions	Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Evacuate area. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated. Avoid inhalation of dust and vapours. Use suitable respiratory protection if ventilation is inadequate.
-----------------------------	---

Environmental precautions

Environmental precautions	Avoid discharge into drains or watercourses or onto the ground.
----------------------------------	---

Methods and material for containment and cleaning up

Methods for cleaning up	Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Do not allow material to enter confined spaces, due to the risk of explosion. Absorb small quantities with paper towels and evaporate in a safe place. Once evaporation is complete, place paper in a suitable waste disposal container and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.
--------------------------------	--

Reference to other sections

Reference to other sections	For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.
------------------------------------	---

SECTION 7: Handling and storage, including how the chemical may be safely used

Precautions for safe handling

Usage precautions	Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.
--------------------------	--

Advice on general occupational hygiene	Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse.
---	--

Conditions for safe storage, including any incompatibilities

Isoclene 250ml Pump Spray

Storage precautions	Store locked up. Keep away from oxidising materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.
Storage class	Flammable liquid storage.
<u>Specific end use(s)</u>	
Specific end use(s)	The identified uses for this product are detailed in Section 1.

SECTION 8: Exposure controls and personal protection

Control parameters

Occupational exposure limits

Propan-2-ol

Long-term exposure limit (8-hour TWA): 400 ppm 983 mg/m³

Short-term exposure limit (15-minute): 500 ppm 1230 mg/m³

Exposure controls

Protective equipment



Appropriate engineering controls	Provide adequate ventilation.
Eye/face protection	Avoid contact with eyes. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.
Hand protection	No specific hand protection recommended.
Other skin and body protection	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
Hygiene measures	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
Respiratory protection	No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.
Environmental exposure controls	Keep container tightly sealed when not in use. Avoid release to the environment.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	Characteristic.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	12°C Closed cup.

Isoclene 250ml Pump Spray

Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Flammability Limit - Lower(%)	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.7855 @ 20°C
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

SECTION 10: Stability and reactivity

Reactivity	There are no known reactivity hazards associated with this product.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	The following materials may react strongly with the product: Oxidising agents.
Conditions to avoid	Avoid heat, flames and other sources of ignition. Containers can burst violently or explode when heated, due to excessive pressure build-up. Static electricity and formation of sparks must be prevented.
Materials to avoid	Oxidising materials. Acids - oxidising.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Isoclene 250ml Pump Spray

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

Contains a substance which may be potentially carcinogenic. IARC Group 3 Not classifiable as to its carcinogenicity to humans.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H336 May cause drowsiness or dizziness.

Target organs Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.

Ingestion

No specific symptoms known.

Skin Contact

No specific symptoms known.

Eye contact

Irritating to eyes.

Route of exposure

Ingestion Inhalation Skin and/or eye contact

Target Organs

Central nervous system

Toxicological information on ingredients.

Propan-2-ol

Acute toxicity - oral

Notes (oral LD₅₀)

Based on available data the classification criteria are not met.

Isoclene 250ml Pump Spray

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Genotoxicity - in vivo Chromosome aberration: Negative. EU REACH dossier information. Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H336 May cause drowsiness or dizziness.

Target organs Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.

Ingestion

No specific symptoms known.

Isoclene 250ml Pump Spray

Skin Contact	No specific symptoms known.
Eye contact	Irritating to eyes.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target Organs	Central nervous system

SECTION 12: Ecological information

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

Ecological information on ingredients.

Propan-2-ol

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

Toxicity Based on available data the classification criteria are not met.

Ecological information on ingredients.

Propan-2-ol

Toxicity Based on available data the classification criteria are not met.

Acute aquatic toxicity

Acute toxicity - fish LC₅₀, 96 hours: 10000 mg/l, Pimephales promelas (Fat-head Minnow)

Acute toxicity - aquatic invertebrates LC₅₀, 24 hours: >10000 mg/l, Daphnia magna

Acute toxicity - aquatic plants EC₅₀, 7 days: 1800 mg/l, Scenedesmus quadricauda

Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Ecological information on ingredients.

Propan-2-ol

Persistence and degradability The degradability of the product is not known.

Biodegradation Water - Degradation 53%: 5 days

Biological oxygen demand 1.19-1.72 g O₂/g substance

Chemical oxygen demand 2.23 g O₂/g substance

Bioaccumulative potential

Bioaccumulative Potential No data available on bioaccumulation.

Partition coefficient Not available.

Ecological information on ingredients.

Propan-2-ol

Isoclene 250ml Pump Spray

Bioaccumulative Potential No data available on bioaccumulation.

Mobility in soil

Mobility No data available.

Ecological information on ingredients.

Propan-2-ol

Mobility No data available.

Other adverse effects

Other adverse effects None known.

Ecological information on ingredients.

Propan-2-ol

Other adverse effects None known.

SECTION 13: Disposal considerations

Waste treatment methods

General information The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

UN number

UN No. (ADG) 1219

UN No. (IMDG) 1219

UN No. (ICAO) 1219

UN proper shipping name

Proper shipping name (ADG) ISOPROPANOL (ISOPROPYL ALCOHOL)

Proper shipping name (IMDG) ISOPROPANOL (ISOPROPYL ALCOHOL)

Proper shipping name (ICAO) ISOPROPANOL (ISOPROPYL ALCOHOL)

Transport hazard class(es)

ADG class 3

ADG classification code F1

ADG label 3

IMDG class 3

ICAO class/division 3

Isoclene 250ml Pump Spray

Transport labels



Packing group

ADG packing group	II
IMDG packing group	II
ICAO packing group	II

Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

Special precautions for user

EmS	F-E, S-D
Hazchem Code	•2YE

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

Inventories

Australia - AICS

None of the ingredients are listed or exempt.

SECTION 16: Any other relevant information

Training advice	Read and follow manufacturer's recommendations.
Issued by	Toni Ashford
Revision date	24/05/2016
Revision	1
SDS No.	195
Hazard statements in full	H225 Highly flammable liquid and vapour. H319 Causes serious eye irritation. H336 May cause drowsiness or dizziness.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.