Ref.Nr.:

Regulation EC No 1907/2006 Art.31

Rost Flash Productname:

BDS000206_3_20170629 (EN)

Creationdate: Replaces:

29.06.17 Version: 3.0 BDS000206_20130923

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Rost Flash

Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Lubricants

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe byba Touwslagerstraat 1 9240 Zele **Belgium**

Tel.: +32(0)52/45.60.11 Fax.: +32(0)52/45.00.34 E-mail: hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Laurinkatu 57 A 23 B, 08100 Lohja	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTR. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1

Extremely flammable aerosol.

Pressurised container: May burst if heated.

Classification is based on test data.



Regulation EC No 1907/2006 Art.31

Productname :Rost FlashCreationdate :Ref.Nr.:BDS000206 3 20170629 (EN)Replaces:

Creationdate : 29.06.17 Version : 3.0 **Replaces:** BDS000206_20130923

Health: Skin irritation, category 2 Causes skin irritation.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 3

Harmful to aquatic life with long lasting effects.

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Hazard pictogram(s):





Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.

H229: Pressurised container: May burst if heated.

H315: Causes skin irritation.

H412: Harmful to aquatic life with long lasting effects.

Precautionary statement(s): P102 : Keep out of reach of children.

P210: Keep away from heat, hot surfaces, sparks, open flames and other

ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use.

P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area.

P410/412: Protect from sunlight. Do not expose to temperatures exceeding

50°C/122°F.

P501-2: Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information:

None

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS- nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01- 2119485926- 20	68512- 91-4	270- 990-9	50- 75	Press. Gas, Flam. Gas 1	H280,H220	K,G
Hvdrocarbons. C6-C7. n-	01-	-	(921-	<25	Flam. Lig. 2. Skin Irrit.	H225.H315.H336.H304.H411	B.Q



Regulation EC No 1907/2006 Art.31

 Productname :
 Rost Flash
 Creationdate :
 29.06.17 Version : 3.0

 Ref.Nr.:
 BDS000206_3_20170629 (EN)
 Replaces:
 BDS000206_20130923

alkanes,isoalkanes,cyclics,< 5% n-hexane	2119475514- 35		024-6)		2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2		
Hydrocarbons, C13-15, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01- 2119453414- 43	-	(920- 107-4)	5-10	Asp. Tox. 1	H304	B,Q
mineral oil (IP 346 DMSO extract < 3%)	-	-	-	1-5	-	-	В
(2-methoxymethylethoxy)propanol	01- 2119450011- 60	34590- 94-8	252- 104-2	<2.5	-	-	A

Explanation notes

A : substance with Community workplace exposure limit

B: substance with national established workplace exposure limit

G: exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006

K: not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Q: The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes:

	If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse.
	IF ON SKIN: Wash with plenty of soap and water.
	If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Call a POISON CENTER or doctor/physician if you feel unwell.

Ingestion: If swallowed do not induce vomiting because of risk of aspiration into the lungs.

If aspiration is suspected obtain immediate medical attention

If substance has got into eyes, immediately wash out with plenty of water

4.2. Most important symptoms and effects, both acute and delayed

Inhalation : Excessive inhalation of solvent vapours may give rise to nausea, headaches

and dizziness

Ingestion: After vomiting of swallowed product aspiration into lungs is likely. Solvents may

induce chemical pneumonia.

Symptoms: sore throat, abdominal pain, nausea, vomiting

Skin contact : Irritating to skin

Symptoms: redness and pain

Eye contact : May cause irritation.

Symptoms: redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice: If you feel unwell, seek medical advice (show the label where possible

If symptoms persist always call a doctor



^{(*} Explanation phrases : see chapter 16)

Regulation EC No 1907/2006 Art.31

Productname: R

Ref.Nr.:

Rost Flash

BDS000206 3 20170629 (EN)

Creationdate : Replaces:

29.06.17 Version : 3.0 BDS000206 20130923

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C Forms hazardous decomposition products CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources Ensure adequate ventilation Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Ensure adequate ventilation

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.



Regulation EC No 1907/2006 Art.31

Productname: Rost Flash

Ref.Nr.: BDS000206 3 20170629 (EN) Creationdate: Replaces:

29.06.17 Version: 3.0 BDS000206 20130923

Avoid contact with skin and eyes.

Wash thoroughly after use

Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Keep out of reach of children.

7.3. Specific end use(s)

Lubricants

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits:

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm

8.2. Exposure controls

Control procedures: Ensure adequate ventilation

Keep away from heat and sources of ignition

Take precautionary measures against static discharges

Personal protection: Take precautions to avoid contact with skin and eyes when handling the

product.

In all cases handle and use the product in accordance with good industrial

hygiene practices.

Ensure adequate ventilation

inhalation: In case of insufficient ventilation, wear suitable respiratory equipment.

recommended respiratory protection: Air purifying respirator equiped with organic gas/vapor cartridge (type A) hands and skin:

When handling the product wear chemical-resistant gloves (standard EN 374). Use a reusable glove with a minimum breakthrough time of 30 minutes. The

breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be

changed part-way through. Nitrile Recommended gloves:

Wear safety eyewear according to EN 166. eyes:

Environmental protection: Avoid release to the environment.

Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties



Regulation EC No 1907/2006 Art.31

Productname: Rost Flash

Ref.Nr.: BDS000206_3_20170629 (EN)

Creationdate : Replaces:

29.06.17 Version : 3.0 BDS000206_20130923

(for aerosols data for the product without propellant)

Apperance : physical state : Propane/butane propelled liquid.

colour: Amber.

odour :Characteristic odor.pH :Not applicable.Boiling point/range :65-270 °C

Flash point: - 45 °C (Closed Cup)

Evaporation rate: Not available.

Explosion limits: upper limit: Not available.

lower limit: Not available.

Vapour pressure: Not available.

Relative density: 0.740 g/cm3 (@ 20°C).

Solubility in water: Insoluble in water

Auto-ignition: Not available.

Viscosity: Not available.

9.2. Other information

VOC = volatile organic

compounds

94 %

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2



Regulation EC No 1907/2006 Art.31

Productname: Re

Ref.Nr.:

Rost Flash

BDS000206_3_20170629 (EN)

Creationdate : Replaces:

29.06.17 Version : 3.0 BDS000206_20130923

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	Causes skin irritation.
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	based on available data the classification criteria are not met
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and

dizziness

Ingestion: After vomiting of swallowed product aspiration into lungs is likely. Solvents may

induce chemical pneumonia.

Skin contact: Irritating to skin

Eye contact: May cause irritation.

Toxicological data:

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 10000 mg/kg
Hydrocarbons, C13-15, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 4951 mg/l
		LD50 derm.rabit	> 5000 mg/kg
Hydrocarbons, C6-C7, n-alkanes,isoalkanes,cyclics,< 5% n-hexane	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 25000 mg/m3
		LD50 derm.rat	> 2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 3 Harmful to aquatic life with long lasting effects.

Ecotoxicological data:



Regulation EC No 1907/2006 Art.31

Productname: Rost Flash

Ref.Nr.: BDS000206_3_20170629 (EN)

Creationdate : Replaces:

29.06.17 Version : 3.0 BDS000206_20130923

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	IC50 algae	> 100 mg/l
		LC50 fish	> 10000 mg/l
		EC50 daphnia	> 100 mg/l
Hydrocarbons, C13-15, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	IC50 algae	1000 mg/l
		LC50 fish	1000 mg/l
		EC50 daphnia	1000 mg/l
Hydrocarbons, C6-C7, n-alkanes,isoalkanes,cyclics,< 5% n-hexane	-	LC50 fish	> 10 mg/l
		EC50 daphnia	3 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product: This material and its container must be disposed of in a safe way.

Do not discharge into drains or the environment, dispose to an authorised

waste collection point.

Contaminated packaging: Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. **UN** number

UN-number: 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS



Regulation EC No 1907/2006 Art.31

Productname:

Rost Flash

Ref.Nr.:

BDS000206 3 20170629 (EN)

Creationdate : Replaces:

29.06.17 Version : 3.0 BDS000206_20130923

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group:

Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous:

IMDG - Marine pollutant:

No IATA/ICAO - Environmentally hazardous:

14.6. Special precautions for user

 ADR/RID - Tunnelcode:
 (D)

 IMDG - Ems:
 F-D, S-U

 IATA/ICAO - PAX:
 203

 IATA/ICAO - CAO
 203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

Regulation (EC) No 1907/2006 (REACH)

Regulation (EC) No 1272/2008 (CLP)

Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: -:-

H220: Extremely flammable gas.

H225: Highly flammable liquid and vapour.

H280: Contains gas under pressure; may explode if heated.

H304 : May be fatal if swallowed and enters airways.



Regulation EC No 1907/2006 Art.31 **Safety Data Sheet**

Rost Flash 29.06.17 Version: 3.0 Productname: Creationdate: BDS000206_20130923 Ref.Nr.: BDS000206 3 20170629 (EN) Replaces:

H315: Causes skin irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE: 8.2. Exposure controls

acronyms and synonyms: TWA = time weight average

> STEL = short time exposure limit VOC = volatile organic compounds PBT = persistant bioaccumulative toxic vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks,no part of these documents may be reproduced by any process without written permission from CRC.

