



Cable Assembly Business Unit
No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351024

Issue : NA

Date : NA


Customer :

Specification : xxx

Issue : xxx

Date : xxx

All dimensions are in mm



Connectors designation :

Connector 1 : BNC Straight Plug Crimp Type for Cable 5/50D (R141.083.000)

Connector 2 : N Straight Plug Full-Crimp Type for Cable 5/50D (R161.083.000)

Cable designation :

Flexible Cable 5/50D (RG142)
C291.320.007

Nominal length :

Lg: 500mm

Cable colour :

Brown

Outer diameter :

4.95mm

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-4GHz

Insertion Loss max : 0.56dB max at 3GHz and 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 500 Veff max

MECHANICAL CHARACTERISTICS :

Recommend. Min. bending radius : 25 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -55°C to +155°C

Remark : NA

Attachment : R141.083.000-TDS

R161.083.000-TDS

C291.320.007(RG142)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name

Date

Jack Lv	A	2007-06-08	Creation	Garet Xie
Name	Issue	Date	Modification	Checked by



Cable Assembly Business Unit
No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351025

Issue : NA

Date : NA


Customer :

Specification : **xxxx**

Issue : **xxx**

Date : **xxx**

All dimensions are in mm



Connectors designation :

Connector 1 : BNC Straight Plug Crimp Type for Cable 5/50D (R141.083.000)

Connector 2 : N Straight Plug Full-Crimp Type for Cable 5/50D (R161.083.000)

Cable designation :

Flexible Cable 5/50D (RG142)

Nominal length :

C291.320.007

Cable colour :

Lg: 1m

Outer diameter :

Brown

4.95mm

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-4GHz

Insertion Loss max : 1.01dB max at 3GHz and 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 500 Veff max

MECHANICAL CHARACTERISTICS :

Recommend. Min. bending radius : 25 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -55°C to +155°C

Remark : NA

Attachment : R141.083.000-TDS

R161.083.000-TDS

C291.320.007(RG142)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jack Lv	A	2007-06-08	Creation	Garet Xie
Name	Issue	Date	Modification	Checked by