

917 Plug

9-pin insulation insert Code 3 male **EMC - Shielding** Connection Cross Section to 1.5 mm² Earth-to-Housing Connection according to VDE 0627

Technical Data

number of pins 4 (3+PE) power signal -20 °C to 130 °C temperature range clamping range

Ø 3.5 mm to Ø 6.0 mm when connected IP 66/67 protection type **Electrical Data** power signal

rated insulation voltage (L-L)

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

max. 14 A* 630V (AC/DC)

6000 V

500

max. 3.6 A* 63 V (AC/DC)

1500 V

pollution degree 3 III over voltage category max. height for operation 2000 m

Material

rated current rated voltage

mating cycles

zinc diecast / nickel plated PBT, UL 94 / V0 housing insulation insert

seals

clamp ring brass / nickel plated

Contacts (not part of product contents)

Tools (not part of product contents)

B ST A 906 NN 00 87 201A 000 B S A 906 N 00 87 201A 000



Contact Arrangement mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the notice. Specifications are subject to change without notice. Consult TE for the

latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mall: intercontec@te.com Web: www.intercontec.biz



