



SDT15H50P5

15A TRENCH SCHOTTKY BARRIER RECTIFIER PowerDI5

Product Summary (@ TA = +25°C)

V _{RRM} (V)	lo (A)	V _F (MAX) (V)	I _{R(MAX)} (mA)
50	15	0.47	0.50

Features and Benefits

- Low Forward Voltage Drop
- Excellent High Temperature Stability
- Soft, Fast Switching Capability
- +150°C Operating Junction Temperature
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
 Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/

Description and Applications

Packaged in the compact thermally efficient PowerDl $^{\otimes}$ 5 package, the SDT15H50P5 provides very low V_F and excellent reverse leakage stability at high temperatures. It is ideal for use as a rectifier, freewheel diode or blocking diode in:

- DC/DC Converters
- AC/DC Adaptors


Mechanical Data

- Case: PowerDI5
- Case Material: Molded Plastic, "Green" Molding compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
- Terminal Connections: See Diagram Below
- Weight: 0.093 grams (Approximate)

PowerDI5







Note: Pins Left & Right must be electrically connected at the printed circuit board.

Ordering Information (Note 4)

Top View

Part Number	Case	Packaging
SDT15H50P5-7	PowerDI5	1,500/Tape & Reel
SDT15H50P5-7D (Note 5)	PowerDI5	1,500/Tape & Reel
SDT15H50P5-13	PowerDI5	5,000/Tape & Reel
SDT15H50P5-13D (Note 5)	PowerDI5	5,000/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.
- 5. PowerDI5 available in 5K quantity on 13-inch reel & 12mm tape, part number suffix "13D"; Diodes Incorporated also provides 12mm tape with 7-inch reel, part number suffix "7D".

Marking Information



DIII = Manufacturers' Marking
D15H50 = Product Type Marking Code
YYWW = Date Code Marking
YY = Last Two Digits of Year (ex: 20 = 2020)
WW = Week Code (01 to 53)
K = Factory Designator

PowerDI is a registered trademark of Diodes Incorporated.



Maximum Ratings (@ $T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	Vrrm	50	٧
Average Rectified Output Current	lo	15	Α
Non-Repetitive Peak Forward Surge Current 8.3ms	IFSM	290	Α

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Typical Thermal Resistance Junction to Ambient (Note 6)	RθJA	100	°C/W
Typical Thermal Resistance Junction to Ambient (Note 7)	Reja	10	°C/W
Typical Thermal Resistance Junction to Case (Note 6)	Rejc	15	°C/W
Typical Thermal Resistance Junction to Case (Note 7)	R _{θJC}	2	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
Forward Voltage Drop	V	_	0.39	0.44		I _F = 10A, T _J = +25°C	
			_	_		I _F = 10A, T _J = +125°C	
	V _F	_	0.42	.42 0.47 V $I_F = 15A, T_J = +25^{\circ}C$	I _F = 15A, T _J = +25°C		
		_	_	_		I _F = 15A, T _J = +125°C	
Leakage Current (Note 8)	1-		_	0.15	0.5	A	V _R = 50V, T _J = +25°C
	IR	_	_	105	mA	$V_R = 50V, T_J = +125^{\circ}C$	

Notes:

- 6. FR-4 PCB, 2oz. copper, minimum recommended pad layout per http://www.diodes.com/package-outlines.html.
 7. Aluminum 2inch*2inch substrate PCB with 50mm x 50mm x 23mm Al heatsink.
 8. Short duration pulse test used to minimize self-heating effect.






Figure 1. Typical Forward Characteristics





Figure 2. Typical Reverse Characteristics




14 12 $T_1 = 150^{\circ}C$ P_D, AVERAGE FORWARD POWER DISSIPATION (W) 10 8 6 4 2 0 5 10 15 20 25 30 I_E(AV), AVERAGE FORWARD CURRENT (A) Figure 4. Forward Power Dissipation



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5




PowerDI5					
Dim	Min	Max	Тур		
Α	1.05	1.15	1.10		
A1	0.00	0.05			
A2	0.33	0.43	0.381		
b1	0.80	0.99	0.89		
b2	1.70	1.88	1.78		
D	3.90	4.05	3.966		
D2			3.054		
Е	6.40	6.60	6.51		
е			1.84		
E1	5.30	5.45	5.37		
E2			3.549		
L	0.75	0.95	0.85		
L1	0.50	0.65	0.57		
W	1.10	1.41	1.255		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

PowerDI5



Dimensions	Value (in mm)
С	1.840
G	0.852
Х	1.400
X1	4.860
X2	1.310
Y	1.390
Y1	3.360



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com