Waterproof D-Sub Connectors High Density, Cable Mount Solder Pin

multicomp PRO





Specifications:

Manufacturer Identifications : High Density D-SUB

Current Rating : 2A
Pin Configuration : 15

Material

Contact : Copper Alloy, Gold Plated

Connector Body : PBT or Nylon 9T Shield : Steel, Nickel Plated

Temperature Range

Cable : -20° C to $+80^{\circ}$ C (PVC) Connector Body- Panel : -40° C to $+100^{\circ}$ C Connector Body - Assembly : -20° C to $+80^{\circ}$ C


Electrical Characteristics

Contact Resistance : $10m\Omega$ Max.

Hi-Pot test: 1,000V AC 5mA (1 minute)Insulation Resistance: 100M Ω Min. by 500V DC

IP Rating : IP67

Diagram



Dimensions: Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Page <1> 07/01/21 V1.0

Waterproof D-Sub Connectors High Density, Cable Mount Solder Pin


multicomp PRO

MC000971



| No | Description | Qty | Material | Plating & Colour | |
|----|-------------|-----|-------------------|---|--|
| Α | Sealing Nut | 1 | PC | Black | |
| В | Seal | 1 | EPDM | Black | |
| С | Clamp Ring | 1 | PC | Black | |
| D | Screw | 2 | HBi59-1.5B | Nickel Plating 100μ" | |
| Е | O-Ring 1 | 1 | Silicon | Black | |
| F | O-Ring 2 | 2 | EPDM | Black | |
| G | O-Ring 3 | 2 | Silicone | Clear | |
| Н | Housing | 1 | ABS UL94V-0 | Black | |
| I | Female Pin | 15 | Phosphor Bronze | (1 to 3)µ" Gold plating over nickel plating | |
| J | Shell | 2 | Cold Roller Steel | Nickel Plating | |
| K | Insulator | 2 | PBT | Black | |
| L | Gasket | 1 | EPDM | Black | |

MC000972



| No | Description | Qty | Material | Plating & Colour |
|----|-------------|-----|--------------------|--|
| Α | Sealing Nut | 1 | PPE 540Z | Black |
| В | Seal | 1 | EPDM | Black |
| С | Clamp Ring | 1 | PPE 540Z | Black |
| D | Screw | 2 | HBi59-1.5B | Nickel Plating 100μ" |
| Е | O-Ring 1 | 1 | Silicon | Black |
| F | O-Ring 2 | 2 | EPDM | Black |
| G | O-Ring 3 | 2 | Silicone | Clear |
| Н | Housing | 1 | ABS 765A UL94V-0 | Black |
| I | Shell | 2 | Cold Roller Steel | Nickel Plating 60μ" |
| J | Insulator | 2 | PBT | Black |
| K | Male Pin | 15 | Brass (HBi59-1.5B) | (1 to 3)μ" Gold plating over nickel plating |
| L | Gasket | 1 | EPDM | Black |

Part Number Table

| Description | Part Number |
|--|-------------|
| Waterproof D-Sub 15 pin Female Connector; High Density, Solder pin cable mount | MC000971 |
| Waterproof D-Sub 15 pin Male Connector; High Density, Solder pin cable mount | MC000972 |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

