

Safe-IT Cat6a 10G Certified Snagless Antibacterial UTP Ethernet Cable (RJ45 M/M), White, 25-ft. (7.62 m)

MODEL NUMBER: N261AB-025-WH









Connects critical components, such as switches and servers, in 10G Ethernet networks, while also providing extra protection against bacteria.

Features

Cat6a Cable Ideal for Connecting Equipment in Your 10G Ethernet Network

This Cat6a Ethernet cable (M/M) with RJ45 connectors transmits 10 Gbps data, voice and video through high-speed 10G equipment, including network switches, modems, servers, routers, adapters, hubs and patch panels, in high-density data centers. Designed for fast transmission and excellent signal quality, this Cat6a cable ensures peak performance throughout your local area network (LAN).

Provides Extra Protection Against Certain Bacteria

The connectors and PVC jacket are constructed using an antibacterial material that is 99.9% effective in inhibiting Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this cable an ideal solution for medical facilities, schools, businnts/kitchens and anywhere else that wants extra protection against bacteria.

Snagless RJ45 Male Connectors Keep Tabs Intact During Installation

The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

Premium Construction for Superior Performance

Manufactured from 24 AWG copper wire, the four-pair stranded cable is rated for speeds up to 10 Gbps. The RJ45 connectors improve near-end crosstalk (NEXT) performance to 500 MHz and feature 3-micron gold plating to help ensure the most accurate signal transfer possible.

White Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The cable has a white PVC jacket, which is easy to identify quickly in a crowded patch panel or switch and helps prevent the cable from becoming accidentally disconnected.

Highlights

- Premium Cat6a cable rated for high-speed 10 Gbps home/office communications
- Made with antibacterial material proven 99.9% effective in inhibiting E. coli and staph
- Snagless RJ45 connectors protect locking tabs against damage during installation
- 24 AWG copper wire and 3 µm gold-plated contacts allow superior signal transfer
- White jacket permits fast, easy identification in a crowded switch or patch panel

Applications

- Connect a computer and its peripherals to a home or office 10G Ethernet network
- Connect switches, modems and servers in a high-density data center
- Provide extra protection against bacteria to give cable installers
 - and IT personnel peace of mind
- during installation

Package Includes

N261AB-025-WH Cat6a 10G Certified Snagless Antibacterial UTP Ethernet Cable (RJ45 M/M), White, 25-ft. (7.62 m)

Specifications

OVERVIEW	
UPC Code	037332259837
Technology	Cat6a



PHYSICAL		
Color	White	
Cable Shielding	UTP	
Cable Jacket Material	PVC	
Cable Jacket Rating	СМХ	
Cable Outer Diameter (OD)	6.2mm	
Number of Conductors	4 Pair	
Conductor Material	Stranded Copper	
Conductor Gauge	24 AWG	
Cable Length (ft.)	25	
Cable Length (m)	7.6	
Cable Length (in.)	300	
ENVIRONMENTAL		
Operating Temperature Range	14 to 122 F (-10 to 50 C)	
Storage Temperature Range	5 to 140 F (-15 to 60 C)	
Operating Humidity Range	0% TO 90% RH, NON-CONDENSING	
Storage Humidity Range	0% TO 90% RH, NON-CONDENSING	
COMMUNICATIONS		
Bandwidth per TIA Standard	500 MHz	
Maximum Bandwidth as Tested	600 MHz	
Network Speed	10Gbps	
CONNECTIONS		
Side A - Connector 1	RJ45 (MALE)	
Side B - Connector 1	RJ45 (MALE)	
Crossover Wiring	No	
Contact Plating	Gold	
Connector Type	Molded	
Wiring Configuration	EIA/TIA 568B	
FEATURES & SPECIFICATIONS		
Cable Style	Unshielded; Molded	
SPECIAL FEATURES		



IP68 Rated	No	
Snagless Connector	Yes	
Antibacterial	Yes	
STANDARDS & COMPLIANCE		
Certifications	RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies