



**Size 6x6 mm**

**Rated inductance 1  $\mu$ H .. 1000  $\mu$ H**

### Construction

- Ferrite core
- Winding: enamel copper wire
- Winding welded to terminals

### Features

- Wide temperature range
- High rated current
- Low DC resistance
- Suitable for reflow soldering

### Applications

- Filtering of supply voltages
- Coupling, decoupling
- DC/DC converters
- Automotive electronics

### Terminals

- Leadfree tinned

### Marking

Marking on component:

Manufacturer

L value (in  $\mu$ H) and tolerance (coded)

date code

Minimum marking on reel:

Manufacturer, part number, ordering code,

L value and tolerance

quantity, date of packing

### Delivery mode

Blister tape 12mm, reel packing


packaging quantity 2500 pcs per reel



General technical data

Rated inductance $L_R$	Measured with HP 4294A, measuring voltage 100 mV
Rated current $I_R$	Maximum permissible DC with temperature increase of $\leq 40$ K at ambient temperature of 85 °C
Saturation current	Maximum permissible DC with inductance decrease $\Delta L/L_0 \approx 10\%$
Climatic category	In accordance with IEC 60068-1 55/125/56 (-55 °C/ +125 °C/ 56 days damp heat test)
Solderability	5s, 235°C, wetting > 90%
Resistance to soldering heat	acc. to IEC 60068-2-58, leadfree reflow soldering profile
DC resistance $R_{max}$	Measured at 20 °C ambient temperature
Self-resonance frequency $f_{res}$	Measured with network analyzer HP 8753
Weight	Approx. 0,75g


Dimensional drawing and layout recommendation




**Characteristics and ordering codes**

$L_R$ $\mu\text{H}$	$f_L$ MHz	Tolerance	$I_R$ A	$I_{\text{sat}}$ A	$R_{\text{max}}$ $\Omega$	$f_{\text{res,min}}$ MHz	Ordering code
1,0	0,1	20 %	3,00	5,8	0,024	130	B82462-A4102-M
1,5	0,1	20 %	2,60	4,6	0,030	90	B82462-A4152-M
2,2	0,1	20 %	2,30	3,8	0,042	76	B82462-A4222-M
3,3	0,1	20 %	2,00	3,2	0,060	60	B82462-A4332-M
4,7	0,1	20 %	1,65	2,8	0,080	50	B82462-A4472-M
6,8	0,1	20 %	1,40	2,3	0,10	40	B82462-A4682-M
10	0,1	20 %	1,15	1,8	0,14	32	B82462-A4103-M
15	0,1	10 %	0,90	1,5	0,21	25	B82462-A4153-K
22	0,1	10 %	0,80	1,28	0,26	21	B82462-A4223-K
33	0,1	10 %	0,63	1,04	0,42	15	B82462-A4333-K
47	0,1	10 %	0,54	0,82	0,64	12	B82462-A4473-K
68	0,1	10 %	0,43	0,69	0,86	10	B82462-A4683-K
100	0,1	10 %	0,35	0,57	1,28	9,0	B82462-A4104-K
150	0,1	10 %	0,29	0,49	1,76	7,5	B82462-A4154-K
220	0,1	10 %	0,24	0,40	2,72	6,0	B82462-A4224-K
330	0,1	10 %	0,20	0,34	3,90	5,0	B82462-A4334-K
470	0,1	10 %	0,17	0,28	5,60	4,0	B82462-A4474-K
680	0,1	10 %	0,14	0,23	8,00	3,2	B82462-A4684-K
1000	0,1	10%	0,11	0,18	13,0	2,8	B82462-A4105-K

B82462-XXXX-X: current derating versus ambient temperature





**Size 6x6 mm**

**Rated inductance 0,82  $\mu$ H .. 330  $\mu$ H**

### Construction

- Ferrite core
- Magnetically shielded
- Winding: enamel copper wire
- Winding welded to terminals

### Features

- Wide temperature range
- High rated current
- Low DC resistance
- Suitable for reflow soldering

### Applications

- Filtering of supply voltages
- Coupling, decoupling
- DC/DC converters
- Automotive electronics

### Terminals

- Leadfree tinned

### Marking

Marking on component:

Manufacturer

L value (in  $\mu$ H) and tolerance (coded)

Date code

Minimum marking on reel:

Manufacturer, part number, ordering code,

L value and tolerance

quantity, date of packing

### Delivery mode

Blister tape 12mm, reel packing


packaging quantity 2500 pcs per reel



**General technical data**

Rated inductance $L_R$	Measured with HP 4294A, measuring voltage 100 mV
Rated current $I_R$	Maximum permissible DC with temperature increase of $\leq 40$ K at ambient temperature of 85 °C
Saturation current	Maximum permissible DC with inductance decrease $\Delta L/L_0 \approx 10\%$
Climatic category	In accordance with IEC 60068-1 55/125/56 (-55 °C/ +125 °C/ 56 days damp heat test)
Solderability	5s, 235°C, wetting > 90%
Resistance to soldering heat	acc. to IEC 60068-2-58, leadfree reflow soldering profile
Self-resonance frequency $f_{res}$	Measured with network analyzer HP 8753
DC resistance $R_{max}$	Measured at 20 °C ambient temperature
Weight	Approx. 1,5g

**Dimensional drawing**




**Characteristics and ordering codes**

$L_R$ $\mu\text{H}$	$f_L$ MHz	Tolerance	$I_{\text{sat}}$ A	$I_R$ A	$R_{\text{max}}$ $\Omega$	$f_{\text{res,typ}}$ MHz	Ordering code
0,82	0,1	20 %	4,45	3,45	0,015	182	B82462-G4821-M
1,0	0,1	20 %	4,40	3,40	0,016	180	B82462-G4102-M
1,5	0,1	20 %	3,60	3,10	0,020	100	B82462-G4152-M
2,2	0,1	20 %	2,60	2,55	0,025	75	B82462-G4222-M
3,3	0,1	20 %	2,15	2,30	0,031	60	B82462-G4332-M
4,7	0,1	20 %	1,80	2,00	0,040	55	B82462-G4472-M
6,8	0,1	20 %	1,50	1,65	0,050	40	B82462-G4682-M
10	0,1	20 %	1,30	1,50	0,062	31	B82462-G4103-M
15	0,1	20 %	1,05	1,25	0,097	23	B82462-G4153-M
22	0,1	20 %	0,85	1,05	0,15	20	B82462-G4223-M
33	0,1	20 %	0,72	0,85	0,23	16	B82462-G4333-M
47	0,1	20 %	0,60	0,75	0,34	13	B82462-G4473-M
68	0,1	20 %	0,50	0,65	0,42	10	B82462-G4683-M
100	0,1	20%	0,42	0,53	0,58	8,5	B82462-G4104-M
150	0,1	20 %	0,33	0,38	0,96	6,5	B82462-G4154-M
220	0,1	20 %	0,28	0,35	1,35	5,5	B82462-G4224-M
330	0,1	20 %	0,24	0,27	2,30	4,5	B82462-G4334-M

