

- Compact metal case with screw terminal block
- Universal input 85-264 VAC
- Convection cooled (no fan)
- High efficiency up to 90%
- Active PFC >0.95
- EMI/EMC compliance with EN 61000-6-3 and EN 61000-6-1
- Compliance to EN 61000-3-2
- Short circuit, overvoltage and overload protection
- IEC/EN/UL 62368-1 safety approvals
- 3 year product warranty



The TXLN series is a family of encased power supplies designed for a wide range of cost critical applications. With a low profile metal case and screw terminal block connection, they are easy to install in any equipment. These power supplies have universal input and comply with European EMC standards and the Low Voltage Directive (LVD).

Models				
Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TXLN 150-105	150 W	5 VDC (4.5 - 5.5 VDC)	30'000 mA	86 %
TXLN 150-112		12 VDC (10.8 - 13.2 VDC)	12'500 mA	88 %
TXLN 150-124		24 VDC (21.6 - 26.4 VDC)	6'300 mA	89 %
TXLN 150-148		48 VDC (43.2 - 52.8 VDC)	3'200 mA	90 %

### Input Specifications

Input Voltage	- AC Range	85 - 264 VAC (Full Range)
	- DC Range	120 - 375 VDC (Designed for, no certification)
Input Frequency		47 - 63 Hz
Input Current	- Full Load & Vin = 115 VAC	2'200 mA max.
Input Inrush Current	- At 230 VAC	45 A max.
	- At 115 VAC	25 A max.
Power Factor	- At 230 VAC	0.95 min. (Active Power Factor Correction)
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

### Output Specifications

Output Voltage Adjustment		±10% (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±2% max. (5 Vout model)
		±1% max. (other models)
Regulation	- Input Variation (Vmin - Vmax)	2% max. (5 Vout model) 1% max. (other models)
	- Load Variation (0 - 100%)	2% max. (5 Vout model) 1% max. (other models)
Ripple and Noise (20 MHz Bandwidth)	5 VDC model:	100 mVp-p max. (w/ 0.1 µF // 47 µF)
	12 VDC model:	100 mVp-p max. (w/ 0.1 µF // 47 µF)
	24 VDC model:	150 mVp-p max. (w/ 0.1 µF // 47 µF)
	48 VDC model:	200 mVp-p max. (w/ 0.1 µF // 47 µF)
Minimum Load		Not required
Hold-up Time	- At 230 VAC	16 ms min.
	- At 115 VAC	16 ms min.
Start-up Time	- At 230 VAC	2'500 ms max.
	- At 115 VAC	2'500 ms max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		105 - 150% of Iout max.
Overvoltage Protection		115 - 140% of Vout nom.

### Safety Specifications

Safety Standards	- IT / Multimedia Equipment	EN 62368-1 UL 62368-1
	- Certification Documents	<a href="http://www.tracopower.com/overview/txln150">www.tracopower.com/overview/txln150</a>
Protection Class		Class I (Prepared): Connection to PE
Pollution Degree		PD 2
Over Voltage Category		OVC II

### EMC Specifications

EMI Emissions		EN 61000-6-3 (Generic Residential)
	- Conducted Emissions	EN 55032 class B (internal filter)
	- Radiated Emissions	EN 55032 class B (internal filter)
	- Harmonic Current Emissions	EN 61000-3-2, class D
	- Voltage Fluctuations & Flicker	EN 61000-3-3

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

EMS Immunity	<ul style="list-style-type: none"> <li>- Electrostatic Discharge</li> <li>- RF Electromagnetic Field</li> <li>- EFT (Burst) / Surge</li> <li>- Conducted RF Disturbances</li> <li>- PF Magnetic Field</li> <li>- Voltage Dips &amp; Interruptions</li> </ul>	<p>EN 55024 (IT Equipment)</p> <p>Air: EN 61000-4-2, ±8 kV, perf. criteria A</p> <p>Contact: EN 61000-4-2, ±4 kV, perf. criteria A</p> <p>EN 61000-4-3, 3 V/m, perf. criteria A</p> <p>EN 61000-4-4, ±1 kV, perf. criteria A</p> <p>L to L: EN 61000-4-5, ±1 kV, perf. criteria A</p> <p>L to PE: EN 61000-4-5, ±2 kV, perf. criteria A</p> <p>EN 61000-4-6, 3 Vrms, perf. criteria A</p> <p>Continuous: EN 61000-4-8, 3 A/m, perf. criteria A</p> <p>230 VAC / 50 Hz: EN 61000-4-11</p> <p>30%, 25 periods, perf. criteria A</p> <p>&gt;95%, 0.5 periods, perf. criteria A</p> <p>&gt;95%, 250 periods, perf. criteria B</p>
--------------	--	---

### General Specifications


Relative Humidity		90% max. (non condensing)
Temperature Ranges	<ul style="list-style-type: none"> <li>- Operating Temperature</li> <li>- Storage Temperature</li> </ul>	<p>-30°C to +70°C</p> <p>-40°C to +85°C</p>
Power Derating	<ul style="list-style-type: none"> <li>- High Temperature</li> <li>- Low Input Voltage</li> </ul>	<p>2.5 %/K above 50°C</p> <p>0.66 %/V below 100 VAC</p>
Over Temperature Protection Switch Off	- Protection Mode	Automatic recovery
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote	<p>On: 0 to 0.8 VDC</p> <p>Off: 4 to 10 VDC</p> <p>Refers to '+Remote' and '-Remote' Pin</p>
Altitude During Operation		5'000 m max. (The ambient temperature has to be derated by 5 K / 1000 m when operated above 2000 m)
Switching Frequency		65 kHz typ. (PWM)
Insulation System		Reinforced Insulation
Isolation Test Voltage	<ul style="list-style-type: none"> <li>- Input to Output, 60 s</li> <li>- Input to Case or PE, 60 s</li> <li>- Output to Case or PE, 60 s</li> </ul>	<p>3'000 VAC</p> <p>1'800 VAC</p> <p>500 VAC</p>
Isolation Resistance	- Input to Output, 500 VDC	100 MΩ min.
Leakage Current (at 264 VAC / 60Hz)	- Touch Current	1500 μA max.
Reliability	- Calculated MTBF	162'800 h
Housing Material		Aluminium
Connection Type		Screw Terminal
Weight		560 g
Status Indicator		Indicated by green LED
Environmental Compliance	<ul style="list-style-type: none"> <li>- REACH Declaration</li> <li>- RoHS Declaration</li> </ul>	<p><a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a></p> <p>REACH SVHC list compliant</p> <p>REACH Annex XVII compliant</p> <p><a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a></p> <p>Exemptions: 6a, 6c, 7a, 7c-I, 7c-II</p>

### Supporting Documents

Overview Link (for additional Documents)	<a href="http://www.tracopower.com/overview/txln150">www.tracopower.com/overview/txln150</a>
--	--

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

**Outline Dimensions**



Screw Terminal	
Pin	Function
1	AC (L)
2	AC (N)
3	FG
4-5	-Vout
6-7	+Vout

JTS Connector	
Pin	Function
1	+Remote
2	-Remote

Dimensions in mm  
 Tolerances:  
 0 - 8: ±0.2  
 8 - 25: ±0.3  
 25 - 80: ±0.5  
 80 - 250: ±0.8

