

N Plug Crimp


multicomp PRO



Specifications:

Connector Type	: N Coaxial
Body Style	: Straight
Coaxial Termination	: Crimp
Impedance	: 50Ω
Contact Material	: Brass
Contact Plating	: Silver
Connector Mounting	: Cable
Approval Bodies	: MIL Spec
Cable Diameter Max	: 5mm
Coaxial Type	: RG58
Contact Resistance	: 1.5mΩ
Insulator Material	: PTFE
Operating Temperature	: -65°C to +165°C
Proof Voltage	: 2kV
VSWR	: 1.15
Working Voltage	: 1,500V

Diagram



Dimensions : Millimetres (Inches)

No	Description	Material	Finish
1	Centre Contact	Brass	Silver 70μ" Min.
2	Crimp Ferrule		
3	Shell		
4	Gasket	Silicone	Red
5	Body	Brass	Silver 70μ" Min.
6	Insulation	PTFE	None
7	Washer		
8	Chassis	Brass	Silver 70μ" Min.

Part Number Table

Description	Part Number
Plug, N, Crimp, 50Ω	MP-11-11-4 UTSS

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO