# CLD-CT1533.000

### Cree® PLCC6 3 in 1 SMD LED CLV6F-FKB

#### **PRODUCT DESCRIPTION**

CREE 🔶

These SMD LEDs are packaged in an industry standard PLCC6 package. These high performance tricolor SMT LEDs are designed to work in a wide range of applications. A wide viewing angle and high brightness make these LEDs suitable for various full color applications.

The encapsulation resin contains UV inhibitors to minimize the effects of long-term exposure to direct sunlight, resulting in stable light output over the life of the LED.

#### FEATURES

- Size (mm):5.5 x 5.5
- Dominant Wavelength: Red (619 - 624nm) Green (520 - 540nm) Blue (460 - 480nm)
- Luminous Intensity (mcd) Red (805-1600) Green (1600 - 3175) Blue (355-805)
- Moisture Sensitivity Level: 5a
- Lead-Free
- RoHS Compliant



#### **APPLICATIONS**

- Decorative lighting
- Amusement

#### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^{\circ}C$ )

Thomas	Complete	Ab	Absolute Maximum Rating				
Items	Symbol	R	G	В	Unit		
Forward Current Note 1	I <sub>F</sub>	50	mA				
Peak Forward Current Note 2	I <sub>FP</sub>	200	100	100	mA		
Reverse Voltage	V <sub>R</sub>	5	5	5	V		
Power Dissipation	P <sub>D</sub>	130	126	140	mW		
Operation Temperature	T <sub>opr</sub>	-40 ~ +85					
Storage Temperature	T <sub>stg</sub>	-40 ~ +100 °C					
Junction Temperature	T,	110	110	110	°C		
Junction/ambient	R <sub>THJA</sub>	450	400	450	°C/W		
Junction/solder point	R <sub>THJS</sub>	230	230	200	°C/W		
Electrostatic Discharge Classification(MIL-STD-883E)	ESD	1000 V					

#### **Note:** 1.Single-color light.

2.Pulse width  $\leq 0.1$  msec, duty  $\leq 1/10$ .

#### **TYPICAL ELECTRICAL & OPTICAL CHARACTERISTICS (T<sub>A</sub> = 25^{\circ}C)**

Characteristics	Condition	Symbol -		Unit		
Characteristics	Condition		R	G	В	Onic
Dominant Wavelength	$I_{F} = 20 \text{ mA}$	$\lambda_{_{ m DOM}}$	619~624	520~540	460~480	nm
Spectral bandwidth at 50% $I_{\rm \tiny REL}$ max	$I_F = 20 \text{ mA}$	Δλ	24	38	28	nm
Forward Voltage	$I_F = 20 \text{ mA}$	$V_{F(avg)}$	2.1	2.9	3.2	V
		V <sub>F(max)</sub>	2.6	3.6	4.0	V
	$I_{F} = 20 \text{ mA}$	I <sub>v(min)</sub>	805	1600	355	mcd
Luminous Intensity		$I_{V(avg)}$	1100	2600	600	mcd
Reverse Current (max)	$V_{R} = 5 V$	I <sub>R</sub>	10	10	10	μA

Note: Continuous reverse voltage can cause LED damage.

## CREE 🔶

#### **INTENSITY BIN LIMIT (I**<sub>F</sub> = 20 mA)

Red		
Bin Code	Min.(mcd)	Max.(mcd)
qr	805	1010
Ν	900	1120
st	1010	1260
Р	1120	1400
VW	1260	1600

Green		
Bin Code	Min.(mcd)	Max.(mcd)
ху	1600	2020
R	1800	2240
z1a	2020	2520
S	2240	2800
1b1c	2520	3175

Blue		
Bin Code	Min.(mcd)	Max.(mcd)
Н	355	450
hj	403	505
J	450	560
km	505	635
К	560	710
np	635	805

Tolerance of measurement of luminous intensity is  $\pm 10\%$ .

#### COLOR BIN LIMIT ( $I_F = 20 \text{ mA}$ )

Red			Gre	en			Blue		
Bin Code	Min.(nm)	Max.(nm)	Bi	n Code	Min.(nm)	Max.(nm)	Bin Code	Min.(nm)	Max.(nm)
RB	619	624		G7	520	525	B3	460	465
				G23	522.5	527.5	B23	462.5	467.5
				G8	525	530	B4	465	470
				G45	527.5	532.5	B45	467.5	472.5
				G9	530	535	B5	470	475
				G67	532.5	537.5	B67	472.5	477.5
				Ga	535	540	B6	475	480

Tolerance of measurement of dominant wavelength is  $\pm 1$  nm.

#### **ORDER CODE TABLE\***

		Luminous Int	tensity (mcd)	Dominant Wavelength (nm)				Pack-
Kit Number	Color	Min.	Max.	Color Bin	Min. (nm)	Color Bin	Max. (nm)	age
	Red	805	1600	RB	619	RB	624	Reel
CLV6F-FKB-Cqrvwxy1b1cHnpBB7a363	Green	1600	3175	G7	520	Ga	540	Reel
	Blue	355	805	B3	460	B6	480	Reel
	Red	Any 1 Intensity bin fro	RB	619	RB	624	Reel	
CLV6F-FKB-Cqr1xy1H1BB7D3D3	Green	Any 1 Intensity bin from	n xy(1600) - 1b1c(3175)	Any 1 hue bin from G7(520) - Ga			Ga(540)	Reel
	Blue	Any 1 Intensity bin fr	om H(355) - np(805)	Any 1 hue bin from B3(460) - B6(480)				Reel


Notes:

- 1. The above kit numbers represent the order codes which include multiple intensity-bin and color-bin codes.Only one intensity-bin code and one color-bin code will be shipped on each reel. Single intensity-bin code and single color-bin code will be orderable in certain quantities. For example, any 1 intensity bin from xy 1b1c means only 1 intensity bin (xy or R or z1a or S or 1b1c) will be shipped by Cree. For example, any 1 color bin from G7 Ga means only 1 color bin(G7 or G23 or G8 or G45 or G9 or G67 or Ga) will be shipped by Cree.
- 2. Please refer to the "Cree LED Lamp Reliability Test Standards" document <sup>#1</sup> for reliability test conditions.
- 3. Please refer to the "Cree LED Lamp Soldering & Handling" document <sup>#2</sup> for information about how to use this LED product safely.

#1: Refer to http://www.cree.com/led-components/media/documents/LED\_Lamp\_Reliability\_Test\_Standard.pdf #2: Refer to http://www.cree.com/led-components/media/documents/sh-HB.pdf




#### GRAPHS



The above data are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.



#### GRAPHS





The above data are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.



#### **MECHANICAL DIMENSIONS**

All dimensions are in mm.





#### **NOTES**

#### **RoHS** Compliance

The levels of RoHS-restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application in accordance with EU Directive 2011/65/EC (RoHS2), as implemented by EU member states on January 2, 2013 and amended on March 31, 2015 by EU Directive 2015/863/EU.

RoHS Declarations for this product can be obtained from your Cree representative or from the Product Ecology section of the Cree website.

#### Vision Advisory Claim


Users should be cautioned not to stare at the light of this LED product. The bright light can damage the eye.



#### **KIT NUMBER SYSTEM**

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options. Please refer to the "Cree LED Lamp Packaging Standard" document for more information about shipping and packaging options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



#### RELIABILITY

#### Tests and Results

ests and Results				
Test	Applicable Standards	Test Condition	Note	Number of Damaged
Temperature Cycle	JEITA ED-4701 100 105	-40°C~25°C~100°C~25°C 30 mins, 5 mins, 30 mins, 5 mins	100 cycles	0/45
Thermal Shock	MIL-STD-202G	-40°C~100°C 30 mins, 30 mins	100 cycles	0/45
Moisture Resistance	JEITA ED-4701 200 203	25°C~65°C~ 90%RH 24hrs/1cycle	10 cycles	0/45
High Temperature Storage	JEITA ED-4701 200 201	T <sub>A</sub> =100°C	500 hrs	0/45
Temperature Humidity Storage	JEITA ED-4701 100 103	T <sub>A</sub> =60°C RH=90%	500 hrs	0/45
Low Temperature Storage	JEITA ED-4701 200 202	T <sub>A</sub> =-40°C	500 hrs	0/45
High Temperature Life Test	-	T <sub>A</sub> =85°C I <sub>F</sub> =15 mA	1000 hrs	0/45
Life Test	-	T <sub>A</sub> =25°C IF: R=30mA G=35mA B=20mA	1000 hrs	0/45
High Humidity Heat Life Test	-	60°C RH=90% I <sub>F</sub> =15 mA	500 hrs	0/45
Low Temperature Life Test	-	Ta=-40°C IF: R=30mA G=35mA B=20mA	500 hrs	0/45
Resistance to Soldering Heat(Reflow Soldering)	JEITA ED-4701 300 301	T <sub>sol</sub> =235°C,10sec (Pre treatment 30°C,70%,168hrs)	2 times	0/45
Vibration-variable Frequency	MIL-STE-883 Method 2007	20G min, 20 to 2000Hz, 4cycles, 4mins, Each x,y,z	/	0/45
Electrostatic Discharge Test	AEC(Q101-001)	Human body model 1000 V (Forward and reverse current conduct electricity each 1time)	/	0/45


#### **Failure Criteria**

Item	Symbol	Test	Criteria for Judgment				
Item	Symbol	Condition	Min.	Max.			
Forward Voltage	V <sub>F</sub>	I <sub>F</sub> = 20 mA	– Initial Data x 1.1				
Reverse Current	I <sub>R</sub>	$V_{R} = 5 V$	- 10 µA				
Luminous Flux/Intensity	Φ <sub>v</sub>	$I_{F} = 20 \text{ mA}$	Initial Data x 0.7 -				
Resistance to Soldering Heat	-	$I_F = 20 \text{ mA}$	No dead lamps and visual damage				
Vibration-variable Frequency	-	$I_F = 20 \text{ mA}$	No dead lamps and visual damage				



#### **REFLOW SOLDERING**

- The CLV6F-FKB is rated as a MSL 5a product.
- The recommended floor life out of bag is 24hrs.
- The temperature profile is as below.



Use only with CLV6F-FKB

Time


Solder
Average ramp-up rate = $4^{\circ}C/s$ max
Preheat temperature = 150°C ~200°C
Preheat time = 120s max
Ramp-down rate = $6^{\circ}C/s$ max
Peak temperature = 250°C max
Time within 5°C of actual Peak Temperature = 10s max
Duration above 217°C is 60s max

Refer to "http://www.cree.com/led-components/media/documents/sh-HB.pdf" for soldering & handling details.



#### NOTES

- The packaging sizes of these SMD products are very small and the resin is still soft after solidification. Users are required to handle with care. Never touch the resin surface of SMD products.
- To avoid damaging the product's surface and interior device, it is recommended to choose a special nozzle to pick up the SMD products during the process of SMT production. If handling is necessary, take special care when picking up these products. The following method is necessary:





#### PACKAGING

- The boxes are not water resistant and they must be kept away from water and moisture.
- The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- Cardboard boxes will be used to protect the LEDs from mechanical shocks during transportation.
- The reel pack is applied in SMD LED.
- Max 3000 pcs per reel.

