



## Product Description



M



F



## Worth knowing

screw termination

occupies 2 slots in the MCR frame

### Suitable housing

EPIC® MCR 24

EPIC® MCR 16

EPIC® MCR 10

EPIC® MCR 6

EPIC® MC Modulösewerkzeug

EPIC® MCR 24

EPIC® MCR 16

EPIC® MCR 10

EPIC® MCR 6

### Accessories

## Technical Data

### Rated voltage in V

1000 V

### Rated current in A

82 A

### Contact resistance

< 2 mOhm

### Contacts

Copper alloy, hard silver plated

### Numbers of contacts

1 + PE

### Termination methods

Screw connection: 10,0 - 25,0 mm<sup>2</sup>

### Cycle of mechanical operation

100

### Range of temperature

-40°C - +100°C, temporary up to +125°C

### VDE-tested

VDE-REG.-No. 870

### Pollution degree

3



Article List

Part number	Part	Conductor cross-section in mm <sup>2</sup>	Version	Contacts	Rated voltage in V	Rated current in A	Pieces / VPE
Module: High Current 1 + PE (occupies 2 slots in the MCR frame)							
10344600	MCS-HC 1+PE	10 - 25	male	1 + PE	1000	82	5
10345600	MCB-HC 1+PE	10 - 25	female	1 + PE	1000	82	5